



PRODUCT NUMBER

10063544-XXX HT Z


INSPECTION LEVEL
SEE SHEET 2 INSPECTION TABLE
PACKAGE OPTION SEE NOTE 1
HIGH TEMPERATURE PLASTIC
SEE NOTE 1
NO OF
POSITIONS
SEE NOTE 1
PIN PLATING
SEE SHEET 2
BASE PART NO.



TOP VIEW



SIDE VIEW



END VIEW

Ø .020/0.51 (M) U (M) V (S)

NOTE 4
□ .025±.001
0.64±0.03
TYP
□ .013 MAX
0.33
TYP

DETAIL P
TYP BOTH ENDS


25°±5° TYP
4 SIDES

mat'l. code				surface		tolerance		projection		product family	
				ISO 1302		ISO 406		ISO 1101		BERGSTIK	
ltr	ecn	no	dr	date	tolerances unless otherwise specified	angles	linear	INCH/MM	scale 1:1	title	
A	M05-0247	MHT		11/23/05						BERGSTIK® II HDR. D/R	
B	M06-0107	MHT		3/07/06						.100 CTR.	
C	M06-0134	MHT		4/06/06							
D	M06-0243	MHT	dr	6/30/06	M.HERNANDEZ					dwg no	
E	M07-0262	MHT	enr	6/05/07	S.FIERRO					sheet 1 of 2 size	
F	M07-0272	MHT	chr	6/13/07	S.FIERRO					10063544	
G	M07-0380	MHT	appd	8/24/07	S.FIERRO					A3	
sheet	revision	G	G							type Product Customer Drawing	
index	sheet	1	2								

PRODUCT NUMBER	CUSTOMER P/N
10063544-X14HT	09R43641Z02
10063544-X26HT	09R43641Z01

INSPECTION LEVEL	DESCRIPTION
0%	NO VISUAL INSPECTION
100%	ADD 'A' AT THE END OF THE PART NUMBER FOR VISUAL INPSECTION
200%	ADD 'B' AT THE END OF THE PART NUMBER FOR VISUAL INPSECTION
300%	ADD 'C' AT THE END OF THE PART NUMBER FOR VISUAL INPSECTION

PIN PLATING CODES:	WIRE CODES:
10063544-4YYH	120u"/3.05u MIN 93/7 SnPb OVER 50u"/1.27u MIN Ni



DOUBLE ROW
RECOMMENDED HOLE PATTERN

NOTES

①. PART NUMBER OPTIONS:

PIN PLATING CODES (SEE ABOVE)

HIGH TEMP. MATERIAL:

FOR HIGH-TEMPERATURE APPLICATIONS, SPECIFY AN "H" AT THE END OF THE PART NUMBER.

NUMBER OF POSITION:

ANY NUMBER OF POSITIONS FROM 4 (2X2) THRU 72 (2X36).

PACKAGING:

PART NUMBERS FOLLOWED BY A "T" ARE PACKAGED IN TUBES. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.

②. BODY MATERIAL:

LCP THERMOPLASTIC, MINERAL FILLED MOLDING COMPOUND
FLAME RETARDENT PER UL-94V-0.
COLOR: BLACK

③. PIN MATERIAL: BRASS

④. MEASURED WITH PART IN RESTRAINED CONDITION.

5. TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS.

⑥. 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family BERGSTIK
ltr	ecn	no	dr	tolerances unless otherwise specified		scale 1:1	title BERGSTIK® II HDR. D/R .100 CTR.
G				angles	linear		
				0°±2°	linear		
dr				M.HERNANDEZ	11/04/05	FCJ	dwg no 10063544 sheet 2 of 2 size A3
enr				S.FIERRO	11/04/05		
chr				S.FIERRO	11/04/05		
app				S.FIERRO	11/04/05		
sheet index	revision	sheet					type Product Customer Drawing