



SAK-TC234LP-32F200N AC

Access to complete AURIX™ documentation!

1. Please register under myinfineon.com with your company e-mail address
2. Send login name to: AURIX@infineon.com
3. Automated update service will be provided for new documents once you are registered

[More Information](#)

Parametrics

Parametrics	SAK-TC234LP-32F200N AC
A/D Input Lines	24
A/D Input Lines (incl. FADC)	24
CAN Nodes	6
Clock Frequency max	200.0 MHz
DMA Channels	16
DSP Functionality	yes
External Bus Interface	no
Fast Flash Programming	no
FlexRay™	yes

Parametrics	SAK-TC234LP-32F200N AC
Floating Point Unit	yes
I/O Operation Voltages	3.3 V
Instruction Set Architecture	TriCore™ v1.6E (32-bit)
Instruction Width ([bits])	32/16
Number of ADC Modules	2.0
On-chip Clock Generation	yes
On-chip Voltage Regulator	yes
Oscillator Watchdog	yes
Program Memory	2.0 MByte
Real Time Clock	yes
SRAM (incl. Cache)	192.0 kByte
Temperature	-40°C - +125 °C
Touch/LED Matrix Control	no
Type of Memory	Flash
Watchdog Timer	yes

Documents

[Application Notes](#)

- [An introduction to MTV Multi-Core Debug Solution \(MCDS\) Trace ViewerEN](#)

01_00 | 2018-04-03 | pdf | 1.1 MB

-
- [EMC and System-ESD Design Guidelines for Board LayoutEN](#)
-

01_00 | 2018-03-15 | pdf | 3 MB

Material Content Sheet *Info*

-
- [MCDS 2018-01-19 11-59-49 MA001654634 PG-TQFP-144-27EN](#)
-

01_00 | 2018-01-30 | pdf | 28 KB

Product Selection Guide

-
- [Power and Sensing Selection Guide 2018EN](#)
-

00_00 | 2018-02-19 | pdf | 23.9 MB

Presentations

-
- [Microcontroller Pocket GuideEN](#)
-

01_00 | 2018-02-22 | pdf | 2.6 MB

Order

Sales Product Name	SAK-TC234LP-32F200N AC
OPN	TC234LP32F200NACKXUMA1
Product Status	active and preferred
Package name	PG-TQFP-144
Completely lead free	yes
Halogen free	yes

Sales Product Name	SAK-TC234LP-32F200N AC
RoHS compliant	yes
Packing Size	1000
Packing Type	TAPE & REEL
Moisture Level	
Moisture Packing	DRY