


THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT  
REV 17579


Restricted to: General Release

USED ON



Left Side

Connector(s): MT-RJ SECURE (No Pins)  
Mode: MM  
Housing Color: Green  
Geom. Spec: 115-1215



Fiber Path

Fiber A - ——— - B  
Fiber B - ——— - A

Notes:


- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).

Right Side


Connector(s): SC-Duplex  
Mode: MM  
Housing Color: Beige  
Geom. Spec: N/A

LOC  
CE  
DIST  
16

|   |     |             |               |           |    |      |  |
|---|-----|-------------|---------------|-----------|----|------|--|
|   |     |             |               |           |    |      |  |
|   | B   | Rev Per EC# | ECR-06-020123 | 9/21/2006 | -  | MK   |  |
| P | LTR | REVISION    | RECORD        | DATE      | DN | APVD |  |



Customer Print

|       |     |                                                                                            |    |                                                                                       |            |            |       |        |     |   |
|-------|-----|--------------------------------------------------------------------------------------------|----|---------------------------------------------------------------------------------------|------------|------------|-------|--------|-----|---|
| DRN   |     | Cable Assy Configurator                                                                    |    | MATERIAL                                                                              |            | HEAT TREAT |       |        |     |   |
| CHK   |     | Michael Kepko                                                                              |    |  |            |            |       |        |     |   |
| APVD  |     | Michael Kepko                                                                              |    |                                                                                       |            |            |       |        |     |   |
| NAME  |     | FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ<br>SECURE (No Pins) to SC-Duplex |    |                                                                                       |            |            |       |        |     |   |
| SCALE | NTS | SIZE                                                                                       | A2 | DRAWING NO                                                                            | C- 6754412 |            | SHEET | 1 of 3 | REV | B |

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC  
CE  
DIST  
16

CAC Customer Layout Rev: D

THIS DRAWING IS A CONTROLLED DOCUMENT.

Restricted to: General Release

USED ON

| Part #      | L (meters)      | L (feet)        | MT-RJ SECURE (No Pins), Green |         | SC-Duplex, Beige |         |
|-------------|-----------------|-----------------|-------------------------------|---------|------------------|---------|
|             |                 |                 | IL (dB)                       | RL (dB) | IL (dB)          | RL (dB) |
| 0-6754412-1 | 0.950 - 1.050   | 3.11 - 3.44     | 0.5                           | 20      | 0.5              | -       |
| 0-6754412-2 | 1.950 - 2.050   | 6.39 - 6.72     | 0.5                           | 20      | 0.5              | -       |
| 0-6754412-3 | 2.950 - 3.050   | 9.67 - 10.00    | 0.5                           | 20      | 0.5              | -       |
| 0-6754412-4 | 3.920 - 4.080   | 12.86 - 13.38   | 0.51                          | 20      | 0.51             | -       |
| 0-6754412-5 | 4.920 - 5.080   | 16.14 - 16.66   | 0.51                          | 20      | 0.51             | -       |
| 0-6754412-6 | 5.920 - 6.080   | 19.42 - 19.94   | 0.51                          | 20      | 0.51             | -       |
| 0-6754412-7 | 6.920 - 7.080   | 22.70 - 23.22   | 0.51                          | 20      | 0.51             | -       |
| 0-6754412-8 | 7.920 - 8.080   | 25.98 - 26.50   | 0.51                          | 20      | 0.51             | -       |
| 0-6754412-9 | 8.850 - 9.150   | 29.03 - 30.01   | 0.51                          | 20      | 0.51             | -       |
| 1-6754412-0 | 9.850 - 10.150  | 32.31 - 33.30   | 0.52                          | 20      | 0.52             | -       |
| 1-6754412-1 | 10.850 - 11.150 | 35.59 - 36.58   | 0.52                          | 20      | 0.52             | -       |
| 1-6754412-2 | 11.850 - 12.150 | 38.87 - 39.86   | 0.52                          | 20      | 0.52             | -       |
| 1-6754412-3 | 12.850 - 13.150 | 42.15 - 43.14   | 0.52                          | 20      | 0.52             | -       |
| 1-6754412-4 | 13.850 - 14.150 | 45.43 - 46.42   | 0.52                          | 20      | 0.52             | -       |
| 1-6754412-5 | 14.850 - 15.150 | 48.72 - 49.70   | 0.52                          | 20      | 0.52             | -       |
| 1-6754412-6 | 15.840 - 16.160 | 51.96 - 53.01   | 0.52                          | 20      | 0.52             | -       |
| 1-6754412-7 | 16.830 - 17.170 | 55.21 - 56.33   | 0.53                          | 20      | 0.53             | -       |
| 1-6754412-8 | 17.820 - 18.180 | 58.46 - 59.64   | 0.53                          | 20      | 0.53             | -       |
| 1-6754412-9 | 18.810 - 19.190 | 61.71 - 62.95   | 0.53                          | 20      | 0.53             | -       |
| 2-6754412-0 | 19.800 - 20.200 | 64.96 - 66.27   | 0.53                          | 20      | 0.53             | -       |
| 2-6754412-1 | 20.790 - 21.210 | 68.20 - 69.58   | 0.53                          | 20      | 0.53             | -       |
| 2-6754412-2 | 21.780 - 22.220 | 71.45 - 72.90   | 0.53                          | 20      | 0.53             | -       |
| 2-6754412-3 | 22.770 - 23.230 | 74.70 - 76.21   | 0.53                          | 20      | 0.53             | -       |
| 2-6754412-4 | 23.760 - 24.240 | 77.95 - 79.52   | 0.54                          | 20      | 0.54             | -       |
| 2-6754412-5 | 24.750 - 25.250 | 81.20 - 82.84   | 0.54                          | 20      | 0.54             | -       |
| 2-6754412-6 | 25.740 - 26.260 | 84.44 - 86.15   | 0.54                          | 20      | 0.54             | -       |
| 2-6754412-7 | 26.730 - 27.270 | 87.69 - 89.46   | 0.54                          | 20      | 0.54             | -       |
| 2-6754412-8 | 27.720 - 28.280 | 90.94 - 92.78   | 0.54                          | 20      | 0.54             | -       |
| 2-6754412-9 | 28.710 - 29.290 | 94.19 - 96.09   | 0.54                          | 20      | 0.54             | -       |
| 3-6754412-0 | 29.700 - 30.300 | 97.44 - 99.40   | 0.55                          | 20      | 0.55             | -       |
| 3-6754412-1 | 30.690 - 31.310 | 100.68 - 102.72 | 0.55                          | 20      | 0.55             | -       |
| 3-6754412-2 | 31.680 - 32.320 | 103.93 - 106.03 | 0.55                          | 20      | 0.55             | -       |
| 3-6754412-3 | 32.670 - 33.330 | 107.18 - 109.35 | 0.55                          | 20      | 0.55             | -       |
| 3-6754412-4 | 33.660 - 34.340 | 110.43 - 112.66 | 0.55                          | 20      | 0.55             | -       |
| 3-6754412-5 | 34.650 - 35.350 | 113.68 - 115.97 | 0.55                          | 20      | 0.55             | -       |
| 3-6754412-6 | 35.640 - 36.360 | 116.92 - 119.29 | 0.55                          | 20      | 0.55             | -       |
| 3-6754412-7 | 36.630 - 37.370 | 120.17 - 122.60 | 0.56                          | 20      | 0.56             | -       |
| 3-6754412-8 | 37.620 - 38.380 | 123.42 - 125.91 | 0.56                          | 20      | 0.56             | -       |
| 3-6754412-9 | 38.610 - 39.390 | 126.67 - 129.23 | 0.56                          | 20      | 0.56             | -       |
| 4-6754412-0 | 39.600 - 40.400 | 129.92 - 132.54 | 0.56                          | 20      | 0.56             | -       |
| 5-6754412-0 | 49.500 - 50.500 | 162.40 - 165.68 | 0.58                          | 20      | 0.58             | -       |

| Qty | U of M | Description                                            | Item No. |
|-----|--------|--------------------------------------------------------|----------|
| 1   | piece  | DUST COVER, MT-RJ                                      | 1        |
| 1   | piece  | SPRING, MT-RJ, 3.8 DESIGN                              | 2        |
| 1   | piece  | PIN KEEPER, 3.8MM                                      | 3        |
| 1   | piece  | MT-RJ, SPRING PUSH, UNIVERSAL                          | 4        |
| 1   | piece  | CRIMP EYELET, MT-RJ                                    | 5        |
| 1   | piece  | MT-RJ Keyed Connector Housing - Green                  | 6        |
| 2   | piece  | LC, SC, FC Straight Boot, Beige                        | 7        |
| 1   | piece  | MT-RJ FERRULE, THERMOPLAST,MM                          | 8        |
| 2   | piece  | SC Simplex Housing, Beige                              | 9        |
| 2   | piece  | 2.5mm ferrule cover                                    | 10       |
| AR  | meter  | 2 fiber, XG-50/125, 1.8mm, Twinzip, Aqua, OFNR (Riser) | 11       |
| 1   | piece  | MT-RJ TwinZip Bend Limiting Boot, Beige                | 12       |
| 2   | piece  | SC Duplex Clip                                         | 13       |
| 2   | piece  | Eyelet/Shrink tube assembly - White                    | 14       |
| 2   | piece  | CONN SUBASSY, MM, SC 1.6MM                             | 15       |
| 2   | piece  | Trace Label                                            | 16       |

|   |             |                 |           |     |      |
|---|-------------|-----------------|-----------|-----|------|
|   |             |                 |           |     |      |
|   |             |                 |           |     |      |
| B | Rev Per EC# | ECR-06-020123   | 8/21/2006 | -   | MK   |
| P | LTR         | REVISION RECORD | DATE      | DIN | APVD |

DIMENSIONS:  
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 P.L.C. ±  
1 P.L.C. ±  
2 P.L.C. ±  
3 P.L.C. ±  
4 P.L.C. ±


Customer Print

|       |                                                                                         |                                                                |    |            |            |
|-------|-----------------------------------------------------------------------------------------|----------------------------------------------------------------|----|------------|------------|
| DIN   | Cable Assy Configurator                                                                 | MATERIAL                                                       | -  | HEAT TREAT | -          |
| CHK   | Michael Kepko                                                                           | <b>AMP</b> Tyco Electronics, Inc.<br>Harrisburg, PA 17105-3608 |    |            |            |
| APVD  | Michael Kepko                                                                           |                                                                |    |            |            |
| NAME  | FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex |                                                                |    |            |            |
| SCALE | NTS                                                                                     | SIZE                                                           | A2 | DRAWING NO | C- 6754412 |
| SHEET | 2 of 3                                                                                  |                                                                |    | REV        | B          |

8 7 6 5 4 3 2 1

## Label 1


Per specification 107-1645-1



This label is used on all lengths on this drawing.

## Label 2

Per specification 107-1645-1



This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC  
CE  
DIST  
16

CAC Customer Layout Rev: D

|   |             |                 |           |     |      |  |  |
|---|-------------|-----------------|-----------|-----|------|--|--|
|   |             |                 |           |     |      |  |  |
|   |             |                 |           |     |      |  |  |
| B | Rev Per EC# | ECR-06-020123   | 9/21/2006 | -   | MK   |  |  |
| P | LTR         | REVISION RECORD | DATE      | DIN | APVD |  |  |

| DIMENSIONS: | TOLERANCES UNLESS OTHERWISE SPECIFIED: |
|-------------|----------------------------------------|
| meters      |                                        |
|             | 0 P.L.C. ±                             |
|             | 1 P.L.C. ±                             |
|             | 2 P.L.C. ±                             |
|             | 3 P.L.C. ±                             |
|             | 4 P.L.C. ±                             |

Customer Print

|                                                                                                 |               |                                                                                       |              |     |
|-------------------------------------------------------------------------------------------------|---------------|---------------------------------------------------------------------------------------|--------------|-----|
| DIN Cable Assy Configurator                                                                     |               | MATERIAL -                                                                            | HEAT TREAT - |     |
| OK                                                                                              | Michael Kepko |  |              |     |
| APVD                                                                                            | Michael Kepko |                                                                                       |              |     |
| NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ<br>SECURE (No Pins) to SC-Duplex |               |                                                                                       |              |     |
| SCALE                                                                                           | SIZE          | DRAWING NO.                                                                           | SHEET        | REV |
| NTS                                                                                             | A2            | C- 6754412                                                                            | 3 of 3       | B   |

8

7

6

5

4

3

2

1