



A cross-sectional diagram of a cable. On the left, a thick black outer jacket is shown. To its right, a grey braided shield is visible. Further right, five individual conductors are shown, each with a different color: red, yellow, green, blue, and black. The conductors are arranged in a row. The entire diagram is set against a light orange background with a thin orange border.

- FIT-600: highly flexible, cross-linked elastomer
- FIT-400: temperature/chemical resistant FEP

14 AWG (2.08 mm²)					
Stranding: 41/30 (41 x 0.25 mm) Insulation thickness: 0.032 (0.81 mm)					
Part No.	Conductors	Nominal Diameter		Jacket Thickness	
		Inch	mm	Inch	mm
45442	2	0.390	9.91	0.055	1.40
45443	3	0.412	10.46	0.055	1.40
45444	4	0.448	11.38	0.055	1.40
45445	5	0.489	12.42	0.055	1.40
45447	7	0.551	14.00	0.065	1.65