





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K	REVISED PER ECO-12-016930	05OCT12	KH	SM



RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD

		.700	17.78
.060	1.52	.468	11.89
.051	1.30	.450	11.43
.046	1.17	.425	10.80
.045	1.14	.412	7.92
.030	0.76	.300	7.62
.015	0.38	.180	4.57
.012	0.30	.175	4.45
.010	0.25	.156	3.96
.008	0.20	.125	3.18
.005	0.13	.078	1.98
.003	0.08	.068	1.73
.001	0.03	.063	1.60
[IN]	MM	[IN]	MM

CONVERSION TABLE

643960-1 SHOWN

OBSOLETE	3	643960-2
	2	643960-1
	POST NUMBER OMITTED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN S. HOOVER	07NOV02	 TE Connectivity
		CHK D. BOSSI	07NOV02	
DIMENSIONS:		APVD D. BOSSI	07NOV02	
TOLERANCES UNLESS OTHERWISE SPECIFIED:				
INCHES				NAME MTA-156 HEADER ASSEMBLY, FRICTION LOCK, STRAIGHT .045 ROUND POST, TIN PLATED, 3 POSITION, OMITTED POST
		PRODUCT SPEC —		
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		APPLICATION SPEC —		
MATERIAL		WEIGHT —		
				SIZE A1
FINISH		CUSTOMER DRAWING		
		CASE CODE 00779		DRAWING NO C-643960
		RESTRICTED TO —		
		SCALE 5:1		SHEET 1 OF 1
		REV K		