





REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₀	RELEASED	3/10/98	<i>[Signature]</i>
02 ₀	MAJOR CHANGES PER ECN 98-0124-5	4/27/98	<i>[Signature]</i>

ELECTRICAL	MECHANICAL	ENVIRONMENTAL	HOUSING CAP		STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204	
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 319.2	Temperature Rating -55°C to +125°C	DIELECTRIC		PTFE FLUOROCARBON PER ASTM-D-1457	N/A	
Frequency Range (GHz) DC to 18	Recommended Mating	Vibration MIL-STD-202, Method 204, Condition D	CENTER CONTACT		BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204	
Volt Rating (VRMS MAX) @ Sea Level 250	Torque 7 to 8 In-Lbs	Shock MIL-STD-202, Method 213, Condition I	COMPONENT		MATERIAL	FINISH	
VSWR N/A	Mating Characteristics:	Thermal Shock MIL-STD-202, Method 107, Condition B, Except High Temp Shall Be +115°C	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON		DRAWN BY <i>[Signature]</i> DATE 3/10/98		
Insertion Loss (dB MAX) N/A	Insertion (MAX Lbs) 3	Moisture Resistance MIL-STD-202, Method 106	FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		CHECKED BY <i>[Signature]</i>		
RF Leakage (dB MIN) N/A	Withdrawal (MIN Oz) 1	Corrosion - MIL-STD-202, Method 106, No Measurements at High Humidity	APPD BY <i>[Signature]</i> 3/10/98		M/A-COM a Division of AMP Incorporated 140 Fourth Avenue Waltham, MA 02154-7577		
Corona, 70,000 Ft (VRMS MIN) 190	Force to Engage and Disengage (In-Lbs MAX) 2		These drawings and specifications are the property of M/A-COM Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		AMP M/A-COM		
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750	Center Contact Captivation		USE ASSY PROCEDURE		TITLE OSSM RIGHT ANGLE PRINTED WIRING BOARD JACK STRAIGHT TERMINAL		
Contact Resistance (Milliohms MAX) Center Contact 2.0 Outer Contact 2.0	Axial (Lbs) 6 Radial (In-Oz) 4		NO. AP. N/A		SIZE B	CODE IDENT NO. 26805	1064-5005-00
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500	Weight (Grams) TBD				SCALE 5:1		REV 020
LR.(Megohms MIN) 5000							SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1064-5005-00](#)