






FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



mat'l. code NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC				
ltr	ecn	nol	dr	date	tolerances unless otherwise specified					title				
E	v40285	PCP		1/20/94	angles	linear	.XX ±.01/.3			INCH/MM				
F	v40941	PCP		6/01/94			.XXX ±.005/.13							
G	v82253	HTB		12/28/98			.0±2°			.XXXX ±.0020/.051				
H	v00271	JWS		1/31/00	dr	D. SHEAFFER			3/14/91			scale 1:1		
J	V05-0758	DAI		9/12/05	enrg	S. CLARK			3/14/91					
K	V05-1039	DAI		11/11/05	chr	S. CLARK			3/14/91			FCI		
L	M06-0261	AEA		7/08/06	appd	S. CLARK			3/14/91					
sheet index		revision sheet		L	L	L	L	L						
				1	2	3	4							



form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100/2.54 GRID
UNLESS OTHERWISE SPECIFIED)

mat'l. code NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified	scale 1:1 FCI	title 4 ROW VERTICAL HEADER W/PRESS FIT PINS, 1 G.P.
L					angles linear .XX ±.01/.3		
					.XXX ±.005/.13		
					0°±2' .XXX ±.0020/.051		
			dr	D. SHEAFFER	3/14/91		dwg no
			enr	S. CLARK	3/14/91		sheet 2 of 4 size
			chr	S. CLARK	3/14/91		50010 A3
			appd	S. CLARK	3/14/91		type Product Customer Drawing
sheet index	revision sheet						

form: A3

PDM: Rev:L STATUS: **Released** Printed: May 13, 2011

Copyright FCI

PRODUCT NO.	NO. OF POSITIONS SEE NOTE 2	TAIL LENGTH ±.015/0.38	TERMINAL PLATING	MATING LENGTH
50010 -1YYYA	YYY	.177/4.50	30μ"/0.76μ GOLD	.220[5.59]
50010 -1YYYC	YYY	.533/13.54	30μ"/0.76μ GOLD	
50010 -1YYYD	YYY	.733/18.62	30μ"/0.76μ GOLD	
50010 -1YYYG	YYY	.250/6.35	30μ"/0.76μ GOLD	
50010 -1YYYL	YYY	.188/4.78	30μ"/0.76μ GOLD	
50010 -1YYYP	YYY	.470/11.94	30μ"/0.76μ GOLD	
50010 -3YYYA	YYY	.177/4.50	50μ"/1.27μ GOLD	
50010 -3YYYC	YYY	.533/13.54	50μ"/1.27μ GOLD	
50010 -3YYYD	YYY	.733/18.62	50μ"/1.27μ GOLD	
50010 -3YYYG	YYY	.250/6.35	50μ"/1.27μ GOLD	
50010 -3YYYL	YYY	.188/4.78	50μ"/1.27μ GOLD	
50010 -3YYYP	YYY	.470/11.94	50μ"/1.27μ GOLD	
50010 -5YYYA	YYY	.177/4.50	30μ"/0.76μ GXT	
50010 -5YYYALF	YYY	.177/4.50	30μ"/0.76μ GXT	
50010 -5YYYC	YYY	.533/13.54	30μ"/0.76μ GXT	
50010 -5YYYCLF	YYY	.533/13.54	30μ"/0.76μ GXT	
50010 -5YYYD	YYY	.733/18.62	30μ"/0.76μ GXT	
50010 -5YYYDLF	YYY	.733/18.62	30μ"/0.76μ GXT	
50010 -5YYYG	YYY	.250/6.35	30μ"/0.76μ GXT	
50010 -5YYYGLF	YYY	.250/6.35	30μ"/0.76μ GXT	
50010 -5YYYL	YYY	.188/4.78	30μ"/0.76μ GXT	
50010 -5YYYLLF	YYY	.188/4.78	30μ"/0.76μ GXT	
50010 -5YYYP	YYY	.470/11.94	30μ"/0.76μ GXT	
50010 -5YYYP LF	YYY	.470/11.94	30μ"/0.76μ GXT	.220[5.59]
50010 -XX009	368	SEE SHEET 3	30μ"/0.76μ GXT	SEE SHEET 3
50010 -XX009LF	368	SEE SHEET 3	30μ"/0.76μ GXT	SEE SHEET 3

NOTES:

①. PRODUCT NUMBERING CODE:

50010 - X YYY Z LF

LEAD FREE (OPTIONAL), SEE NOTE 9
TAIL LENGTH, SEE TABLE
NO. OF POSITIONS, SEE NOTE 2
PLATING, SEE TABLE
BASE NUMBER

PRODUCT NUMBERING CODE FOR SELECT LOAD:

50010 - XXYYY LF

LEAD FREE (OPTIONAL) SEE NOTE 9
SEQUENCE NUMBER
ALWAYS 'XX'
BASE NUMBER

② THIS PRODUCT IS CONFIGURED IN SIZES OF 20 thru 122 COLUMNS IN INCREMENTS OF TWO.
i.e.: 20,22,24,26,.....118,120,122.

③ HOUSING MATERIAL: GLASS AND MINERAL FILLED
HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER
UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS BRONZE

④ LENGTH FORMULAS
DIM "A" .100/2.54 x NO. OF COLUMNS +1.05/26.7
DIM "B" .100/2.54 x NO. OF COLUMNS +.750/19.05
DIM "C" .100/2.54 x NO. OF COLUMNS DIVIDED BY 2 -.100/2.54

⑤ .0453/1.151 DRILLED HOLE PLATED WITH .0003/.007 MIN.
SnPb OVER .001/.03 to .003/.08 Cu. PLATING TO ACHIEVE
A .040±.003/1.02±.08 HOLE.

⑥ TO ASSURE PROPER INSTALLATION: TOOLING, AS
SPECIFIED IN INSTRUCTION MANUAL 155915-001 MUST
BE USED. PIN MATING LENGTH WILL BE ±.002/.05
AFTER INSTALLATION.

⑦ COMPANY NAME, PART NUMBER AND LOT CODE TO APPEAR ON
THIS SURFACE PER BUS-12-108.

⑧ REFERENCE 50808 FOR F.M.L.B. AVAILABLE OPTIONS
AND WORKSHEET.

⑨ THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

10. THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE
FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

mat'l. code NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family HPC	
ltr	ecn	no	dr	date	tolerances unless otherwise specified			title		4 ROW VERTICAL HEADER	
L					angles	linear	.XX ±.01/.3	INCH/MM		W/PRESS FIT PINS, 1 G.P.	
					0°±2°		.XXX ±.005/.13	scale 1:1		dwg no	
					dr	D. SHEAFFER	3/14/91	FCI		sheet 4 of 4 size	
					enrg	S. CLARK	3/14/91			50010 A3	
					chr	S. CLARK	3/14/91			type	
					appd	S. CLARK	3/14/91			Product Customer Drawing	
sheet index	revision	sheet									