



SPECIFICATION FOR APPROVAL

Customer_____

Description_____ DC FAN

Part No. _____ REV. _____

Delta Model No. PFR1212DHE-F00 REV. 00

Sample Issue No._____

Sample Issue Date NOV.04.2011

PLEASE SEND ONE COPY OF THIS SPECIFICAITON BACK
AFTER YOU SIGNED APPROVAL FOR PRODUCTION PRE-
ARRANGMENT.

APPROVED BY:_____

DATE :_____

DELTA ELECTRONICS, INC.

TAOYUAN PLANT

252, SHANG YING ROAD, KUEI SAN INDUSTRIAL ZONE TAOYUAN
SHIEN, TAIWAN, R.O.C.

TEL:886-(0)3-3591968

FAX:886-(0)3-3591991

DELTA ELECTRONICS, INC.
252, SHANG YING ROAD, KUEI SAN
TAOYUAN HSIEN 333, TAIWAN, R. O. C.

TEL : 886-(0)3-3591968
FAX : 886-(0)3-3591991

SPECIFICATION FOR APPROVAL

Customer:

Description: DC FAN

Customer P/N: REV:

Delta Model NO.: PFR1212DHE-FO0

Sample Rev: 00 Issue No:

Sample Issue Date: Quantity:

1. SCOPE:

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE DC BRUSHLESS AXIAL FLOW FAN. THE FAN MOTOR IS WITH SINGAL PHASE AND EIGHT POLES.

2. CHARACTERS:

ITEM	DESCRIPTION
RATED VOLTAGE	12 VDC
OPERATION VOLTAGE	8.0 - 13.2 VDC
INPUT CURRENT	3.7 (MAX. 5.2) A
INPUT POWER	44.40 (MAX. 62.4) W
SPEED	7400 R.P.M. (REF.)
MAX. AIR FLOW (AT ZERO STATIC PRESSURE)	7.202 (MIN. 6.482) M ³ /MIN. 254.349(MIN. 228.914) CFM
MAX.AIR PRESSURE (AT ZERO AIRFLOW)	36.513 (MIN. 29.575) mmH ₂ O 1.438(MIN. 1.164) inchH ₂ O
ACOUSTICAL NOISE (AVG.)	68.5 (MAX. 72.5) dB-A
INSULATION TYPE	UL: CLASS A


(continued)

PART NO:

DELTA MODEL: PFR1212DHE-F00

INSULATION STRENGTH	10 MEG OHM MIN. AT 500 VDC (BETWEEN FRAME AND (+) TERMINAL)	
DIELECTRIC STRENGTH	5 mA MAX. AT 500 VAC 60 Hz ONE MINUTE, (BETWEEN FRAME AND (+) TERMINAL)	
EXTERNAL COVER	OPEN TYPE	
LIFE EXPECTANCE	70,000 HOURS CONTINUOUS OPERATION AT 40 °C WITH 15 ~ 65 %RH.	
ROTATION	CLOCKWISE VIEW FROM NAME PLATE SIDE	
OVER CURRENT PROTECTION	THE FAN WILL SHUT DOWN WHEN THE CURRENT IS ABNORMAL AND WILL RESTART AFTER 10 SECONDS	
STARTING PROTECTION	START AT LOW SPEED , AFTER 10 SEC RUNNING AT FULL SPEED	
LEAD WIRE	UL 1430 AWG #22 BLACK WIRE NEGATIVE(-) RED WIRE POSITIVE(+)	UL 1007 AWG #24 BLUE WIRE (F00)

NOTES: 1. ALL READINGS ARE MEASURED AFTER STABLY WARMING UP
THROUGH 10 MINUTES.
2. THE VALUES WRITTEN IN PARENS , (), ARE LIMITED SPEC.
3. ACOUSTICAL NOISE MEASURING CONDITION:



NOISE IS MEASURED AT RATED VOLTAGE IN FREE AIR IN ANECHOIC
CHAMBER WITH B & K SOUND LEVEL METER WITH MICROPHONE AT
A DISTANCE OF ONE METER FROM THE FAN INTAKE.

PART NO:

DELTA MODEL: PFR1212DHE-F00

3. MECHANICAL:

3-1. DIMENSIONS -----	SEE DIMENSIONS DRAWING
3-2. FRAME -----	PLASTIC UL: 94V-0
3-3. IMPELLER -----	PLASTIC UL: 94V-0
3-4. BEARING SYSTEM -----	TWO BALL BEARINGS
3-5. WEIGHT -----	410 GRAMS

4. ENVIRONMENTAL:

4-1. OPERATING TEMPERATURE -----	-10 TO +70 DEGREE C
4-2. STORAGE TEMPERATURE -----	-40 TO +75 DEGREE C
4-3. OPERATING HUMIDITY -----	5 TO 90 % RH
4-4. STORAGE HUMIDITY -----	5 TO 95 % RH

5. PROTECTION:

5-1. LOCKED ROTOR PROTECTION

IMPEDANCE OF MOTOR WINDING PROTECTS MOTOR FROM FIRE IN 96 HOURS OF LOCKED ROTOR CONDITION AT THE RATED VOLTAGE.

5-2. POLARITY PROTECTION

BE CAPABLE OF WITHSTANDING IF REVERSE CONNECTION FOR POSITIVE AND NEGATIVE LEADS.

6. RE OZONE DEPLETING SUBSTANCES:

6-1. NO CONTAINING PBBs, PBB0s, CFCs, PBBEs, PBDPEs AND HCFCs.

7. PRODUCTION LOCATION

7-1. PRODUCTS WILL BE PRODUCED IN CHINA OR THAILAND OR TAIWAN.

PART NO:

DELTA MODEL: PFR1212DHE-FOO


8. BASIC RELIABILITY REQUIREMENT:

8-1. THERMAL CYCLING	LOW TEMPERATURE: -40°C HIGH TEMPERATURE: +85°C SOAK TIME: 30 MINUTES TRANSITION TIME : < 5 MIN NUMBER OF CYCLES : 10												
8-2. HUMIDITY EXPOSURE	TEMPERATURE: 60°C HUMIDITY: 90-95% DURATION: 10 DAYS THREE PCS ARE IN OPERATION (RATED VOLTAGE)												
8-3. VIBRATION	ORIENTATION: X, Y, Z POWER: NON-OPERATING VIBRATION LEVEL: OVERALL gRMS=3.2 <table> <thead> <tr> <th>FREQUENCY(Hz)</th> <th>PSD(G^2/Hz)</th> </tr> </thead> <tbody> <tr> <td>10</td> <td>0.040</td> </tr> <tr> <td>20</td> <td>0.100</td> </tr> <tr> <td>40</td> <td>0.100</td> </tr> <tr> <td>800</td> <td>0.002</td> </tr> <tr> <td>1000</td> <td>0.002</td> </tr> </tbody> </table> DURATION: 2 HOURS ON EACH ORIENTATION SAMPLE CONDITION : NON-PACKING , NON-OPERATION	FREQUENCY(Hz)	PSD(G^2/Hz)	10	0.040	20	0.100	40	0.100	800	0.002	1000	0.002
FREQUENCY(Hz)	PSD(G^2/Hz)												
10	0.040												
20	0.100												
40	0.100												
800	0.002												
1000	0.002												
8-4. MECHANICAL SHOCK	PLUSE SHAPE : HALF-SINE ORIENTATION: X , -X , Y , -Y , Z , -Z DURATION : 6 ms PEAK ACCELERATION: 100G PULSE: 11 ms HALF-SINE WAVE 3 SHOCKS EACH ORIENTATION(TOTAL 18 SHOCKS)												
8-5. LIFE	TEMPERATURE: MAX , OPERATING TEMPERATURE POWER: OPERATING DURATION: 1000 HOURS MIN.												

PART NO:

DELTA MODEL: PFR1212DHE-F00

9. P & Q CURVE:




* TEST CONDITION: INPUT VOLTAGE ----- OPERATION VOLTAGE
TEMPERATURE ----- ROOM TEMPERATURE
HUMIDITY ----- 65%RH

PART NO:

DELTA MODEL: PFR1212DHE-F00

10. DIMENSION DRAWING:

LABEL:



NOTE: 1. LEAD WIRE UL1430 AWG#22

RED WIRE POSITIVE(+)

BLACK WIRE NEGATIVE(-)

LEAD WIRE UL1007 AWG#24

BLUE WIRE FREQUENCY(-F00)

UNIT: MM(INCH)


2. THIS PRODUCT IS RoHS COMPLIANT

PART NO:

DELTA MODEL: PFR1212DHE-F00

11. FREQUENCY GENERATOR (FG) SIGNAL:

1. OUTPUT CIRCUIT - OPEN COLLECTOR MODE:



CAUTION:


THE LEAD WIRE OF FG SIGNAL CAN NOT TOUCH
THE LEAD WIRE OF POSITIVE OR NEGATIVE.

2. SPECIFICATION:


V_{CE} (sat)=0.5V MAX. $V_{FG}=13.2V$ MAX.

$I_c = 5\text{mA}$ MAX. $R \geq V_{FG}/I_c$

3. FREQUENCY GENERATOR WAVEFORM:



FAN RUNNING FOR 8 POLES



$*VOLTAGE LEVEL AFTER BLADE LOCKED$

$*8$ POLES



Application Notice

1. Delta will not guarantee the performance of the products if the application condition falls outside the parameters set forth in the specification.
2. A written request should be submitted to Delta prior to approval if deviation from this specification is required.
3. Please exercise caution when handling fans. Damage may be caused when pressure is applied to the impeller, if the fans are handled by the lead wires, or if the fan was hard-dropped to the production floor.
4. Except as pertains to some special designs, there is no guarantee that the products will be free from any such safety problems or failures as caused by the introduction of powder, droplets of water or encroachment of insect into the hub.
5. The above-mentioned conditions are representative of some unique examples and viewed as the first point of reference prior to all other information.
6. It is very important to establish the correct polarity before connecting the fan to the power source. Positive (+) and Negative (-). Damage may be caused to the fans if connection is with reverse polarity, if there is no foolproof method to protect against such error specifically mentioned in this spec.
7. Delta fans without special protection are not suitable where any corrosive fluids are introduced to their environment.
8. Please ensure all fans are stored according to the storage temperature limits specified. Do not store fans in a high humidity environment. We highly recommend performance testing is conducted before shipping, if the fans have been stored over 6 months.
9. Not all fans are provided with the Lock Rotor Protection feature. If you impair the rotation of the impeller for the fans that do not have this function, the performance of those fans will lead to failure.
10. Please be cautious when mounting the fan. Incorrect mounting of fans may cause excess resonance, vibration and subsequent noise.
11. It is important to consider safety when testing the fans. A suitable fan guard should be fitted to the fan to guard against any potential for personal injury.
12. Except where specifically stated, all tests are carried out at room (ambient) temperature and relative humidity conditions of 25°C, 65% RH. The test value is only for fan performance itself.
13. Be certain to connect an “4.7µF or greater” capacitor to the fan externally when the application calls for using multiple fans in parallel, to avoid any unstable power.