


- 1.5KV Isolation •
- Recommended for CS6152/54, DS185/86/87, ATT7288/90 •
- Meet CCITT I.430 requirements with proper termination •
- Robust construction allows for most severe soldering processes •

Electrical Parameters @ 25° C

Primary Inductance (mH Min.)		Interwinding Capacitance (pF Max.)		Leakage Inductance (μH Max.)		Primary DCR (Ω Max.)		Secondary DCR (Ω Max.)		Hipot (Vrms)
@ 100 KHz, 0.1 Vrms		@ 100 KHz, 0.1 Vrms		@ 100 KHz, 0.1 Vrms				@ 200 Vdc		
T1	T2	T1	T2	T1	T2	T1	T2	T1	T2	
1.6	1.6	60	50	1.0	0.8	1.5	1.5	2.0	1.7	1500

Schematic



Dimensions

Dim.	(Inches)			(Millimeters)		
	Min.	Max.	Nom.	Min.	Max.	Nom.
A	.655	.675	.665	16.64	17.15	16.89
B	.380	.400	.390	9.65	10.16	9.91
C	.320	.340	.330	8.13	8.64	8.38
D	---	---	.500	---	---	12.70
E	.010	.015	.013	.254	.381	.330
F	---	---	.100	---	---	2.54
G	---	---	.600	---	---	13.46
H	.018	.022	.020	.457	.559	.508
I	.008	.012	.010	.203	.305	.254
J	.075	.095	.085	1.91	2.41	2.16
K	0°	8°	---	0°	8°	---
L	.040	.060	.050	1.02	1.52	1.27
M	---	---	.030	---	---	.762
N	---	---	.100	---	---	2.54
P	---	---	.120	---	---	3.05
Q	---	---	.640	---	---	16.26

