


Low Signal Relay

G5V-2

- Suitable for handling low signals in computer peripherals, telecommunications and security equipment.
- Capable of switching loads up to 2 A.
- Conforms to FCC part 68 1500 V surge withstand.
- Reliable bifurcated crossbar contacts.
- Fully-sealed construction.
- RoHS Compliant.



Ordering Information

To Order: Select the part number and add the desired coil voltage rating (e.g., G5V-2-DC12).

Type	Contact form	Construction	Model
Standard	DPDT	Fully-sealed	G5V-2
High-sensitivity			G5V-2-H
Ultra-sensitive			G5V-2-H1

Specifications

■ Contact Data

Item	Standard and high-sensitivity	Ultra-sensitive
Load	Resistive load (p.f. = 1)	
Rated load	0.50 A at 125 VAC 2 A at 30 VDC	0.5 A at 125 VAC 1 A at 24 VDC
Contact material	Ag (Au clad)	
Carry current	2 A	
Max. operating voltage	125 VAC 125 VDC	
Max. operating current	2 A	1 A
Max. switching capacity	62.5 VA 60W	62.5 VA 24W
Min. permissible load	10 μ A, 10 mVDC	

■ Coil Data

Standard Type

Rated voltage (VDC)	Rated current (mA)	Coil resistance (Ω)	Coil inductance (Ref. value) (H)		Pick-up voltage	Dropout voltage	Maximum voltage	Power consumption (mW)
			Armature OFF	Armature ON				
3	166.70	18	0.04	0.05	75% max.	5% min.	120% max. at 65°C (149°F)	Approx. 500
5	100	50	0.09	0.11				
6	83.30	72	0.16	0.19				
9	55.60	162	0.31	0.49				
12	41.70	288	0.47	0.74				
24	20.80	1,152	1.98	2.68				
48	12	4,000	--	--			110% max. at 60°C (140°F)	Approx. 580

High-sensitivity Type

Rated voltage (VDC)	Rated current (mA)	Coil resistance (Ω)	Coil inductance (Ref. value) (H)		Pick-up voltage	Dropout voltage	Maximum voltage	Power consumption (mW)
			Armature OFF	Armature ON				
3	120	25	0.04	0.07	75% max.	5% min.	120% max. at 70°C (158°F)	Approx. 360
5	72	70	0.12	0.19				
6	60	100	0.18	0.29				
9	40	225	0.40	0.62				
12	30	400	0.75	1.18				
24	15	1,600	3.16	4.81				
48	7.5	6,400	--	--			110% max. at 70°C (158°F)	

Ultra-sensitive Type

Rated voltage (VDC)	Rated current (mA)	Coil resistance (Ω)	Coil inductance (Ref. value) (H)		Pick-up voltage	Dropout voltage	Maximum voltage	Power consumption (mW)
			Armature OFF	Armature ON				
3	50	60	0.18	0.26	75% max.	5% min.	150% max. at 70°C (158°F)	Approx. 150
5	30	166.7	0.46	0.47				
6	25	240	0.70	0.97				
9	16.70	540	1.67	2.33				
12	12.50	960	2.90	3.99				
24	8.30	2,880	6.72	9.27				
48	6.25	7,680	20.10	26.70				Approx. 300

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C (73°F) with a tolerance of $\pm 10\%$.

2. The operating characteristics are measured at a coil temperature of 23°C (73°F).


■ Characteristics

Contact resistance		50 mΩ max. G5V-2, G5V-2-H, 100 mΩ max. G5V-2-H1
Operate time		7 ms max. (mean value: approx. 3.5 ms)
Release time		3 ms max. (mean value: approx. 0.8 ms)
Bounce time	Operate	Mean value: approx. 0.5 ms
	Release	Mean value: approx. 3.5 ms
Operating frequency	Mechanical	36,000 operations/hour
	Electrical	1,800 operations/hour (under rated load)
Insulation resistance		1,000 MΩ min (at 500 VDC)
Dielectric strength		1,000 VAC, 50/60 Hz for 1 minute between coil and contacts
		1,000 VAC, 50/60 Hz for 1 minute between contacts of different poles
		750 VAC, 50/60 Hz for 1 minute between contacts of same poles
		(500 VAC, 50/60 Hz for 1 minute between contacts of same poles for ultra-sensitive type)
Surge withstand voltage		1,500 V 10 X 160 μs (conforms to part 68 of FCC rules)
Vibration	Mechanical durability	10 to 55 Hz, 1.50 mm (0.59 in) double amplitude
	Malfunction durability	
Shock	Mechanical durability	1,000 m/s ² (approx. 100 G)
	Malfunction durability	200 m/s ² (approx. 20 G), 100 m/s ² (approx. 10 G) for ultra-sensitive type
Ambient temperature	Operating/storage	-25° to 70°C (-13° to 158°F)
Humidity		35% to 85% RH
Service life	Mechanical	15 million operations min. (at operating frequency of 36,000 operations/hour)
	Electrical	See "Characteristic Data"
Weight		6 g (0.21 oz)


Note: Data shown are of initial value.

■ Characteristic Data


Maximum Switching Capacity



Electrical Service Life



Ambient Temperature vs. Maximum Voltage




Dimensions


Unit: mm (inch)

Relays


Fully-sealed



Terminal arrangement/Internal (bottom view)



Mounting holes (bottom view)



- Note:** 1. and indicate mounting orientation marks.
2. A tolerance of ± 0.10 (0.004) applies to the above dimensions.

Approvals

UL (File No. E41515)/CSA (File No. LR24825)

Type	Contact form	Coil rating	Contact ratings
G5V-2 G5V-2-H	DPDT	3 to 48 VDC	0.6 A, 125 VAC
		3 to 24 VDC	0.6 A, 110 VDC 2.0 A, 30 VDC
G5V-2-H1		3 to 48 VDC	0.5 A, 125 VAC 0.6 A, 125 VAC 0.2 A, 110 VDC 0.6 A, 110 VDC 1.0 A, 24 VDC

- Note:** 1. The rated values approved by each of the safety standards may be different from the performance characteristics individually defined in this catalog.
2. In the interest of product improvement, specifications are subject to change.
3. UL1950 recognition.

Terms and Conditions of Sale

1. Offer: Acceptance. These terms and conditions (these "Terms") are deemed part of all quotations, acknowledgments, invoices, purchase orders and other documents, whether electronic or in writi

Certain Precautions on Specifications and Use

1. **Suitability for Use.** Seller shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in Buyer's application or use of the Product. At Buyer's request, Seller will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given:
 - (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document.
 - (ii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
 - (iii) Use in consumer products or any use in significant quantities.
 - (iv) Systems, machines and equipment that could present a risk to life or property. Please know and observe all prohibitions of use applicable to this product.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.
2. **Programmable Products.** Seller shall not be responsible for the user's programming of a programmable product, or any consequence thereof.
3. **Performance Data.** Performance data given in this publication is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Seller's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to Seller's Warranty and Limitations of Liability.
4. **Change in Specifications.** Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Seller representative at any time to confirm actual specifications of purchased Product.
5. **Errors and Omissions.** The information in this publication has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors, or omissions.
6. **RoHS Compliance.** Where indicated, our products currently comply, to the best of our knowledge as of the date of this publication, with the requirements of the European Union's Directive on the Restriction of certain Hazardous Substances ("RoHS"), although the requirements of RoHS do not take effect until July 2006. These requirements may be subject to change. Please consult our website for current information.

Complete "Terms and Conditions of Sale" for product purchase and use are on Omron's website at www.components.omron.com – under the "About Us" tab, in the Legal Matters section.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON CANADA, INC.

885 Milner Avenue
Toronto, Ontario M1B 5V8

416-286-6465

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Canada - <http://www.omron.ca>