

MATERIALS AND FINISHES






BODY ZINC ALLOY
PLATED NICKEL (70 MICROINCHES MIN)

CENTER CONTACT BRASS
PLATED GOLD (10 MICROINCHES MIN)

INSULATOR TEFLON

OUTER CONTACT BERYLLIUM COPPER
PLATED PLATED GOLD (10 MICROINCHES MIN)

CRIMP DIE: 4.08(.161) HEX



PART # 73415-5190

- UNLESS OTHERWISE SPECIFIED DIMS
ARE MILLIMETERS AND ANGLES ARE DEGREES.
- ∇ ALL OVER.
 - NO CHATTER OR NON-UNIFORM
SURFACE FINISH ALLOWED.
 - PARTS TO BE FREE OF BURRS
& SHARP EDGES 0.13(.005) MAX BREAK.
 - EXTERNAL THREADS TO BE ROLLED
OR SINGLE POINT.
 - DIAMETERS TO BE CONCENTRIC
WITHIN 0.08(.003) TIR.

CHG: NEW RELEASE EC NO: URF2005-0752 DRAWN: FLAHERT CHKD: SHAH APPR: WILNER A	2004/10/28 2004/10/28 2004/10/28 DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY	DATE	TITLE MCX PLUG, R/A FOR RG179 75 OHMS, EWR-2625 MCX-PC		
			4 PLACES	± .---	± .---	TEF	2004/10/27			
			3 PLACES	± .---	± .---	CHECKED BY	DATE			
			2 PLACES	± .---	± .---	SSS	2004/10/27			
			1 PLACE	± .---	± .---	APPROVED BY	DATE			
			ANGULAR ± 2 °		JDW	2004/10/27	MOLEX INCORPORATED			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. 734155190			DOCUMENT NO. SD-73415-519		SHEET NO. 1 OF 1
					SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				