

14.22mm (0.56") DUAL DIGIT NUMERIC DISPLAY


XDUR14A2



SUN LED

Email : sales@us.sunled.com

Web Site : www.sunled.com




Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.

Operating Characteristics (T _A =25°C)		UR (GaAsP/GaP)	Unit
Forward voltage (typ.) (I _F =10mA)	V _F	1.9	V
Forward voltage (max.) (I _F =10mA)	V _F	2.5	V
Reverse current (V _R =5V)	I _R	10	uA
Wavelength at peak emission (I _F =10mA)	λ _{peak}	627	nm
Wavelength at Dominate emission (I _F =10mA)	λ _D	625	nm
Spectral Line half-width (I _F =10mA)	Δλ	45	nm
Capacitance (V _F =0V, f=1MHz)	C	15	pF

Part Number	Emitting Color	Emitting Material	Luminous Intensity (I _F =10mA) ucd		Wavelength nm λ _P	Description
			min.	typ.		
XDUR14A2	Red	GaAsP/GaP	1900	7990	627	Common Anode.Rt. Hand Decimal

XDUR14A2



❖UR

