

0230022224 Basic 240

Compressor Basic 240



- Sturdy, mobile piston compressor – suitable for small and versatile commercial applications
- Oil-less piston condenser – with innovative PLS technology
- For single phase alternating current
- Pressure reducer with manometer for regulated working pressure
- Thermal motor protection
- 1 quick-action coupling
- Pressure switch with start-up valve
- Plastic-coated tank and chassis
- Solid large wheels
- 10 years tank warranty against rusting
- Built according to CE guidelines
- Testing not necessary before initial operation

Comparative device characteristics

Suction rate	220 l/min
Capacity	110 l/min
Effective delivery volume (at 7.2 bar working pressure)	100 l/min
Maximum pressure	8 bar
Rated input power	1,1 kW
Maximum speed	2.850 /min
Tank capacity	24 l
Voltage	230 V
Sound pressure level (LpA)	85 dB(A)
Dimensions	600 x 260 x 660 mm
Weight	21,5 kg