



USA7mmL, For General
Purposes**USR**

7mmL, High CV



- Standard miniature series with 7mm height.
- Compliant to the RoHS directive (2011/65/EU).



- Higher CV series with 7mm height.



■ Specifications


Item	USA				USR				
Category Temperature Range	- 40 to +85°C				-40 to +85°C				
Rated Voltage Range	6.3 to 50V				4 to 50V				
Rated Capacitance Range	1 to 220μF				1 to 470μF				
Capacitance Tolerance	± 20% at 120Hz, 20°C								
Leakage Current	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01CV or 3 (μA), whichever is greater.								
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C								
	Rated voltage (V)	4	6.3	10	16	25	35	50	
	tan δ (MAX.)	0.35	0.24	0.20	0.16	0.14	0.12	0.10	
Stability at Low Temperature	Measurement frequency : 120Hz								
	Rated voltage (V)		4	6.3	10	16	25	35	50
	Impedance ratio	Z-25°C / Z+20°C	6	4	3	2	2	2	2
	ZT / Z20 (MAX.)	Z-40°C / Z+20°C	12	8	6	4	4	3	3
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 85°C.				Capacitance change		Within ±20% of the initial capacitance value		
					tan δ		200% or less than the initial specified value		
					Leakage current		Less than or equal to the initial specified value		
Shelf Life	After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.								
Marking	Printed with white color letter on black sleeve.								

■ Radial Lead Type



	(mm)			
φD	4	5	6.3	8
P	1.5	2.0	2.5	3.5
φd	0.45	0.45	0.45	0.5

Type numbering system (Example : USA : 10V 33μF)



■ Dimensions

Dimensions		V(Code) Type·Series Code	4 (0G)		6.3 (0J)		10 (1A)		16 (1C)		25 (1E)		35 (1V)		50 (1H)	
			USR	USA	USR	USA	USR	USA	USR	USA	USR	USA	USR	USA	USR	
Cap.(μF)																
1	010														4 × 7 10	4 × 7 10
2.2	2R2														4 × 7 19	4 × 7 19
3.3	3R3														4 × 7 24	4 × 7 24
4.7	4R7											4 × 7 24	4 × 7 24		5 × 7 29	4 × 7 28
10	100							4 × 7 28	4 × 7 28	5 × 7 33	4 × 7 28	5 × 7 36	4 × 7 31		6.3 × 7 44	5 × 7 38
22	220		4 × 7 34	4 × 7 34	5 × 7 38	4 × 7 35	5 × 7 44	4 × 7 39	6.3 × 7 51	5 × 7 48	6.3 × 7 57	5 × 7 52		8 × 7 65	6.3 × 7 58	
33	330	4 × 7 33	5 × 7 42	4 × 7 40	5 × 7 47	4 × 7 43	6.3 × 7 57	5 × 7 55	6.3 × 7 63	5 × 7 58	8 × 7 72	6.3 × 7 65			8 × 7 75	
47	470	4 × 7 39	5 × 7 50	4 × 7 48	6.3 × 7 59	5 × 7 59	6.3 × 7 68	5 × 7 65	8 × 7 78	6.3 × 7 71		8 × 7 85				
100	101	5 × 7 65	6.3 × 7 77	5 × 7 78	8 × 7 96	6.3 × 7 87	8 × 7 107	6.3 × 7 98		8 × 7 115						
220	221	6.3 × 7 110	8 × 7 130	6.3 × 7 120		8 × 7 145		8 × 7 150								
330	331	8 × 7 165		8 × 7 180												
470	471	8 × 7 240													Case size φD × L (mm) Rated ripple	

Rated ripple current (mA rms) at 85°C 120Hz

● Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

Please refer to page 20, 21, 22 about the formed or taped product spec.
Please refer to page 4 for the minimum order quantity.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

[USA0J220MDD](#) [USA0J221MDD](#) [USA0J330MDD](#) [USA0J470MDD](#) [USA1C100MDD](#) [USA1E330MDD](#)
[USA1E470MDD](#) [USA1H3R3MDD](#) [USA1H4R7MCA](#) [USA1H4R7MDD](#) [USA1V4R7MCA1TP](#) [USA1V4R7MDD](#)
[USA0J101MDD](#) [USA1A330MDD](#) [USA1A470MDD](#) [USA1E100MDD](#) [USA1E220MDD](#) [USA1H220MDD](#)
[USA1H2R2MCA](#) [USA1H2R2MDD](#) [USA1A101MDD](#) [USA1A220MDD](#) [USA1C330MDD](#) [USA1C470MDD](#)
[USA1E100MCA](#) [USA1H100MDD](#) [USA1HR47MDD](#) [USA1V100MDD](#) [USA1C101MDD](#) [USA1C220MDD](#)
[USA1H010MCA](#) [USA1H010MDD](#) [USA1H0R1MDD](#) [USA1HR22MDD](#) [USA1HR33MDD](#) [USA1V220MDD](#)
[USA1V330MDD](#) [USA1C100MDD1TE](#) [USA1C220MDD1TE](#) [USA1C470MDD1TP](#) [USA1E330MDD1TP](#)
[USA1H010MDD1TE](#) [USA1H2R2MDD1TE](#) [USA1V100MDD1TP](#) [USA1V100MDD1TE](#) [USA1V4R7MDD1TP](#)
[USA1V220MDD1TP](#) [USA1A330MCA](#) [USA1H100MDD1TE](#) [USA1H100MCA](#) [USA1H4R7MDD1TE](#)
[USA1A330MDD1TP](#) [USA1E470MDD1TP](#) [USA1E100MDD1TP](#) [USA1HR47MDD1TE](#) [USA0J101MDD1TP](#)
[USA1H2R2MDD1TP](#) [USA1H2R2MDD1BA](#) [USA1H100MDD1TP](#) [USA1H4R7MDD1TP](#) [USR1E470MDD1TE](#)
[USR1V100MDD1TP](#) [USR0J101MDD1TP](#) [USR1E330MDD1TP](#) [USR1E220MDD1TP](#) [USR0G221MDD1TP](#)
[USA1C100MDD1TP](#) [USR1V4R7MDD1TP](#) [USR1H010MDD1TP](#) [USR1C330MDD1TP](#) [USR1H4R7MDD1TE](#)
[USA1H010MDD1TP](#) [USR0J470MDD1TP](#) [USR1H4R7MDD1TP](#) [USR1C100MDD1TP](#) [USR1C220MDD1TP](#)
[USR1E101MDD1TD](#) [USR1V4R7MDD1TE](#) [USR1E220MDD1TE](#) [USA1A101MDD1TD](#) [USA1A470MDD1TE](#)
[USR0G470MDD1TP](#) [USR1E101MDD1TE](#) [USR1C100MDD1TE](#) [USA1A470MDD1TP](#) [USA0J221MDD1TD](#)
[USA1E330MDD1TE](#) [USR1H010MDD1TE](#) [USR1H100MDD1TE](#) [USR1H220MDD1TE](#)