



A



B



C



NOTES: UNLESS OTHERWISE SPECIFIED;

- 1 CONNECTOR MATERIALS:
HOUSING: GLASS FILLED THERMOPLASTIC,
UL94-V0 COMPLIANT
KEEPER: GLASS FILLED THERMOPLASTIC,
UL94-V0 COMPLIANT
TERMINAL: PHOSPHOR BRONZE ALLOY
- 2 PACKED IN TUBES.
- 3 FEATURE MAY OR MAY NOT BE PRESENT DEPENDING UPON THE MOLD TOOL USED TO PRODUCE PRODUCT.
- 4 PRODUCT SPECIFICATION: GS-12-177.
- 5 APPLICATION SPECIFICATION: GS-20-015.
UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 6 THE PRODUCTS WHERE THE PART NUMBER ENDS IN 'LF' MEET THE EUROPEAN
- 7 ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- 8 LOCATION PEGS ARE EXISTED ONLY IN ONE MODULE

A

B

C

D



Copyright FCI.

rev	ecn no	dr	date
M	V04-1123	TAB	02/03/05
N	V05-0437	VS	07/14/05
P	V05-1026	JRV	11/7/05
R	DG06-0378	KL	09/01/06
S	DG06-0434	Cenh	10/23/06
T	DG08-0173	TER	7/11/08
U	N10-0382	Cenh	11/13/10

www.fciconnect.com			surface	tolerance	std	projection	MM	
			ANGULAR	LINEAR	0.X	± 0.50	size	Scale
Dr V. SEBASTIAN 07/14/05					0.XX	± 0.13	A4	4:1
Eng J. VOLSTROF 07/14/05			0°	±2°	0.XXX	± -	ECN	N10-0382
Chr J. VOLSTROF 07/14/05			Product family		METRAL		Spec ref	
Appr J. VOLSTROF 07/14/05			title		T SERIES R/A RECEPTACLE		Rev.	
			ASSY, 4 ROW, STB		SE96846		U	
			catalog no		CUSTOMER		sheet 1 of 4	

1

2

3

4

A

B

C


D

A

B

C

D



www.fciconnect.com			surface		tolerance std		projection			
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	V. SEBASTIAN	07/14/05	ANGULAR	LINEAR	0.X	± 0.50	size	A4	Scale 4:1	
Eng	J. VOLSTROF	07/14/05			0.XX	± 0.13				
Chr	J. VOLSTROF	07/14/05			0°. ±2°	0.XXX ± -				
Appr	J. VOLSTROF	07/14/05	Product family			METRAL		Spec ref		
	title T SERIES R/A RECEPTACLE ASSY, 4 ROW, STB					dwg no SE96846		Rev U		
catalog no					CUSTOMER			sheet 2 of 4		

REV F - 2006-04-17

1

2


3 PDM: Rev:U

STATUS: Released

4 Printed: Dec 01, 2010



Copyright FCI.





	PCB THICKNESS	DIM D	RETENTION FEATURES
HM1 F 4 T A R 000 H6	1.60	2.90±0.30	HEAT STAKE PEGS
HM1 F 4 T B R 000 H6	2.40	3.60±0.30	
HM1 F 4 T A P 000 H6	1.60	2.90 ±0.30	PRESS-FIT PEGS
HM1 F 4 T B P 000 H6	2.40	3.60 ±0.30	
HM1 F 49 T A P 802 H6	1.60	2.90 ±0.30	


TABLE 2

CODE	CONTACT AREA	PERFORMANCE LEVEL
6	0.75um Au min over 1.3um Ni min or 0.68um PdNi min +0.08um Au min over 1.3um Ni min	TELCORDIA CD

OBSOLETE



RECOMMENDED PC BOARD LAYOUT,
COMPONENT SIDE
SEE PRINT 58351 FOR ADDITIONAL
PCB INFORMATION



	PCB THICKNESS	DIM D	RETENTION FEATURES
HMI F 4_ T A P 400 H__LF	1.60	2.90 ±0.30	PRESS-FIT PEGS
HMI F 4_ T B P 400 H__LF	2.40	3.60 ±0.30	

www.fciconnect.com			surface ☒		tolerance std		projection 		MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	V. SEBASTIAN	07/14/05	ANGULAR		LINEAR	0.X	± 0.50	size	A4	Scale 4:1
Eng	J. VOLSTROF	07/14/05				0.XX	± 0.13			
Chr	J. VOLSTROF	07/14/05	0°	±2°		0.XXX	± -	ECN		N10-0382
Appr	J. VOLSTROF	07/14/05	Product family				METRAL	Spec ref		
		T SERIES R/A RECEPTACLE ASSY, 4 ROW, STB					dwg no		SE96846	Rev.
										U
		catalog no				CUSTOMER			sheet 4 of 4	