

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

LOC

DIST

REVISIONS

AF

50

P

LTR

DESCRIPTION

DATE

DWN

APVD

E1



REVISE PER ECR-14-006618

14MAY2014

GRZ

JL

9 AMPLIVAR SERRATIONS




1. PRODUCT PROVIDED IN STRIP FORM ON REELS; BREAKS MAY BE PRESENT.

2. FOR FOREIGN USE ONLY

3. DIMENSIONS IN BRACKETS ARE IN INCHES.

4. CRIMP WIDTH: .110 F (AMPLIVAR TYPE)
CRIMP HEIGHT (± 0.002) = (TOTAL CMA + 7730) / 188,900
CRIMP WIDTH: .090 F (AMPLIVAR TYPE)
CRIMP HEIGHT (± 0.002) = (TOTAL CMA + 7300) / 153,500
GENERAL APPLICATION GUIDELINES MUST BE FOLLOWED AS SPECIFIED IN CATALOG # 82221
FOR APPLICATOR INFORMATION CALL: 1-800-722-1111
FOR PRODUCT INFORMATION CALL: 1-800-522-6752

5. NOT FOR USE WITH ALUMINUM MAGNET WIRE.
USE WITH COPPER MAGNET WIRE ONLY.




SECTION A-A
SCALE : 20:1

METRIC

E	0.41[.016] PHOS-BRONZE	TIN PL.	62305-3
	0.41[.016] BRASS	TIN PL.	62305-2
	0.41[.016] BRASS	2	62305-1
MATERIAL		FINISH	PART NO.

5

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA		30JAN06		TE Connectivity									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK G.D.PORTA		—									
				APVD G.D.PORTA		—									
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.38[.015] 3 PLC ± — 4 PLC ± — ANGLES ± 1°		PRODUCT SPEC		NAME SPLICE, AMPLIVAR 600—3000 CMA —									
				—											
				APPLICATION SPEC											
				114—2003											
MATERIAL		FINISH		WEIGHT —		SIZE A3		CAGE CODE 00779		DRAWING NO C—62305		RESTRICTED TO —			
SEE TABLE		SEE TABLE		CUSTOMER DRAWING						SCALE 10:1		SHEET 1 OF 1		REV F1	