

# Steckhülsen 2,8 mm

## Clips femelles

## Receptacles

DIN 46247/1

\* ausgenommen  
\* excepté  
\* excepted

Werkstoff/Matière/Material

.2 = Bronze/bronze


.6 = Messing/laiton/brass

= Oberflächen/Surface/Surface-plating  
Seite/page/page 5.011

Strombelastbarkeit / Intensité admissible / Current carrying capacity:

0.3 – 0.5 mm<sup>2</sup> / 2.5 A max.

0.5 – 1.0 mm<sup>2</sup> / 6.0 A max.




| mm <sup>2</sup> | AWG   | Grösse<br>Grandeur<br>Size | Artikelnummer<br>Numéro d'article<br>Part-No. | DIN      | L1<br>mm | L2<br>mm | L3<br>mm | A1<br>mm | A2<br>mm | S<br>mm | Werkzeuge<br>Outils<br>Toolings |
|-----------------|-------|----------------------------|-----------------------------------------------|----------|----------|----------|----------|----------|----------|---------|---------------------------------|
| 0.14-0.3        | 26-24 | 2.8 x 0.5                  | 3760a.6                                       | *        | 14       | 6.3      |          | 5        | 2        | 0.25    | 3975b, 3984g<br>4084.3          |
|                 | 26-24 | 2.8 x 0.8                  | 3762a.6                                       | *        | 14       | 6.3      |          | 5        | 2        | 0.25    |                                 |
|                 | 26-24 | 2.8 x 1.2                  | 3762c.6                                       | *        | 14       | 6.3      |          | 5        | 2        | 0.25    |                                 |
| 0.3-0.5         | 24-22 | 2.8 x 0.5                  | 3760b.6                                       | 46247/T1 | 14       | 6.3      | 3.3      | 5.5      | 2.9      | 0.25    | 3975b, 3984a<br>3988n, 4084.3   |
|                 | 24-22 | 2.8 x 0.8                  | 3762b.2                                       | 46247/T1 | 14       | 6        | 4        | 5.5      | 2.9      | 0.25    |                                 |
|                 | 24-22 | 2.8 x 0.8                  | 3762b.6                                       | 46247/T1 | 14       | 6        | 4        | 5.5      | 2.9      | 0.25    |                                 |
| 0.5-1           | 22-18 | 2.8 x 0.5                  | 3764.6                                        | 46330/T2 | 12.5     | 5        | 3.3      | 5.5      | 2.5      | 0.25    | 3975b, 3984a<br>3988n, 4084.3   |
|                 | 22-18 | 2.8 x 0.8                  | 3765.6                                        | 46330/T2 | 12.5     | 5        | 3.3      | 5.5      | 2.9      | 0.3     |                                 |
|                 | 22-18 | 2.8 x 0.5                  | 3766.6                                        | 46247/T1 | 14       | 6.3      | 3.3      | 5.5      | 2.9      | 0.25    |                                 |
|                 | 22-18 | 2.8 x 0.8                  | 3767.2                                        | 46247/T1 | 14       | 6.3      | 3.3      | 5.5      | 2.9      | 0.25    |                                 |
|                 | 22-18 | 2.8 x 0.8                  | 3767.6                                        | 46247/T1 | 14       | 6.3      | 3.3      | 5.5      | 2.9      | 0.25    |                                 |

Werkstoff/Matière/Material

.6 = Messing/laiton/brass

= Oberflächen/Surface/Surface-plating  
Seite/page/page 5.011




| mm <sup>2</sup> | AWG   | Grösse<br>Grandeur<br>Size | Artikelnummer<br>Numéro d'article<br>Part-No. | DIN      | L1<br>mm | L2<br>mm | L3<br>mm | A1<br>mm | A2<br>mm | S<br>mm | Werkzeuge<br>Outils<br>Toolings |
|-----------------|-------|----------------------------|-----------------------------------------------|----------|----------|----------|----------|----------|----------|---------|---------------------------------|
| 0.14-0.3        | 26-24 | 2.8 x 0.8                  | 3763a.6                                       | 46340/T1 | 14       | 6.3      | 5.6      | 5.5      | 2.5      | 0.25    | 3975b, 3984g                    |
| 0.5-1           | 22-18 | 2.8 x 0.8                  | 3769.6                                        | *        | 15.5     | 8        | 8.3      | 5.5      | 2.5      | 0.3     | 3975b, 3984a<br>3988n, 4084.3   |

Werkstoff/Matière/Material

.6 = Messing/laiton/brass

= Oberflächen/Surface/Surface-plating  
Seite/page/page 5.011




| mm <sup>2</sup> | AWG   | Grösse<br>Grandeur<br>Size | Artikelnummer<br>Numéro d'article<br>Part-No. | DIN | L1<br>mm | L2<br>mm | L3<br>mm | A1<br>mm | A2<br>mm | S<br>mm | Werkzeuge<br>Outils<br>Toolings |
|-----------------|-------|----------------------------|-----------------------------------------------|-----|----------|----------|----------|----------|----------|---------|---------------------------------|
| 0.5-1           | 22-18 | 2.8 x 0.5                  | 3761a.6                                       | *   | 9        | 5        |          | 1.9      |          | 0.25    | 3975b, 3988n                    |
|                 | 22-18 | 2.8 x 0.8                  | 3761.6                                        | *   | 9        | 5        |          | 1.9      |          | 0.25    |                                 |

Werkstoff/Matière/Material

.6 = Messing/laiton/brass

= Oberflächen/Surface/Surface-plating  
Seite/page/page 5.011



| mm <sup>2</sup> | AWG   | Grösse<br>Grandeur<br>Size | Artikelnummer<br>Numéro d'article<br>Part-No. | DIN | L1<br>mm | L2<br>mm | L3<br>mm | A1<br>mm | A2<br>mm | S<br>mm | Werkzeuge<br>Outils<br>Toolings |
|-----------------|-------|----------------------------|-----------------------------------------------|-----|----------|----------|----------|----------|----------|---------|---------------------------------|
| 0.5-1           | 22-18 | 2.8 x 0.5                  | 3764w.6                                       | *   | 8        | 5        | 3.3      | 7.2      | 2.5      | 0.3     | 3973b,                          |
|                 | 22-18 | 2.8 x 0.8                  | 3765w.6                                       | *   | 8        | 5        | 3.3      | 7.2      | 2.5      | 0.3     | 3984wx                          |