BL GALAXY ELECTRICAL

KBPC35005(W)---KBPC3510(W)

SILICON BRIDGE RECTIFIERS

VOLTAGE RANGE: 50 --- 1000 V
CURRENT: 35.0 A

FEATURES

- ◇ Rating to 1000V PRV
- ◇ Surge overload rating to 400 Amperes peak
- ◇ Ideal for printed circuit board
- ◇ Reliable low cost construction utilizing molded plastic technique results in inexpensive product
- ◇ Lead solderable per MIL-STD-202 method 208

KBPC-W



inch (mm)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25℃ ambient temperature unless otherwise specified.

Single phase,half wave,60 Hz,resistive or inductive load. For capacitive load,derate by 20%.

		KBPC 35005 (W)	KBPC 3501 (W)	KBPC 3502 (W)	KBPC 3504 (W)	KBPC 3506 (W)	KBPC 3508 (W)	KBPC 3510 (W)	UNITS
Maximum recurrent peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forw ard Output current @T_A=25℃	$I_{F(AV)}$	35.0							A
Peak forw ard surge current 8.3ms single half-sine-w ave superimposed on rated load	I_{FSM}	400.0							A
Maximum instantaneous forw ard voltage @ 17.5 A	V_F	1.1							V
Maximum reverse current @T_A=25℃	I_R	10.0							μA
at rated DC blocking voltage @T_A=100℃		1.0							mA
Operating junction temperature range	T_J	- 55 ---- + 125							℃
Storage temperature range	T_{STG}	- 55 ---- + 150							℃

www.galaxycn.com

FIG.1 -- PEAK FORWARD SURGE CURRENT



FIG.2 -- FORWARD DERATING CURVE



FIG.3 -- TYPICAL FORWARD CHARACTERISTIC



FIG.4 -- TYPICAL REVERSE CHARACTERISTIC