






LOC		DIST		REVISIONS						
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD	
					B	REVISED PER ECO-11-025276	22DEC11	KH	DY	
					C	REV PER ECO-12-002142	13FEB2012	BC	DY	



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 21DEC2010		 TE Connectivity	
DIMENSIONS:		CHK J. EABY 21DEC2010			
mm		APVD J. EABY 21DEC2010		NAME	
		PRODUCT SPEC		IMPACT, 3 PAIR, 10 COLUMN, HEADER	
		APPLICATION SPEC		UNGUIDED, LEFT END WALL	
				SIGNAL MODULE, 0.39 PTH	
				SIZE	
				CAGE CODE	
				DRAWING NO	
MATERIAL		FINISH		RESTRICTED TO	
		SEE TABLE		-	
		WEIGHT		A100779C=2007789	
		CUSTOMER DRAWING		SCALE 6:1 SHEET 1 OF 2 REV C	

LOC	DIST	REVISIONS					
AD	00	REV	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2007789-6
	4.9	2007789-5
	4.5	2007789-4
	5.5	2007789-3
	4.9	2007789-2
	4.5	2007789-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 21DEC2010	TE Connectivity		
DIMENSIONS:		CHK J. EABY 21DEC2010			
mm		APVD J. EABY 21DEC2010	NAME IMPACT, 3 PAIR, 10 COLUMN, HEADER UNGUIDED, LEFT END WALL SIGNAL MODULE, 0.39 PTH		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		9 PLC ±		APPLICATION SPEC	
		1 PLC ±0.25		SIZE CAGE CODE DRAWING NO	
		2 PLC ±0.13		RESTRICTED TO	
MATERIAL		3 PLC ±		A100779C=2007789	
FINISH		4 PLC ±		SCALE 5:1 SHEET 2 OF 2 REV C	
SEE TABLE		WEIGHT		CUSTOMER DRAWING	
-		-			
-		CUSTOMER DRAWING			