



| Parameter           | Ratings | Units                |
|---------------------|---------|----------------------|
| Blocking Voltage    | 250     | $V_P$                |
| Load Current        | 170     | $mA_{rms} / mA_{DC}$ |
| On-Resistance (max) | 20      | $\Omega$             |

### Features

- 3750V<sub>rms</sub> Input/Output Isolation
- Low Drive Power Requirements (TTL/CMOS Compatible)
- Surface Mount Tape & Reel Version Available
- Arc-Free With No Snubbing Circuits
- FCC Compatible
- VDE Compatible
- No EMI/RFI Generation
- Small 6-Pin Package
- Machine Insertable, Wave Solderable

### Applications

- Telecommunications
  - Telecom Switching
  - Tip/Ring Circuits
  - Modem Switching (Laptop, Notebook, Pocket Size)
  - Hook Switch
  - Dial Pulsing
  - Ground Start
  - Ringing Injection
- Instrumentation
  - Multiplexers
  - Data Acquisition
  - Electronic Switching
  - I/O Subsystems
- Meters (Watt-Hour, Water, Gas)
- Medical Equipment-Patient/Equipment Isolation
- Security
- Aerospace
- Industrial Controls

### Description

The LCB120 is a single-pole, normally closed (1-Form-B) relay that uses optically coupled MOSFET technology to provide 3750V<sub>rms</sub> of input to output isolation.

Its optically coupled outputs, which use the patented OptoMOS architecture, are controlled by a highly efficient GaAlAs infrared LED.

The LCB120 has low on-resistance, and is well suited for most applications requiring a normally closed relay.

### Approvals


- UL Recognized Component: File E76270
- CSA Certified Component: Certificate 1175739
- EN/IEC 60950-1 Certified Component:  
TUV Certificate B 09 07 49410 006

### Ordering Information


| Part #    | Description                     |
|-----------|---------------------------------|
| LCB120    | 6-Pin DIP (50/Tube)             |
| LCB120S   | 6-Pin Surface Mount (50/Tube)   |
| LCB120STR | 6-Pin Surface Mount (1000/Reel) |

\* For other packaging options consult factory.

### Pin Configuration



### Switching Characteristics of Normally Closed Devices



## Absolute Maximum Ratings @ 25°C

| Parameter                            | Ratings     | Units            |
|--------------------------------------|-------------|------------------|
| Blocking Voltage                     | 250         | V <sub>P</sub>   |
| Reverse Input Voltage                | 5           | V                |
| Input Control Current                | 50          | mA               |
| Peak (10ms)                          | 1           | A                |
| Input Power Dissipation <sup>1</sup> | 150         | mW               |
| Total Power Dissipation <sup>2</sup> | 800         | mW               |
| Isolation voltage, Input to Output   | 3750        | V <sub>rms</sub> |
| Operational Temperature              | -40 to +85  | °C               |
| Storage Temperature                  | -40 to +125 | °C               |

<sup>1</sup> Derate linearly 1.33 mW / °C

<sup>2</sup> Derate linearly 6.67 mW / °C


*Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.*

## Electrical Characteristics @ 25°C


| Parameter                           | Conditions                                             | Symbol            | Min | Typ  | Max  | Units                                |
|-------------------------------------|--------------------------------------------------------|-------------------|-----|------|------|--------------------------------------|
| <b>Output Characteristics</b>       |                                                        |                   |     |      |      |                                      |
| Load Current: Continuous            |                                                        |                   |     |      |      |                                      |
| AC/DC Configuration                 | -                                                      | I <sub>L</sub>    | -   | -    | 170  | mA <sub>rms</sub> / mA <sub>DC</sub> |
| DC Configuration                    | -                                                      | I <sub>L</sub>    | -   | -    | 300  | mA <sub>DC</sub>                     |
| Peak Load Current                   | t=10ms                                                 | I <sub>L</sub>    | -   | -    | ±400 | mA <sub>P</sub>                      |
| On-Resistance                       |                                                        |                   |     |      |      |                                      |
| AC/DC Configuration                 | I <sub>L</sub> =170mA                                  | R <sub>ON</sub>   | -   | 11   | 20   | Ω                                    |
| DC Configuration                    | I <sub>L</sub> =300mA                                  | R <sub>ON</sub>   | -   | 5    | 6    | Ω                                    |
| Off-State Leakage Current           | I <sub>F</sub> =5mA, V <sub>L</sub> =250V <sub>P</sub> | I <sub>LEAK</sub> | -   | -    | 1    | μA                                   |
| Switching Speeds                    |                                                        |                   |     |      |      |                                      |
| Turn-On                             | I <sub>F</sub> =5mA, V <sub>L</sub> =10V               | t <sub>on</sub>   | -   | 0.65 | 5    | ms                                   |
| Turn-Off                            | I <sub>F</sub> =5mA, V <sub>L</sub> =10V               | t <sub>off</sub>  | -   | 1.30 | 5    | ms                                   |
| Output Capacitance                  | V <sub>L</sub> =50V, f=1MHz, I <sub>F</sub> =50mA      | C <sub>OUT</sub>  | -   | 50   | -    | pF                                   |
| <b>Input Characteristics</b>        |                                                        |                   |     |      |      |                                      |
| Input Control Current to Activate   | I <sub>L</sub> =170mA                                  | I <sub>F</sub>    | -   | -    | 5    | mA                                   |
| Input Control Current to Deactivate | -                                                      | I <sub>F</sub>    | 0.4 | -    | -    | mA                                   |
| Input Voltage Drop                  | I <sub>F</sub> =5mA                                    | V <sub>F</sub>    | 0.9 | 1.2  | 1.4  | V                                    |
| Reverse Input Current               | V <sub>R</sub> =5V                                     | I <sub>R</sub>    | -   | -    | 10   | μA                                   |
| <b>Common Characteristics</b>       |                                                        |                   |     |      |      |                                      |
| Input to Output Capacitance         | -                                                      | C <sub>I/O</sub>  | -   | 3    | -    | pF                                   |

# PERFORMANCE DATA\* (@25°C Unless Otherwise Noted)


Typical LED Forward Voltage Drop  
(N=50,  $I_F=5\text{mA}$ )




Typical Turn-On Time  
(N=50,  $I_F=5\text{mA}$ ,  $I_L=170\text{mA}_{DC}$ )




Typical Turn-Off Time  
(N=50,  $I_F=5\text{mA}$ ,  $I_L=170\text{mA}_{DC}$ )




Typical  $I_F$  for Switch Operation  
(N=50,  $I_L=170\text{mA}_{DC}$ )




Typical  $I_F$  for Switch Dropout  
(N=50,  $I_L=170\text{mA}_{DC}$ )




Typical On-Resistance Distribution  
(N=50,  $I_L=170\text{mA}_{DC}$ )




Typical Blocking Voltage Distribution  
(N=50,  $I_F=5\text{mA}$ )




Typical LED Forward Voltage Drop  
vs. Temperature



Typical Turn-On Time  
vs. LED Forward Current  
( $I_L=170\text{mA}_{DC}$ )













Typical Turn-Off Time  
vs. LED Forward Current  
( $I_L=170\text{mA}_{DC}$ )



\*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

# PERFORMANCE DATA\* (@25°C Unless Otherwise Noted)



\*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

## Manufacturing Information

### Moisture Sensitivity



All plastic encapsulated semiconductor packages are susceptible to moisture ingress. IXYS Integrated Circuits Division classified all of its plastic encapsulated devices for moisture sensitivity according to the latest version of the joint industry standard, **IPC/JEDEC J-STD-020**, in force at the time of product evaluation. We test all of our products to the maximum conditions set forth in the standard, and guarantee proper operation of our devices when handled according to the limitations and information in that standard as well as to any limitations set forth in the information or standards referenced below.

Failure to adhere to the warnings or limitations as established by the listed specifications could result in reduced product performance, reduction of operable life, and/or reduction of overall reliability.

This product carries a **Moisture Sensitivity Level (MSL) rating** as shown below, and should be handled according to the requirements of the latest version of the joint industry standard **IPC/JEDEC J-STD-033**.

| Device           | Moisture Sensitivity Level (MSL) Rating |
|------------------|-----------------------------------------|
| LCB120 / LCB120S | MSL 1                                   |

### ESD Sensitivity



This product is **ESD Sensitive**, and should be handled according to the industry standard **JESD-625**.

### Reflow Profile

This product has a maximum body temperature and time rating as shown below. All other guidelines of **J-STD-020** must be observed.

| Device           | Maximum Temperature x Time |
|------------------|----------------------------|
| LCB120 / LCB120S | 250°C for 30 seconds       |


### Board Wash

IXYS Integrated Circuits Division recommends the use of no-clean flux formulations. However, board washing to remove flux residue is acceptable. Since IXYS Integrated Circuits Division employs the use of silicone coating as an optical waveguide in many of its optically isolated products, the use of a short drying bake could be necessary if a wash is used after solder reflow processes. Chlorine- or Fluorine-based solvents or fluxes should not be used. Cleaning methods that employ ultrasonic energy should not be used.




## Mechanical Dimensions

### LCB120




#### PCB Hole Pattern




Dimensions  
mm  
(inches)

### LCB120S




#### PCB Land Pattern



Dimensions  
mm  
(inches)

## LCB120STR Tape & Reel



For additional information please visit our website at: [www.ixysic.com](http://www.ixysic.com)

IXYS Integrated Circuits Division makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in IXYS Integrated Circuits Division's Standard Terms and Conditions of Sale, IXYS Integrated Circuits Division assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of IXYS Integrated Circuits Division's product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. IXYS Integrated Circuits Division reserves the right to discontinue or make changes to its products at any time without notice.