

Adapter plate - VS-ADP16-VS25 - 1652415

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Adapter plate, size B16, reinforced, including panel mounting frame with DSUB 25 protective cover without contact insert



RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 969783
GTIN	4017918969783
Weight per Piece (excluding packing)	54.600 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Mechanical characteristics

Weight	50 g
--------	------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------


Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Drawings


Adapter plate - VS-ADP16-VS25 - 1652415

Dimensional drawing



Adapter plate

Dimensional drawing



Mounting cutout

Adapter plate - VS-ADP16-VS25 - 1652415

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27189239
eCl@ss 5.1	27189239
eCl@ss 6.0	27144001
eCl@ss 7.0	27144001
eCl@ss 8.0	27440201
eCl@ss 9.0	27440201

ETIM

ETIM 2.0	EC000007
ETIM 3.0	EC000007
ETIM 4.0	EC000007
ETIM 5.0	EC002309

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501