




© COPYRIGHT 1998 BY SPC TECHNOLOGY. ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


REVISIONS		DOC. NO.	SPC-FD05, Total Pages: 2					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
129	A	RELEASED	DJC	3/11/98	JC	7/15/98	JMM	7/15/98



**SPECIFICATIONS:**

IMPEDANCE: 50 OHMS  
 WORKING VOLTAGE: 500 VRMS @ SEA LEVEL  
 FREQUENCY RANGE: 0-7 GHz  
 INSERTION LOSS: <math>\leq -2\text{ dB}</math> @ 3 GHz  
 VSWR MAX: 1.3:1 @ 3 GHz  
 FOR RG-8/X & 30/U, BELDEN 9258, MAXRAD MBX-100 & MBX-1000, MICRO 8/U, REMEE 1600, SXTON 8315 & TIMES LMR-240 & LMR-240 ULTRAFLEX CABLE

ITEM	DESCRIPTION	QTY	MATERIAL	FINISH
7	FERRULE	1	BRASS	NICKEL
6	RETAINING RING	1	BRASS	NONE
5	GASKET	1	S.I. RUBBER	RED
4	SHELL	1	BRASS	NICKEL
3	DIELECTRIC	1	DELRIN	NONE
2	PIN	1	BRASS	GOLD
1	BODY	1	BRASS	NICKEL



SUGGESTED STRIPPING INSTRUCTIONS  
 SUGGESTED CRIMP DIES: .068 & .213

**DISCLAIMER**  
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL OBTAIN THE SUPPLIERS OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWING TITLE:  
**TNC MALE CRIMP**

DRAWN BY:	DANIEL CAREY	DATE:	3/11/98
CHECKED BY:	JOHN COLE	DATE:	7/15/98
APPROVED BY:	JEFF MCVICKER	DATE:	7/15/98

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	1539	92N3385.DWG	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1