

Snap-In Round Hole Illuminated Rocker




Features

- AC and DC Types



NTE Type No.	Circuitry	Action			Actuator				Diag No.
					Material	Color		V/tg	
						Neon	LED		
54-506	SPST	ON	NONE	OFF	Nylon	Red	—	AC	S90
54-532	SPST	ON	NONE	OFF	Nylon	Amber	—	AC	S90
54-533	SPST	ON	NONE	OFF	Nylon	Green	—	AC	S90
54-534	SPST	ON	NONE	OFF	Nylon	—	Red	DC	S90
54-535	SPST	ON	NONE	OFF	Nylon	—	Amber	DC	S90
54-536	SPST	ON	NONE	OFF	Nylon	—	Green	DC	S90
54-537	SPST	ON	NONE	OFF	Nylon	—	Blue	DC	S90

S90



Specifications

Current Rating: 16A 125VAC, 10A 250VAC
Lamp Voltage: 110V Neon (AC) & 2V @ 20mA* LED (DC)
Insulation Resistance: 100 Megohms (min.) at 500VDC
Dielectric Strength: 1500V RMS (min.)
Temperature Rating: -4° to +149°F (-20° to +65°C)
Electrical Life: 6000 cycles (min.)
Mechanical Life: 100,000 cycles (min.)
Terminal Type: .187" Tab Q.C.
Mounting Hole: .795 (20.2)
 * Resistor needed for other voltages.

Snap-In Round Hole Illuminated Rocker




Features

- Waterproof Types Available on Page 26



NTE Type No.	Circuitry	Action			Actuator			Diag No.
					Material	Color	V/ttg	
54-525	SPST	ON	NONE	OFF	Nylon	Amber	AC	S90
54-526	SPST	ON	NONE	OFF	Nylon	Green	AC	S90
54-527	SPST	ON	NONE	OFF	Nylon	Red	DC	S90
54-528	SPST	ON	NONE	OFF	Nylon	Amber	DC	S90
54-529	SPST	ON	NONE	OFF	Nylon	Green	DC	S90
54-530	SPST	ON	NONE	OFF	Nylon	Blue	DC	S90
54-531	SPST	ON	NONE	OFF	Nylon	Red	AC	S90

S90



Specifications

Current Rating: 16A 125VAC, 10A 250VAC
Lamp Voltage: 110V (AC) Neon, 12V (DC) Incandescent
Insulation Resistance: 100 Megohms (min.) at 500VDC
Dielectric Strength: 1500V RMS (min.)
Temperature Rating: -4° to +149°F (-20° to +65°C)
Electrical Life: 6000 cycles (min.)
Mechanical Life: 100,000 cycles (min.)
Terminal Type: .187" Tab Q.C.
Mounting Hole: .795 (20.2)