

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

.39 Ø (REF)
[9.91]


.26 Ø (REF)
[6.73]

PANDUIT
PART NO.

WEIGHT
lbs 10
(g) pcs

JP131CMB-___

1.06
(478)



4.6
[117.23]
(REF)

.67 (REF)
[17.09]

1.25 (REF)
[31.70]


.18 Ø (REF)
[4.57]

1.81
[46.05]
(REF)



2.18
[55.24]

3.4
[86.21]
(REF)

TAK-TY
SLOT



1.2
[29.95]
(REF)



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
- HOOK MATERIAL: NYLON 6/6
ANGLE BRACKET MATERIAL: PRE-GALVANIZED STEEL,
RIVET MATERIAL: ALUMINUM
- PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 1 5/16" (33.34) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 25 lbs.
- PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
- PRODUCT MARKINGS:
cULus logo and statement:
"SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."
ULC logo and statement:
"IN ACCORDANCE WITH CAN/ULC S-102.2-10 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=35."

TITLE			
J-PRO CEILING MOUNT J-HOOK (JP131CMB-___)			
CUSTOMER DRAWING			
ITEM REVISION NAME		121031AB/00	
DATASET FILE NAME		121031AB_DC_C11001/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x : .1 [2.54] .xx : .01 [2.54]		SEE NOTE 2	
.xxx : .005 [1.27] ANGLES : 5 °		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		C11001	
DRAWN BY	DATE	CHK	SCALE
DBLA	11/08/0212	KLN	NONE
SHT 1 OF 1			SIZE
			A

2

1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	11/08/2012	DBLA	GGC	KLN	INITIAL RELEASE	GAECN00220

21/01000A/12