




LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
T		REV PER ECO-06-018048		05OCT06	PY	DM	

1. CONTACTS INCLUDED IN ASSEMBLY.
- 2 MAT'L: STEEL, PER ASTM-A-109.
- 3 FINISH: CADMIUM PER QQ-P-416.
- 4 MAT'L: BRASS PER ASTM-B-36.
- 5 FINISH: PLATED ZINC .00020 MIN THK PER ASTM-B-633. YELLOW CHROMATE FINISH.
- 6 CONTACT
- BODY MAT'L: BERYLLIUM COPPER PER ASTM-B-197.
- BODY FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER NICKEL, .000050 MIN THK PER QQ-N-290.
- HOOD MAT'L: STAINLESS STEEL PER ASTM-A-240.
- HOOD FINISH: PASSIVATED PER QQ-P-35
- 7 FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER FLASH
- 8 FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.
- 9 CONTACT
- BODY MAT'L: BERYLLIUM COPPER PER ASTM-B-197.
- BODY FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.
- HOOD MAT'L: COPPER ALLOY PER QQ-B-613.
- FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.

OBSOLETE	4 8	4 8	6	4U884 SOCN R10002677-0107	211011-6	
	4 8	4 7	6	2A091-002W-001	211011-5	
	4 8	4 7	9	-	211011-4	
	4 8	4 7	9	-	211011-3	
	4 8	4 7	6	(1J02-107)	211011-2	
	4 8	2 3	6	-	211011-1	
	EYELET		SHELLS		CONTACT	CUSTOMER P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN C.C.THOMAS 11-3-98		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: INCHES				CHK J.NORTON 11-17-98				
				APVD J.NORTON 11-17-98		NAME		
				PRODUCT SPEC		CONNECTOR SAVER,AMPLITE		
				APPLICATION SPEC		26 POSN.,SIZE 2,SERIES 90		
				WEIGHT -		-		
				CUSTOMER DRAWING		-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:				SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -				A1		00779	211011	-
1 PLC ± -								
2 PLC ± -								
3 PLC ± .005 [0.13]								
4 PLC ± -								
ANGLES ± -								
FINISH								
MATERIAL -								