

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD




A2

REVISED PER ECO-11-005294

19APR11



RK

HMR



ORDER NUMBER	NUMBER OF POSITIONS	L MAX.	
		M.M.	INCHES
5164711-3	3	7,5	.296
5164711-4	4	10,0	.394
5164711-5	5	12,5	.493
5164711-6	6	15,0	.591
5164711-7	7	17,5	.690
5164711-8	8	20,0	.788
5164711-9	9	22,5	.886
1-5164711-0	10	25,0	.985
1-5164711-1	11	27,5	1.083
1-5164711-2	12	30,0	1.182
1-5164711-3	13	32,5	1.280
1-5164711-4	14	35,0	1.378
1-5164711-5	15	37,5	1.477
1-5164711-6	16	40,0	1.575
1-5164711-7	17	42,5	1.674
1-5164711-8	18	45,0	1.772
1-5164711-9	19	47,5	1.871
2-5164711-0	20	50,0	1.969

1
OBSOLETE




SECTION B-B

SECTION A-A

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

2	CONTACT	BRASS	TIN OVER NICKEL	SEE TABLE
1	HOUSING	PBT, 20% GF	GREEN	1
ITEM NO.	DESCRIPTION	MATERIAL	FINISH	QUANTITY

		ITEM NO:		DESCRIPTION		MATERIAL		FINISH		QUANTITY					
				DWN M. Gosselink 31 mar 05											
				CHK M. Gosselink 31 mar 05											
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:				TE Connectivity									
mm						NAME									
		0 PLC ±-				3-20 POS FEMALE BOARD TO BOARD									
		1 PLC ±-				CONNECTOR ASSEMBLY FOR MINI-MATCH									
		2 PLC ±-				INTERCONNECTION SYSTEM, PITCH 2.5 MM									
		3 PLC ±-													
		4 PLC ±-													
		ANGLES ±-													
MATERIAL		FINISH				PRODUCT SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
-		-				108-19027		A3		00779		C=5164711		-	
						APPLICATION SPEC		WEIGHT							
						-		-							
CUSTOMER DRAWING								SCALE		SHEET		OF		REV A2	