




CI-23818-000

SHT 1.1



NOTES:

1 A POSITIVE GOING VOLTAGE AT TERMINAL 2, RELATIVE TO TERMINAL 1, CAUSES A DECREASE IN PRESSURE AT THE SOUND OUTLET.




DIMENSIONS IN MILLIMETERS [INCHES]

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
B	CI0111948	12-28-10	Active	B
A	CI0103475	11-30-05		
SCALE: 2:1			DR. BY DMS	DATE 11-30-05
DO NOT SCALE DRAWING			CK. BY GJP	DATE 12-5-05
TITLE: RECEIVER		CI-23818-000	APP. BY GJP	DATE 12-5-05
OUTLINE DRAWING		SHT 1.1	Rev: B	

NO DAMPING



NOTES:

1. MEASUREMENTS MADE USING 8mm (.315") X 1mm (.039") + 28mm (1.10") X 1.5mm (.059") ID EAR HOOK SIMULATOR INTO 25mm (.984") OF 2mm (.097") ID TUBE + 18mm (.709") OF 3mm (.118") ID TUBE + 2 cm³ CAVITY. ANSI S3.6 TYPE HA-3 (IEC 60318-5).

2. SENSITIVITY

FREQUENCY	MIN.	MAX.
200	111.0	117.0
300	112.0	118.0
500	115.5	121.5
750-1000	125.5	131.5
1200-1600	116.0	122.0
1700-2300	124.5	130.5
2300-2800	116.0	---
2800-3300	120.0	128.0
3300-4000	109.0	---
4000-4700	113.0	119.0
4800-5500	98.0	---

3. RESPONSE, IMPEDANCE, AND DISTORTION MEASUREMENTS MADE USING THE ELECTRICAL TEST CONDITIONS SHOWN BELOW.

4. INDIVIDUAL SPECIFICATIONS.

PORT LOCATION	ELECTRICAL TEST CONDITIONS				DCR @20°C OHMS ±10%	DISTORTION		IMPEDANCE @ 500 Hz OHMS±15%
	RESPONSE & IMPEDANCE		DISTORTION			MAX. %	FREQ. Hz	
	AC mA RMS	DC mA	AC mA RMS	DC mA				
IS	2.25	0.0	4.5	0.0	51	10	500	132

5. ELECTRICAL SOURCE IMPEDANCE MUST BE GREATER THAN 20 TIMES STATED IMPEDANCE FOR TEST CONDITIONS ABOVE.

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.

Revision	C.O. #	Implementation Date	RELEASE LEVEL		REVISION
B	CI0111948	12-28-10	Active		B
A	CI0103475	11-30-05			
WHEN TEST LIMITS ARE USED TO ESTABLISH INCOMING INSPECTION ACCEPTANCE/REJECTION CRITERIA, CORRELATION OF TEST EQUIPMENT WITH KNOWLES IS ALSO REQUIRED FOR ELIMINATION OF EQUIPMENT AND TEST METHOD VARIATION			DR. BY	DATE	
			DMS	11-30-05	
			CK. BY	DATE	
			GJP	12-5-05	
			APP. BY	DATE	
			GJP	12-5-05	

TITLE: RECEIVER
PERFORMANCE SPECIFICATION

CI-23818-000
SHT 2.1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Knowles:](#)

[CI-23818-000](#)