




PRODUCT NUMBER
73326-XXXLF

PLATING OPTION
1= GXT 0.76 μm
3= GOLD 0.76 μm
5= GOLD 1.27 μm

PACKAGE OPTION
1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG


TERMINAL LOADING
1= FULLY LOADED
2= POS 2,3,4,5
3= POS 1,2,5,6

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.



NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μm MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μm MINIMUM MATTE TIN OVER 1.27 μm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.








CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family MOD JACK			
ltr	ecn no	dr	date	tolerances unless otherwise specified				title		SMT RA JACK 6 POS INSIDE			
H	F06-0240	DLE	06.07.18	angles		linear		mm 					
J	F09-0070	LSA	09.07.23	±2'				scale 2:1					
K	B-15798	JFA	13.09.09	±2'									
L	F-21888	AMA	15.09.09	dr	D LEGRAND		04.10.18			dwg no		sheet 1 of 3	size
				enrg	P NIZZI		04.10.18			73326		A3	
F	F04-0363	DLE	04.10.18	chr	D LEGRAND		04.10.18						
G	F05-0247	DLE	05.09.12	appd	P NZ		04.10.18			type		CUSTOMER Drawing	
sheet index	revision	L	E	B									
	sheet	1	2	3									

PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3


CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		MOD-JACK
ltr	ecr no	dr	date	tolerances unless otherwise specified			title
D	F80620	DLE	98.11.26	angles			SMT RA JACK
E	F06-024Q	DLE	06.07.18	linear			6 POS. INSIDE
				dr	D LEGRAND	06.07.18	dwg no
				enrg	P NIZZI	06.07.18	73326
				chr	D LE	06.07.18	sheet 2 of 3
				appd	P NZ	06.07.18	size
							A3
							type
							CUSTOMER Drawing
sheet index	revision	sheet					



FCconnect.com

Copyright FCJ



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302		ISO 406 ISO 1101				MOD JACK	
ltr		ecn no		date		tolerances unless otherwise specified		title	
A		F04-0363		04.10.18		±0.13		SMT RA JACK	
B		F06-0240		06.07.18		mm		6 POS INSIDE	
				angles		linear		scale 2:1	
				±2°					
				dr		D LEGRAND		dwg no	
				engr		P NIZZI		sheet 3 of - size	
				chr		D LEGRAND		73326 A4	
				appd		P NZ		type	
								CUSTOMER Drawing	
sheet index		revision sheet							

form: A4