


SF20JC10

100V 20A

OUTLINE DIMENSIONS

Case : FTO-220

Unit : mm



RATINGS


●Absolute Maximum Ratings (If not specified, Tc=25℃)

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-55~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	V _{RM}		100	V
Average Rectified Forward Current	I _O	50Hz sine wave, R-load, Rating for each diode I _O /2, T _c =114°C	20	A
Peak Surge Forward Current	I _{FSM}	50Hz sine wave, Non-repetitive 1 cycle peak value, T _j =25°C	200	A
Dielectric Strength	V _{dis}	Terminals to case, AC 1 minute	2.0	kV
Mounting Torque	TOR	(Recommended torque : 0.3N·m)	0.5	N·m


●Electrical Characteristics (If not specified, Tc=25℃)



Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	V_F	$I_F=10A$, Pulse measurement, Rating of per diode	Max 0.86	V
Reverse Current	I_R	$V_R=V_{RM}$, Pulse measurement, Rating of per diode	Max 0.7	mA
Junction Capacitance	C_j	$f=1MHz$, $V_R=10V$, Rating of per diode	Typ 260	pF
Thermal Resistance	θ_{jc}	junction to case	Max 2.0	°C/W



SF20JC10 Forward Voltage



SF20JC10 Reverse Voltage




 $T_j = 150^\circ\text{C}$ 


 $T_J = 150^\circ\text{C}$ 

SF20JC10

Derating Curve




$V_R = 50V$



SF20JC10

Peak Surge Forward Capability



SF20JC10 Junction Capacitance

