

8514019 SPRAGUE, SEMICONDUCTORS/ICS

93D 03604 D

T-29-25

PLASTIC-CASE JUNCTION FIELD-EFFECT TRANSISTORS

P-Channel JFETs

ELECTRICAL CHARACTERISTICS at $T_A = 25^\circ\text{C}$

Device Type	$V_{DS(ON)}$		I_{DSS}		g_{fs}		C_{iss}^1		C_{rss}^1		r_{DS} Max. (Ω)	Process
	Min. (V)	Max. (μA)	Min. (V)	Max. (V)	Min. (mS)	Max. (mS)	Min. (pF)	Max. (pF)	Min. (pF)	Max. (pF)		
TP3994	25	1.0	1.0	15	1.0	5.5	-10	-12	-2.0	—	-10	PJ99
TP4381	25	1.0	1.0	15	1.0	5.0	-15	-10 ²	-3.0	-12	-15	PJ32
TP5018	30	1.0	2.0	15	—	10	-15	-12	-10	—	-20	PJ99
TP5019	30	1.0	2.0	15	—	5.0	-15	-12	-5.0	—	-20	PJ99
TP5020	25	1.0	1.0	15	0.3	1.5	-15	-12	-0.3	-1.2	-15	PJ32
TP5021	25	1.0	1.0	15	0.5	2.5	-15	-12	-1.0	-3.5	-15	PJ32
TP5033	20	10	10	15	0.3	2.5	-15	-10 ²	0.3	3.5	-15	PJ99
TP5114	30	1.0	1.0	20	5.0	10	-15	-1.0	-30	-90	-15	PJ99
TP5115	30	1.0	1.0	20	3.0	6.0	-15	-1.0	-16	-60	-15	PJ99
TP5116	30	1.0	1.0	20	1.0	4.0	-15	-1.0	-5.0	-25	-15	PJ99
2N5460	40	10	5.0	20	0.75	6.0	-15	-1.0	-1.0	-5.0	-15	PJ32
2N5461	40	10	5.0	20	1.0	7.5	-15	-1.0	-2.0	-9.0	-15	PJ32
2N5462	40	10	5.0	20	1.8	9.0	-15	-1.0	-4.0	-16	-15	PJ32
J174	30	1.0	1.0	20	5.0	10	-15	-10	-20	-135	-15	PJ99
J175	30	1.0	1.0	20	3.0	6.0	-15	-10	-7.0	-70	-15	PJ99
J176	30	1.0	1.0	20	1.0	4.0	-15	-10	-2.0	-35	-15	PJ99
J177	30	1.0	1.0	20	0.8	2.25	-15	-10	-1.5	-20	-15	PJ99
J270	30	1.0	0.2	20	0.5	2.0	-15	-1.0	-2.0	-15	-15	PJ99
J271	30	1.0	0.2	20	1.5	4.5	-15	-1.0	-6.0	-50	-15	PJ99
P1086	30	1.0	2.0	15	—	10	-15	-12	-10	—	-20	PJ99
P1087	30	1.0	2.0	15	—	5.0	-15	-12	-5.0	—	-20	PJ99
TPU304	30	1.0	1.0	20	5.0	10	-15	-12	-30	-90	-15	PJ99
TPU305	30	1.0	1.0	20	3.0	6.0	-15	-12	-15	-60	-15	PJ99
TPU306	30	1.0	1.0	20	1.0	4.0	-15	-12	-5.0	-25	-15	PJ99

NOTES:


- 1) $V_{GS} = 0\text{ V}$.
- 2) I_D in μA .
- 3) $V_{DS} = 0\text{ V}$, V_{GS} in volts.
- 4) $V_{GS} = 1.0\text{ V}$.

T-91-20

PACKAGE INFORMATION

TO-226AA/STYLES CG AND CO


DIMENSIONS IN INCHES




Dwg No A-13.610

DIMENSIONS IN MILLIMETERS

Based on 1" = 25.4 mm



Dwg. No. A-13.611

MAXIMUM ALLOWABLE PACKAGE POWER DISSIPATION
AS A FUNCTION OF AMBIENT TEMPERATURE

Dwg No A-13.612



CG PINOUT


Pin	Terminal
1	Drain
2	Source
3	Gate

CO PINOUT



Pin	Terminal
1	Source
2	Drain
3	Gate

T-91-20

PACKAGE INFORMATION

TO-226AA/STYLES CI AND CN**DIMENSIONS IN INCHES****DIMENSIONS IN MILLIMETERS**

Based on 1" = 25.4 mm

**MAXIMUM ALLOWABLE PACKAGE POWER DISSIPATION
AS A FUNCTION OF AMBIENT TEMPERATURE****CI PINOUT**

Pin	Terminal
1	Drain
2	Gate
3	Source

CN PINOUT

Pin	Terminal
1	Source
2	Gate
3	Drain