

Data Sheet

Models 9120, 9121, 9122 Single Output Programmable DC Power Supplies

The 9120 series power supplies are designed to meet the needs of today's applications in R&D design verification, university labs, production testing, and other applications that require clean/reliable power and excellent performance. With meter resolution of 10mV and 1mA, these power supplies are ideal for low power surface mount circuits that require very precise voltage and current settings.



New microprocessor control circuitry allows these power supplies to offer unmatched temperature stability and remarkably fast transient response times with a load regulation of $0.01\% + 3\text{mV}$. These power supplies are smart enough to power-up in to the same state they were when they were powered off. This allows the units to go back to work as soon as power is restored whether the power-off was intentional or caused by a power outage. There is enough non-volatile memory to store up to 100 power supply settings allowing quick and easy testing when multiple voltage and current values are required.

- 10mV & 1mA Display Resolution
- RS 232 Interface
- SCPI Compatible
- Remote Sensing
- Front and Rear Output Terminals
- Low Noise
- Excellent Regulation
- Rock Solid Temperature Stability
- Fast Transient Response Time
- Closed Case Calibration

Specifications	9120	9121	9122
Output Voltage	0-30V	0-20V	0-60V
Output Current	0-3A	0-5A	0-2.5A
Voltage Regulation			
Load (Utilizing Remote Sensing)	$\leq 0.01\% + 3\text{mV}$		
Ripple & Noise	$\leq 0.5\text{mVrms} \& 5\text{mVp-p}$		$\leq 1\text{mVrms} \& 8\text{mVp-p}$
Metering			
Type	Backlit LCD		
Voltmeter Resolution	10mV		
Voltmeter Accuracy	$\leq 0.05\% + 5\text{mV}$		
Current Meter Accuracy	$\leq 0.15 + 5\text{mA}$		
Current Meter Resolution	1mA		

B&K Precision Corporation

22820 Savi Ranch Parkway, Yorba Linda, CA 92887
Tel: 714-921-9095, Fax: 714-921-6422
www.bkprecision.com

Specifications subject to change without notice