







PART NUMBER 10106265-B006001LF



spec ref		*		dr		Peng-Bing Fu	2012/03/09	projection		mm		size		A3	scale		3:2			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Eddy Zeng	2013/10/21					ecn no		-						
chr				Li-He	2013/10/17															
appr				Pei-Ming Zheng	2013/10/21	product family						PwrBlade+	rel level		Released					
surface			linear	0.X		±0.5				title		3ACP + 8HP + 24S		dwg no		10106265-B006001		rev		A
ISO 406				0.XX		±0.25														
ISO 1101				0.XXX		±0.10														
ISO 1302		angular	0°	±2°		www.fci.com		cat. no.		-	Product - Customer Drw		sheet 1 of 3							

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE P/N CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.

dr	Peng-Bing Fu	2012/03/09	projection 	mm 	size	scale
eng	Eddy Zeng	2013/10/21			A3	3:2
chr	Li- He	2013/10/17			ecn no	-
appr	Pei-Ming Zheng	2013/10/21	product family	PwrBlade+	rel level	Released
www.fci.com		cat. no.	-	Product - Customer Drw		sheet 3 of 3
FCI		title			dwg no	rev
		3ACP + 8HP + 24S			10106265-B006001	A
		RA PF RECEPTACLE				



Copyright FCI.