



Specifications

- Certifications*: UL, CSA, VDE, TUV, SEMKO, DEMKO, SEV, NEMKO, SETI
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon

Dimensional Specifications: in. [mm]



The diagram shows a 6-pin rocker switch with the following labels and options:

- SERIES:** 6
- ACTUATOR STYLE:** 11 PADDLE, 21 CURVED ROCKER
- BASE/ACTUATOR COLOR:** BASE (1 BLACK, 2 BLACK, 4 WHITE, 5 WHITE), ACTUATOR (1 BLACK, 2 WHITE, 4 BLACK, 5 WHITE)
- POLES:** 1 SINGLE POLE, 2 DOUBLE POLE, 5 DOUBLE POLE W/ HIGH BARRIERS, 6 SINGLE POLE W/ HIGH BARRIERS
- RATING:** 1 .4VA MAX @20V MAX (AC/DC), 2 2A 250VAC 5A 125VAC RESISTIVE, 3 11A 125VAC H³, 4 4A 250 VAC 8A 125VAC, 9 4A 250VAC 8A 125VAC INDUCTIVE, 6(4)A 250VAC T85⁸
- FUNCTION:** 1 ON-NONE-OFF
- TERMINATION:** 1 .080 SOLDER LUG, 2 PC TERM, 3 WIRE LEAD⁷, 4 WIRE LEAD, 6 .187 SOLDER LUG, 7 PC BACK MOUNT, 8 PC FRONT MOUNT, 9 .187TAB (QC)
- EPOXY SEALED TERMINALS:** E EPOXY, 0 NONE REQUIRED
- ROCKER FACE LEGEND:** MOLED-IN⁵ (0 NO LEGEND ON-OFF (VERTICAL), 8 I-O (HORIZONTAL), 9 I-O (VERTICAL)), INK TRANSFER STAMP⁶ (0 A, B, D, E, F)

8 Rating 9 using Termination 1 or 2 is rated T55 only.

al. **N** NOT APPLICABLE
B BLACK
V VISI-RED
W WHITE