

P6KE6.8A THRU P6KE440A  
P6KE6.8CA THRU P6KE440CA

UNI-DIRECTIONAL  
AND BI-DIRECTIONAL  
SILICON TRANSIENT  
VOLTAGE SUPPRESSORS  
600 WATTS, 6.8 THRU 440 VOLTS

Specified by  
BREAKDOWN VOLTAGE



DO-15 CASE



www.centrasemi.com

#### DESCRIPTION:

The CENTRAL SEMICONDUCTOR P6KE6.8A (Uni-Directional) and P6KE6.8CA (Bi-Directional) Series types are Transient Voltage Suppressors designed to protect voltage sensitive components from high voltage transients.

**THIS DEVICE IS MANUFACTURED WITH A GLASS PASSIVATED CHIP FOR OPTIMUM RELIABILITY.**

Note: For Uni-Directional devices add suffix "A" to part number. For Bi-Directional devices add suffix "CA" to part number.

#### MARKING: FULL PART NUMBER

Bi-directional devices shall not be marked with a Cathode band.

**MAXIMUM RATINGS:** ( $T_A=25^\circ\text{C}$  unless otherwise noted)

Peak Power Dissipation (Note 1)

Steady State Power Dissipation ( $T_L=75^\circ\text{C}$ )

Forward Surge Current (Uni-Directional only)

Operating and Storage Junction Temperature

#### SYMBOL

$P_{PK}$  600

$P_D$  5.0

$I_{FSM}$  100

$T_J, T_{stg}$  -65 to +175

#### UNITS

W

W

A

$^\circ\text{C}$

**ELECTRICAL CHARACTERISTICS:** ( $T_A=25^\circ\text{C}$  unless otherwise noted)

| TYPE    | BREAKDOWN VOLTAGE |       |       | TEST CURRENT<br>$I_T$<br>mA | WORKING PEAK REVERSE VOLTAGE<br>$V_{RWM}$<br>V | MAXIMUM REVERSE LEAKAGE CURRENT<br>$I_R @ V_{RWM}$<br>$\mu A$ | MAXIMUM CLAMPING VOLTAGE<br>$V_C @ I_{PP}$<br>V | PEAK PULSE CURRENT (Note 1)<br>$I_{PP}$<br>A | MAXIMUM TEMPERATURE COEFFICIENT<br>$\theta V_{BR}$<br>% / °C |
|---------|-------------------|-------|-------|-----------------------------|------------------------------------------------|---------------------------------------------------------------|-------------------------------------------------|----------------------------------------------|--------------------------------------------------------------|
|         | $V_{BR} @ I_T$    |       |       |                             |                                                |                                                               |                                                 |                                              |                                                              |
|         | MIN V             | NOM V | MAX V |                             |                                                |                                                               |                                                 |                                              |                                                              |
| P6KE6.8 | 6.45              | 6.8   | 7.14  | 10                          | 5.8                                            | 1000                                                          | 10.5                                            | 57                                           | 0.057                                                        |
| P6KE7.5 | 7.13              | 7.5   | 7.88  | 10                          | 6.4                                            | 500                                                           | 11.3                                            | 53                                           | 0.061                                                        |
| P6KE8.2 | 7.79              | 8.2   | 8.61  | 10                          | 7.02                                           | 200                                                           | 12.1                                            | 50                                           | 0.065                                                        |
| P6KE9.1 | 8.65              | 9.1   | 9.55  | 1.0                         | 7.78                                           | 50                                                            | 13.4                                            | 45                                           | 0.068                                                        |
| P6KE10  | 9.5               | 10    | 10.5  | 1.0                         | 8.55                                           | 10                                                            | 14.5                                            | 41                                           | 0.073                                                        |
| P6KE11  | 10.5              | 11    | 11.6  | 1.0                         | 9.4                                            | 5.0                                                           | 15.6                                            | 38                                           | 0.075                                                        |
| P6KE12  | 11.4              | 12    | 12.6  | 1.0                         | 10.2                                           | 5.0                                                           | 16.7                                            | 36                                           | 0.078                                                        |
| P6KE13  | 12.4              | 13    | 13.7  | 1.0                         | 11.1                                           | 5.0                                                           | 18.2                                            | 33                                           | 0.081                                                        |
| P6KE15  | 14.3              | 15    | 15.8  | 1.0                         | 12.8                                           | 5.0                                                           | 21.2                                            | 28                                           | 0.084                                                        |
| P6KE16  | 15.2              | 16    | 16.8  | 1.0                         | 13.6                                           | 5.0                                                           | 22.5                                            | 27                                           | 0.086                                                        |
| P6KE18  | 17.1              | 18    | 18.9  | 1.0                         | 15.3                                           | 5.0                                                           | 25.2                                            | 24                                           | 0.088                                                        |
| P6KE20  | 19.0              | 20    | 21.0  | 1.0                         | 17.1                                           | 5.0                                                           | 27.7                                            | 22                                           | 0.090                                                        |
| P6KE22  | 20.9              | 22    | 23.1  | 1.0                         | 18.8                                           | 5.0                                                           | 30.6                                            | 20                                           | 0.092                                                        |
| P6KE24  | 22.8              | 24    | 25.2  | 1.0                         | 20.5                                           | 5.0                                                           | 33.2                                            | 18                                           | 0.094                                                        |
| P6KE27  | 25.7              | 27    | 28.4  | 1.0                         | 23.1                                           | 5.0                                                           | 37.5                                            | 16                                           | 0.096                                                        |
| P6KE30  | 28.5              | 30    | 31.5  | 1.0                         | 25.6                                           | 5.0                                                           | 41.4                                            | 14.4                                         | 0.097                                                        |
| P6KE33  | 31.4              | 33    | 34.7  | 1.0                         | 28.2                                           | 5.0                                                           | 45.7                                            | 13.2                                         | 0.098                                                        |
| P6KE36  | 34.2              | 36    | 37.8  | 1.0                         | 30.8                                           | 5.0                                                           | 49.9                                            | 12                                           | 0.099                                                        |
| P6KE39  | 37.1              | 39    | 41    | 1.0                         | 33.3                                           | 5.0                                                           | 53.9                                            | 11.2                                         | 0.100                                                        |
| P6KE43  | 40.9              | 43    | 45.2  | 1.0                         | 36.8                                           | 5.0                                                           | 59.3                                            | 10.1                                         | 0.101                                                        |

Notes: (1) Non-repetitive 10x1,000 $\mu\text{s}$  pulse.

R1 (8-September 2011)

P6KE6.8A THRU P6KE440A  
P6KE6.8CA THRU P6KE440CA


UNI-DIRECTIONAL  
AND BI-DIRECTIONAL  
SILICON TRANSIENT  
VOLTAGE SUPPRESSORS  
600 WATTS, 6.8 THRU 440 VOLTS



**ELECTRICAL CHARACTERISTICS - Continued:** ( $T_A=25^{\circ}\text{C}$  unless otherwise noted)

| TYPE    | BREAKDOWN VOLTAGE<br>$V_{BR} @ I_T$ |       |       | TEST CURRENT<br>$I_T$ | WORKING PEAK REVERSE VOLTAGE<br>$V_{RWM}$ | MAXIMUM REVERSE LEAKAGE CURRENT<br>$I_R @ V_{RWM}$ | MAXIMUM CLAMPING VOLTAGE<br>$V_C @ I_{PP}$ | PEAK PULSE CURRENT<br>(Note 1)<br>$I_{PP}$ | MAXIMUM TEMPERATURE COEFFICIENT<br>$\Theta V_{BR}$ |
|---------|-------------------------------------|-------|-------|-----------------------|-------------------------------------------|----------------------------------------------------|--------------------------------------------|--------------------------------------------|----------------------------------------------------|
|         | MIN V                               | NOM V | MAX V |                       |                                           |                                                    |                                            |                                            |                                                    |
| P6KE47  | 44.7                                | 47    | 49.4  | 1.0                   | 40.2                                      | 5.0                                                | 64.8                                       | 9.3                                        | 0.101                                              |
| P6KE51  | 48.5                                | 51    | 53.6  | 1.0                   | 43.6                                      | 5.0                                                | 70.1                                       | 8.6                                        | 0.102                                              |
| P6KE56  | 53.2                                | 56    | 58.8  | 1.0                   | 47.8                                      | 5.0                                                | 77                                         | 7.8                                        | 0.103                                              |
| P6KE62  | 58.9                                | 62    | 65.1  | 1.0                   | 53.0                                      | 5.0                                                | 85                                         | 7.1                                        | 0.104                                              |
| P6KE68  | 64.6                                | 68    | 71.4  | 1.0                   | 58.1                                      | 5.0                                                | 92                                         | 6.5                                        | 0.104                                              |
| P6KE75  | 71.3                                | 75    | 78.8  | 1.0                   | 64.1                                      | 5.0                                                | 103                                        | 5.8                                        | 0.105                                              |
| P6KE82  | 77.9                                | 82    | 86.1  | 1.0                   | 70.1                                      | 5.0                                                | 113                                        | 5.3                                        | 0.105                                              |
| P6KE91  | 86.5                                | 91    | 95.5  | 1.0                   | 77.8                                      | 5.0                                                | 125                                        | 4.8                                        | 0.106                                              |
| P6KE100 | 95.0                                | 100   | 105   | 1.0                   | 85.5                                      | 5.0                                                | 137                                        | 4.4                                        | 0.106                                              |
| P6KE110 | 104.5                               | 110   | 115.5 | 1.0                   | 94.0                                      | 5.0                                                | 152                                        | 4.0                                        | 0.107                                              |
| P6KE120 | 114                                 | 120   | 126   | 1.0                   | 102                                       | 5.0                                                | 165                                        | 3.6                                        | 0.107                                              |
| P6KE130 | 123.5                               | 130   | 136.5 | 1.0                   | 111                                       | 5.0                                                | 179                                        | 3.3                                        | 0.107                                              |
| P6KE150 | 142.5                               | 150   | 157.5 | 1.0                   | 128                                       | 5.0                                                | 207                                        | 2.9                                        | 0.108                                              |
| P6KE160 | 152                                 | 160   | 168   | 1.0                   | 136                                       | 5.0                                                | 219                                        | 2.7                                        | 0.108                                              |
| P6KE170 | 161.5                               | 170   | 178.5 | 1.0                   | 145                                       | 5.0                                                | 234                                        | 2.6                                        | 0.108                                              |
| P6KE180 | 171                                 | 180   | 189   | 1.0                   | 154                                       | 5.0                                                | 246                                        | 2.4                                        | 0.108                                              |
| P6KE200 | 190                                 | 200   | 210   | 1.0                   | 171                                       | 5.0                                                | 274                                        | 2.2                                        | 0.108                                              |
| P6KE220 | 209                                 | 220   | 231   | 1.0                   | 185                                       | 5.0                                                | 328                                        | 2.0                                        | 0.108                                              |
| P6KE250 | 237.5                               | 250   | 262.5 | 1.0                   | 214                                       | 5.0                                                | 344                                        | 2.0                                        | 0.110                                              |
| P6KE300 | 285                                 | 300   | 315   | 1.0                   | 256                                       | 5.0                                                | 414                                        | 2.0                                        | 0.110                                              |
| P6KE350 | 332.5                               | 350   | 367.5 | 1.0                   | 300                                       | 5.0                                                | 482                                        | 2.0                                        | 0.110                                              |
| P6KE400 | 380                                 | 400   | 420   | 1.0                   | 342                                       | 5.0                                                | 548                                        | 2.0                                        | 0.110                                              |
| P6KE440 | 418                                 | 440   | 462   | 1.0                   | 376                                       | 5.0                                                | 600                                        | 2.0                                        | 0.110                                              |

#### DO-15 CASE - MECHANICAL OUTLINE



| SYMBOL | DIMENSIONS |       |             |      |
|--------|------------|-------|-------------|------|
|        | INCHES     |       | MILLIMETERS |      |
|        | MIN        | MAX   | MIN         | MAX  |
| A      | 0.028      | 0.034 | 0.71        | 0.86 |
| B      | 0.230      | 0.300 | 5.84        | 7.62 |
| C      | 0.104      | 0.140 | 2.64        | 3.56 |
| D      | 1.000      | -     | 25.40       | -    |

DO-15 (REV: R1)

**MARKING: FULL PART NUMBER**  
Bi-directional devices shall not be marked with a Cathode band.

R1 (8-September 2011)

## OUTSTANDING SUPPORT AND SUPERIOR SERVICES



---

### PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

---

### DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2<sup>nd</sup> day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

---

### REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix " TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix " PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

---

### CONTACT US

#### Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.  
145 Adams Avenue  
Hauppauge, NY 11788 USA  
Main Tel: (631) 435-1110  
Main Fax: (631) 435-1824  
Support Team Fax: (631) 435-3388  
[www.centrasemi.com](http://www.centrasemi.com)

**Worldwide Field Representatives:**  
[www.centrasemi.com/wwreps](http://www.centrasemi.com/wwreps)

**Worldwide Distributors:**  
[www.centrasemi.com/wwdistributors](http://www.centrasemi.com/wwdistributors)

---

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: [www.centrasemi.com/terms](http://www.centrasemi.com/terms)