

745335

- 2

Product Details



745335

- 2

Obsolete

Search for Replacement Parts

Standard Board Mount Connectors

Not EU RoHS or ELV Compliant

Product Highlights:

? Number of Positions = 9

? Receptacle

? PCB Mount Angle = Vertical

? Product Series = HDP -20

? Without Mating Connector Lock

View all Features

|

Find Similar Products

Live Product Chat

US Only

8:30am - 5pm ET, Mon - Fri

Quick Links

- Check Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Documentation & Additional Information

Product Drawings: ? None Available Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling
---	--

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features: ? Number of Positions = 9 ? Gender = Receptacle ? PCB Mount Angle = Vertical ? Product Series = HDP -20 ? Mating Connector Lock = Without ? PCB Retention Feature = Yes ? Shell Type = All Plastic ? Shell Size = 1 ? PCB Thickness (in [mm]) = 0.063 [1.60] ? Grounding Indents = Without ? Grounding Straps = Without ? PCB Mount Style = Thru Hole ? Color Code = None ? Sealed = No ? Mounting Hole Diameter (mm [in]) = 3.10 [.122] ? Color = Black Mechanical Attachment: ? Panel Attachment = Without Termination Related Features: ? Grounding Clips = Without ? Termination (Solder) Post Length (mm [in]) = 5.80 [0.228] ? Solder Tail Contact Plating = Bright Tin -Lead	Body Related Features: ? PCB Retention Method = ACTION (Compliant) Press -fit Posts ? Insert Flammability Rating = UL 94V -0 Contact Related Features: ? Contact Mating Area Plating Material = Gold (30) ? Contact Material = Copper Alloy Housing Related Features: ? Housing Material = Thermoplastic Industry Standards: ? RoHS/ELV Compliance = Not ELV/RoHS compliant ? Lead Free Solder Processes = Not suitable for lead free processing Operation/Application: ? Application = Standard Other: ? Brand = AMP
--	---