


Duplex Singlemode 8.3/125 Fiber Patch Cable (SC/SC), 3M (10-ft.)

MODEL NUMBER: **N356-03M**



Description

Tripp Lite's 3-meter, single mode duplex fiber optic SC/SC patch cable is manufactured from 8.3/125 zipcord fiber. The cable has SC connectors on each end, a PVC jacket, and is FDDI and OFNR rated. Duplex single mode fiber is most commonly used in LAN applications.

Features

- Manufactured from 8.3/125 duplex (zipcord) fiber
- PVC jacket
- Length: 3-meter. Connectors: 2 SC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Clad Diameter	125 micron
Core Diameter	8.3 micron

Highlights

- Premium PVC 8.3/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

Applications

- Networking equipment that requires single mode fiber optic patch cables

System Requirements

- Any fiber optic hardware or NIC card requiring singlemode duplex cable with SC/SC connectors

Package Includes

- 3-meter Duplex Single mode Fiber Patch Cable, SC/SC

Fiber Type	8.3/125
Number of Fibers	2
Intended Application	Computer Networking (Fiber)
Cable Type	SINGLEMODE 8.3/125 FIBER OPTIC
Model Type	SC/SC
INPUT	
Cable Length (m)	3
UPC ASSIGNMENT	
Unit Carton UPC#	037332098047
PHYSICAL	
Color	Yellow
Style	Fiber Optic
CONNECTIONS	
Connector A	SC
Connector B	SC
Number of Connectors	4
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.