

## ENERGIZER CR1216

## Lithium Coin




### Industry Standard Dimensions

mm (inches)



This Battery has Underwriters Laboratories component Recognition




### Simulated Application test

Typical Performance at 21°C (70°F)

Schedule:	Typical Drains: at 2.85V (mA)	Load (ohms)	Cutoff 2.0V (hours)
Continuous	0.046	62,000	739

### Typical Discharge Characteristics

Load: 62,000 ohms - Continuous  
Typical Drain @ 2.85V: 0.046 mA




### Internal Resistance Characteristics

Pulse Test at 21°C (70°F)

**Bkgnd Drain:** Continuous  
62K ohms  
0.046 mA @ 2.85V

**Pulse Drain:** 2 seconds X 12 times/day  
1K ohms  
2.8 mA @ 2.8V



### Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.  
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.