



DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2070	A	Released	JN	09-03-09	JWM	09-03-09	JWM	09-03-09



Specification

1. Rated Voltage: 12VDC
2. Operating Voltage: 8 ~ 15VDC
3. Max. Rated Current: 20mA at 12VDC
4. Min. Sound Pressure Level: 100dB at 12VDC/10cm
5. Resonant Frequency: 3.7±0.5KHz
6. Tone Nature: Continuous
7. Case Material: PBT/Black
8. Operating Temperature: -20~+80°C
9. Store Temperature: -30~+100°C
10. Weight: 7g

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY: Jason Nash DATE: 09-03-09
CHECKED BY: Jason Nash DATE: 09-03-09
APPROVED BY: Jason Nash DATE: 09-03-09

DRAWING TITLE: Piezo Buzzer & Transducer
SIZE DWG. NO. ELECTRONIC FILE REV
A MCKPI-G2437-3671 25R0648.dwg A
SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1