


Switches &gt; Tactile Switches

Actuator Style: **Extended, Top Actuator**Operating Function: **Off (On)**Contact Base Material: **Stainless Steel**Switch Contact Plating Material: **Silver**Contact Current Rating: **5 mA**

## Features

### Product Type Features

Leg Style

Gull Wing

Actuator Style

Extended, Top Actuator

### Configuration Features

Switch Feedback Type

Non-Tactile

ESD Grounding Terminal

Without

Ganged

Without

Operating Function

Off (On)

Configuration (Pole-Throw)

Single Pole - Single Throw

Number of Actuators

Single

### Body Features

Actuator Material

Thermoplastic

Actuator Force

35 g[1.23 oz]

Product Orientation

Vertical

### Contact Features

Contact Base Material	Stainless Steel
Switch Contact Plating Material	Silver
Contact Current Rating	5 mA

### Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

### Housing Features

Process Sealed	No
----------------	----

### Usage Conditions

Operating Temperature Range	-20 – 70 °C[-4 – 158 °F]
-----------------------------	--------------------------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 2331394-1  
DET SW4.7X3.5X2.25 GW VERT. NOH  
AG RL



TE Part # 2331393-1  
DET SW5.7X4.0X2.0 GW HORZ. NO  
AG RL



TE Part # 2331365-1  
DET SW4.7X3.8X2.3 GW VERT. NO  
AG RL




TE Part # 2331370-1  
DET SW4.7X3.8X2.3 GW VERT. NO  
AG RL



TE Part # 2331398-1  
DET SW6.5X3.9X6.0 GW VERT. NO  
AG TB

## Also in the Series | ALCOSWITCH JJ



Tactile Switches(52)

## Customers Also Bought



TE Part #2345986-1  
USB TYPE C 3.1 TOP MOUNT DUAL  
SMT 1.63CH

## Documents

### Product Drawings

[DET SW6.5X3.9X6.0 GW VERT. NO AG RL](#)

English

### CAD Files

[3D PDF](#)

3D

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2331400-2\\_A.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2331400-2\\_A.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2331400-2\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[JJ Series Detector Switches Data Sheet](#)

English