


The copying, distribution and utilisation of this document as well as the communication of the contents to others without expressed authorization is prohibited according to §18 UWG German Law. Offenders will be held liable for the payment of damages according to §19 UWG German Law. All rights reserved. In particular the right to carry out patent, utility model or ornamental design registrations.

Mechanical data (according to IEC 61076-2-101)		Material	
no. of poles / coding	8 / A	contacts / surface	CuZn with gold layer
contact termination	dip solder / socket	contact carrier	PA6T/66
contact-Ø	8xØ0.8mm	colour	black
temperature range	-40 °C to +85 °C	sealing gasket	FKM
protection class	IP67		
mating cycles	>100		


further information:
- see technical data M12-3



All specified data refers to the mounted M12 installation plugs ≥ IP54 and requires that the connector pair be correctly plugged and locked. Influences from wires, cables or PCB mounting are also to be taken into consideration.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts gem §18 UWG verboten. soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadensersatz (§19 UWG). Alle Rechte vorbehalten, insbesondere das Recht, Patent-, Gebrauchsmuster- oder Geschmacksmusteranmeldungen durchzuführen. CONINVERS GmbH Heisenbergstrasse 1 D-71083 Herrenberg

drilling plan
component side (front view PC-Board)



general tolerance acc. to DIN ISO 2768-c			technical changes reserved		Index 1 / 2012-07-05		scale: 2:1		
	date	name	Series DSIV M12-installation plug straight 8-pole socket/A-coding/SC0/o-ring					page: 1 of: 2	
design	2012-07-05	Thumm							
chk.									
			drawing-no.:	BS-08S2NB2M100		doc.-no.:	00671279		
			order-no.:	1542790					
			article designation:	SACC-DSIV-FS-8CON-L180 SCOTHR					




The copying, distribution and utilization of this document as well as the communication of the contents to others without expressed authorization is prohibited according to §18 UWG German Law. Offenders will be held liable for the payment of damages according to §19 UWG German Law. All rights reserved, in particular the right to carry out patent, utility model or ornamental design registrations.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts gem §18 UWG verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz (§19 UWG). Alle Rechte vorbehalten, insbesondere das Recht, Patent-, Gebrauchsmuster- oder Geschmacksmusteranmeldungen durchzuführen.

CONINVERS GmbH Heisenbergstrasse 1 D-71083 Herrenberg

Mechanical data (according to IEC 61076-2-101)	
Locking thread	M12 SPEEDCON
Material	
flange housing	GD-Zn, nickel-plated
sealing gasket	EPDM
nut	brass, nickel-plated
temperature range	-40 °C to +85 °C

further information:
- see installation recommendation SACC-M12-SCO NUT



All specified data refers to the mounted M12 installation plugs ≥ IP54 and requires that the connector pair be correctly plugged and locked. Influences from wires, cables or PCB mounting are also to be taken into consideration.

general tolerance acc. to DIN ISO 2768-c			technical changes reserved		Index 1 / 2012-07-05		scale: 2:1		
	date	name	Series DSIV M12-installation plug straight 8-pole socket/A-coding/SC0/o-ring					page: 2 of: 2	
design	2012-07-05	Thumm							
chk.									
			drawing-no.:		BS-08S2NB2M100		doc.-no.: 00671279		
			order-no.:		1542790				
			article designation:		SACC-DSIV-FS-8CON-L180 SC0THR				