

## 3M™ Pedestal Stand 749

The Pedestal Stand 749 can be used with 3M™ Wrist Strap Testers 740, 747 and 746. The Pedestal Stand 749 is made of stainless steel for durability and has a tip-over angle of greater than 45 degrees. Its unique top plate can support any of the 3M Wrist Strap Testers, and it can accommodate certain models of barcode and magnetic readers.

Designed for use in manufacturing areas, this unit is designed to be self-supporting, stand alone and portable. The base plate is joined to the support column by stainless steel bolts and has insulated washers to keep the operator from bypassing the grounding wire and creating an electrical short. This feature helps guard against a false reading by creating a second path for the circuit.

### Includes:

- Stand pole (4.32 H x 8.38 W x 11.68 H cm)
- Base
- Hardware
- Ground wire
- Instructions


### Specifications

Weight	9 lbs.
Assembled Height	40.5 inches
Construction	Stainless Steel



### Assembly Instructions

1. Run grounding cable (ring terminal end) through top plate and through support column. For 3M™ Wrist Strap Tester 740, use cable included in this kit. For 3M™ Wrist Strap Testers 747, use the wire packaged with that Wrist Strap Tester.
2. Make sure that grounding cable is also placed through the isolation gasket.
3. Secure the ground cable ring terminal to the base plate using the bolts provided (fasten to center hole).
4. Install the isolation sleeves inside the pre-drilled holes at the base of the support column. Next, insert a washer/head bolt into the sleeve and hand tighten by turning the bolt clockwise onto the threaded hole at the base of the support column. Use a Phillips Head screwdriver to tighten the assembly.
5. Adhere the provided 3M™ Dual Lock™ Reclosable Fasteners on both the top plate and the 3M Wrist Strap Tester. Place tester over top plate and push down to adhere both strips of Dual Lock Fasteners to each other. Make sure that tester and top plate assembly make a tight bond.



3M and Dual Lock are trademarks of 3M Company.

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



### Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive  
Sanford, NC 27332-9733  
Toll-Free: 866-722-3736  
International: 919-718-0000  
Email: 3mstaticinfo@mmm.com  
www.3Mstatic.com

Please recycle. Printed in USA.  
© 3M 2014. All rights reserved.  
78-9102-1911-8 JHA