




LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			S	REVISED PER ECR-20-000541	15MAY2020	PC	SW



LEADER	71.12	[2.800]	28	5-641198-8
	68.58	[2.700]	27	5-641198-7
	66.04	[2.600]	26	5-641198-6
	63.50	[2.500]	25	5-641198-5
	60.96	[2.400]	24	5-641198-4
	58.42	[2.300]	23	5-641198-3
	55.88	[2.200]	22	5-641198-2
	53.34	[2.100]	21	5-641198-1
	50.80	[2.000]	20	5-641198-0
	48.26	[1.900]	19	4-641198-9
	45.72	[1.800]	18	4-641198-8
	43.18	[1.700]	17	4-641198-7
	40.64	[1.600]	16	4-641198-6
	38.10	[1.500]	15	4-641198-5
	35.56	[1.400]	14	4-641198-4
	33.02	[1.300]	13	4-641198-3
	30.48	[1.200]	12	4-641198-2
	27.94	[1.100]	11	4-641198-1
	25.40	[1.000]	10	4-641198-0
	22.86	[.900]	9	3-641198-9
	20.32	[.800]	8	3-641198-8
	17.78	[.700]	7	3-641198-7
	15.24	[.600]	6	3-641198-6
	12.70	[.500]	5	3-641198-5
	10.16	[.400]	4	3-641198-4
	7.62	[.300]	3	3-641198-3
5.08	[.200]	2	3-641198-2	
DIM A			NO.OF POSN	ASSEMBLY

SUPERCEDED




SUPERCEDED



SUPERCEDED



LEADS CONTAINING COORDINATES	71.12 [2.800]	28	-2-641198-8
	68.58 [2.700]	27	-2-641198-7
	66.04 [2.600]	26	-2-641198-6
	63.50 [2.500]	25	-2-641198-5
	60.96 [2.400]	24	-2-641198-4
	58.42 [2.300]	23	-2-641198-3
	55.88 [2.200]	22	-2-641198-2
	53.34 [2.100]	21	-2-641198-1
	50.80 [2.000]	20	-2-641198-0
	48.26 [1.900]	19	-1-641198-9
	45.72 [1.800]	18	-1-641198-8
	43.18 [1.700]	17	-1-641198-7
	40.64 [1.600]	16	-1-641198-6
	38.10 [1.500]	15	-1-641198-5
	35.56 [1.400]	14	-1-641198-4
	33.02 [1.300]	13	-1-641198-3
	30.48 [1.200]	12	-1-641198-2
	27.94 [1.100]	11	-1-641198-1
	25.40 [1.000]	10	1-641198-0
	22.86 [.900]	9	—641198-9
	20.32 [.800]	8	—641198-8
	17.78 [.700]	7	—641198-7
	15.24 [.600]	6	—641198-6
	12.70 [.500]	5	641198-5
10.16 [.400]	4	—641198-4	
7.62 [.300]	3	—641198-3	
5.08 [.200]	2	641198-2	
DIM A		NO.OF POSN	ASSEMBLY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 20-DEC-2004 CHK D. ROSSI 20-DEC-2004 APP'D D. ROSSI 20-DEC-2004		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME MTA .100 CONNECTOR ASSEMBLY, 22 AWG, STANDARD	
		PRODUCT SPEC		APPLICATION SPEC	
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO A1 00779 C 641198	
				RESTRICTED TO	
FINISH		CUSTOMER DRAWING		SCALE 6:1 SHEET 1 of 1 REV S	