



Micro Commercial Components

Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

Features

- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix designates RoHS Compliant. See ordering information)
- High temperature metallurgically bonded construction
- Glass passivated cavity-free junction
- 2.0 amperes operation at $T_A=55^{\circ}\text{C}$ and with no thermal runaway. Typical I_R less than 0.2uA
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0 and MSL Rating 1

Maximum Ratings

- Operating Temperature: -55°C to $+150^{\circ}\text{C}$
- Storage Temperature: -55°C to $+150^{\circ}\text{C}$
- Typical Thermal Resistance: 22°C/W Junction to Ambient

MCC Part Number	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
RGP20A	50V	35V	50V
RGP20B	100V	70V	100V
RGP20D	200V	140V	200V
RGP20G	400V	280V	400V
RGP20J	600V	420V	600V
RGP20K	800V	560V	800V
RGP20M	1000V	700V	1000V

Electrical Characteristics @ 25°C Unless Otherwise Specified


Maximum Average Forward Current	$I_{F(AV)}$	2.0 A	$T_A = 55^{\circ}\text{C}$
Peak Forward Surge Current	I_{FSM}	80A	8.3ms, half sine
Maximum Instantaneous Forward Voltage	V_F	1.3V	$I_{FM} = 2.0\text{A};$ $T_A=25^{\circ}\text{C}$
Maximum DC Reverse Current At Rated DC Blocking Voltage	I_R	5.0uA 200uA	$T_A=25^{\circ}\text{C}$ $T_A=125^{\circ}\text{C}$
Maximum Reverse Recovery Time RGP20A-20G RGP20J RGP20K-20M	T_{rr}	150nS 250nS 500nS	$I_F=0.5\text{A}, I_R=1.0\text{A},$ $I_r=0.25\text{A}$
Typical Junction Capacitance	C_J	35pF	Measured at $f=1.0\text{MHz}$ $V_R=4.0\text{V}$

Notes:1.High Temperature Solder Exemption Applied, see EU Directive Annex 7.

RGP20A THRU RGP20M

2.0 Amp Glass Passivated Junction Fast Recovery Rectifiers 50 to 1000 Volts




DO-201AE



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	---	.370	---	9.50	
B	---	.250	---	6.40	
C	.038	.042	0.96	1.06	
D	1.000	---	25.40	---	

RGP20A thru RGP20M

Figure 1
Typical Forward Characteristics



RGP20A thru RGP20M





Figure 5
Reverse Recovery Time Characteristic And Test Circuit Diagram



Ordering Information

Device	Packing
(Part Number)-TP	Tape&Reel; 1.2Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . *Micro Commercial Components Corp.* does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp.* and all the companies whose products are represented on our website, harmless against all damages.

APPLICATIONS DISCLAIMER

Products offer by *Micro Commercial Components Corp.* are not intended for use in Medical, Aerospace or Military Applications.