




PRODUCT NUMBER

77336-YXXLF


- LEAD FREE, SEE NOTE 5.
- TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2
- OPTIONAL STRAIN RELIEF
SEE SHEET 2

NOTES:


- MATERIAL: BASE AND COVER: 30% GLASS FILLED POLYESTER FLAME RETARDANT PER UL-94-V0
COLOUR GREY
STRAIN RELIEF: UNREINFORCED THERMOPLASTIC FLAME RETARDANT PER UL-94-V0
COLOUR GREY
CONTACT: BERYLLIUM COPPER
- PLATING: 0.76µm Au OVER 1.27 µm Ni MIN
IN CONTACT AREA, REMAINDER OF PRODUCT (IDC PART) 1.27µm Ni MIN.
- TRIANGLE NOT MOLDED-IN ON 2x2 AND 2x3 POSITIONS WITH CENTRAL KEY
- FOR PRINTING SPECIFICATION SEE TA 812.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.

mat'l. code SEE NOTES		surface ISO 1302	tolerance ISO 416 ISO 1101	projection ISO 1101	product family 2.54MM IDC
lfr	ecn no	dr	date	tolerances unless otherwise specified	title
X	F08-0270	LMU	06.08.12	angles	XXX ±0.3
Y	F06-0274	LMU	06.09.25	Linear	XXX ±0.13
					XXX ±0.05
T	F20556	DLE	02.10.11	dr	P NIZZI
U	F03019	DLE	03.01.23	engr	JM PHAMVAN
V	F04-0166	LMU	04.04.08	chr	O MATHEVON
W	F05-0109	JCO	05.01.17	appd	JM P
sheet	revision	Y	V		
index	sheet	1	2		
				scale 5:1	dwg no
					sheet 1 of 2
					size
					Az
					type
					CUSTOMER Drawing


PRODUCT NUMBER	SIZE	DIM "A"	DIM "B"	DIM "C"	DIM "S"	SLOT STYLE
77336-X04LF	2x 2	9.54	2.54	9.46	5.66	NO SLOT
77336-X06LF	2x 3	12.08	5.08	12.00	8.20	RIGHT IF NO KEY
77336-X08LF	2x 4	14.62	7.62	14.54	10.74	RIGHT IF NO KEY
77336-X10LF	2x 5	17.16	10.16	17.08	13.28	RIGHT SLOT
77336-X14LF	2x 7	22.24	15.24	22.16	18.36	RIGHT SLOT
77336-X16LF	2x 8	24.78	17.78	24.70	20.90	2 SLOTS
77336-X18LF	2x 9	27.32	20.32	27.24	23.44	2 SLOTS
77336-X20LF	2x 10	29.86	22.86	29.78	25.98	2 SLOTS
77336-X24LF	2x 12	34.94	27.94	34.85	31.06	2 SLOTS
77336-X26LF	2x 13	37.48	30.48	37.40	33.60	2 SLOTS
77336-X30LF	2x 15	42.56	35.56	42.48	38.68	2 SLOTS
77336-X34LF	2x 17	47.64	40.64	47.56	43.76	2 SLOTS
77336-X40LF	2x 20	55.26	48.26	55.18	51.38	2 SLOTS
77336-X44LF	2x 22	60.34	53.34	60.26	56.46	2 SLOTS
77336-X50LF	2x 25	67.96	60.96	67.88	64.08	2 SLOTS
77336-X60LF	2x 30	80.66	73.66	80.58	76.78	2 SLOTS
77336-X64LF	2x 32	85.74	78.74	85.66	81.86	2 SLOTS




WITHOUT STRAIN RELIEF



WITH LOW PROFILE STRAIN RELIEF



WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF

AFTER TERMINATION SIDE VIEW OF ASSEMBLY (* LATCHING DIM ON HEADER)

77336-7YYLF		⊙				⊙	724
77336-6YYLF	⊙					⊙	624
77336-5YYLF		⊙			⊙		504 524 530
77336-4YYLF		⊙		⊙			
77336-3YYLF		⊙	⊙				304
77336-2YYLF	⊙				⊙		204 224 230
77336-1YYLF	⊙			⊙			
77336-0YYLF	⊙		⊙				004
PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT CENTRAL KEY	STANDARD	WITHOUT STRAIN RELIEF	LOW PROFILE	LATCHING	DASHES NOT AVAILABLE

mat'L code				surface ISO 1302		tolerance ISO 416 ISO 1101		projection		product family	
lfr	ecr	no	dr	date	tolerances unless otherwise specified	angles	Linear	mm [inch]		QKIE FEM	
P	F50100	PNZ	95.02.07							title EURO QUICKIE 0.76 µm Au	
R	F10586	DLE	01.10.24								
S	F20194	DLE	02.04.10							scale N/A	
T	F03019	DLE	03.01.23	dr	P NIZZI	94.02.10				dwg no 77336	
U	F06-0270	LMU	06.09.12	engr	JM PHAMVAN	94.02.10					
V	F06-0274	LMU	06.09.25	chr	O MATHEVON	91.10.31				type CUSTOMER Drawing	
				appo	JM P	94.02.10					
sheet index	revision sheet										