

Double cassette tape recorder system preamplifier

BA3426AS

The BA3426AS is a record/playback system preamplifier for radio cassette decks. It also has a CD input. It has three control switches for function and tape mode switching and mic on/off.

It requires far fewer external components than its predecessors which means simplified assembly and overall savings.

●Applications

Dual-cassette radio cassette players.

●Features

- 1) Built-in switch for recording/playback equalize.
- 2) Motor control output provided.
- 3) CD input.
- 4) Smoothing capacitors to suppress switching noise are not required.
- 5) Built-in bias oscillator transistor.

●Absolute maximum ratings (Ta = 25°C)


| Parameter | Symbol | Limits | Unit |
|-----------------------|------------------|----------|------|
| Power supply voltage | V _{CC} | 9 | V |
| Power dissipation | P _d | 1250*1 | mW |
| Operating temperature | T _{opr} | -10~+75 | °C |
| Storage temperature | T _{stg} | -55~+125 | °C |

* Reduced by 12.5mW for each increase in Ta of 1°C over 25°C.

●Recommended operating conditions (Ta = 25°C)

| Parameter | Symbol | Min. | Typ. | Max. | Unit |
|----------------------|-----------------|------|------|------|------|
| Power supply voltage | V _{CC} | 4.5 | — | 7.0 | V |

● Block diagram



● Pin descriptions

| Pin No. | Pin name | Function |
|---------|------------|--|
| 1 | A-L | Tape A input (L ch) |
| 2 | Tape-NF-L | Playback equalizer amplifier negative input (L ch) |
| 3 | Tape-O-L | Playback equalizer amplifier output (L ch) |
| 4 | A-R | Tape A input (R ch) |
| 5 | Tape-NF-R | Playback equalizer amplifier negative input (R ch) |
| 6 | Tape-O-R | Playback equalizer amplifier output (R ch) |
| 7 | Mic/HS | Int/Ext mic switch, motor control |
| 8 | Mic-NF | Microphone amplifier negative input |
| 9 | Mic-IN | Microphone amplifier input |
| 10 | Radio-IN-L | Radio input (L ch) |
| 11 | Radio-IN-R | Radio input (R ch) |
| 12 | CD-IN-L | CD input (L ch) |
| 13 | CD-IN-R | CD input (R ch) |
| 14 | Line-Out-L | Line amplifier (L ch) |
| 15 | Line-Out-R | Line amplifier (R ch) |
| 16 | Bias-IN | Bias input |
| 17 | Vcc | Power supply |
| 18 | GND | Substrate GND |
| 19 | Bias | Operating reference point |
| 20 | τ | Transient mute, ALC time constant |
| 21 | LPF-R | Low-pass filter (R ch) |
| 22 | LPF-L | Low-pass filter (L ch) |
| 23 | Rec-NF-R | ALC amplifier negative feedback (R ch) |
| 24 | Rec-NF-L | ALC amplifier negative feedback (L ch) |
| 25 | Rec-EQ-R | Recording equalizer amplifier negative feedback (R ch) |
| 26 | Rec-EQ-L | Recording equalizer amplifier negative feedback (L ch) |
| 27 | Fnc | Function switch |
| 28 | Tape-Mode | Tape mode switch |
| 29 | Tr-C | Bias oscillator transistor (collector) |
| 30 | Tr-B | Bias oscillator transistor (base) |
| 31 | B-R | Tape B input and recording equalizer amplifier output (R ch) |
| 32 | B-L | Tape B input and recording equalizer amplifier output (L ch) |

- Electrical characteristics (unless otherwise noted, $T_a = 25^\circ\text{C}$, $V_{CC} = 5.5\text{V}$, $f = 1\text{kHz}$, $R_g = 680\Omega$,
Tape input = -66dBm , Mic. input = -50dBm , and Radio input = -23dBm ,
and CD input = -12dBm)

| Parameter | Symbol | Min. | Typ. | Max. | Unit | Symbol* | Conditions |
|---------------------------------------|------------|-------|------|------|---------------|---------|--------------------------------|
| Quiescent current | I_Q | — | 28 | 36 | mA | TAE | |
| Voltage gain | | | | | | | |
| Mic \sim Line | GvcML | 28 | 31 | 34 | dB | TNM | |
| Radio \sim Line | GvcRL | 1 | 4 | 7 | dB | RAE | |
| CD \sim Line | GvcCL | -10 | -7 | -4 | dB | CAE | |
| Radio \sim Rec | GvcRR | 13 | 16 | 19 | dB | RNE | |
| CD \sim Rec | GvcCR | 2 | 5 | 8 | dB | CNE | |
| Tape \sim Line | GvcTL1 | 54 | 57 | 60 | dB | TAE | $V_{IN}=76\text{dBm}$, 315Hz |
| Tape \sim Line | GvcTL2 | 41.6 | 44 | 46.4 | dB | TAE | $V_{IN}=-63\text{dBm}$, 10kHz |
| Maximum output voltage | | | | | | | Mic input |
| Line Out | V_{OML} | 2.5 | 4.5 | — | dBm | TNM | THD=1% |
| Rec Out | V_{OMR} | 2.0 | 4.0 | — | dBm | TNM | THD=3%, ALC OFF |
| Total harmonic distortion | | | | | | | |
| Mic \sim Line | THD ML | — | 0.08 | 0.5 | % | TNM | |
| Radio \sim Line | THD RL | — | 0.02 | 0.5 | % | RNE | |
| CD \sim Line | THD CL | — | 0.02 | 0.5 | % | CNE | |
| Radio \sim Rec | THD RR | — | 0.2 | 0.7 | % | RNE | ALC OFF |
| CD \sim Rec | THD CR | — | 0.2 | 0.7 | % | CNE | ALC OFF |
| Tape \sim Line | THD TL | — | 0.1 | 0.7 | % | TAE | |
| Input conversion noise voltage (Tape) | V_{NINT} | — | 0.8 | 1.6 | μV_{rms} | TAE | DIN AUDIO Line Out |
| Output noise voltage (CD) | V_{NoCD} | — | 5 | 10 | μV_{rms} | CAE | DIN AUDIO Line Out |


| Parameter | Symbol | Min. | Typ. | Max. | Unit | Symbol* | Conditions |
|-----------------------------|---------------------|------|------|------|------|----------|--|
| Rec EQ Amp f characteristic | | | | | | CD Input | |
| Nor | ΔG_{vcNor} | 4.6 | 7.0 | 9.4 | dB | CNE | Measured at 10kHz (output voltage=0dB at f=1kHz) |
| HS | ΔG_{vcHS} | 1.7 | 3.7 | 5.7 | dB | CHE | Measured at 10kHz (output voltage=0dB at f=1kHz) |
| PB EQ Amp f characteristic | ΔG_{vcPB} | 3.1 | 5.5 | 7.9 | dB | D * E | * =Difference between N and H output levels at f=10kHz. Measured at Line Out. |
| L/R channel separation | | | | | | | |
| Radio~Line | CS _{LR} RL | 55 | 66 | — | dB | RNE | Vo=0dBm |
| CD ~Line | CS _{LR} CL | 55 | 66 | — | dB | CNE | Vo=0dBm |
| Tape ~Line | CS _{LR} TL | 50 | 62 | — | dB | TAE | Vo=0dBm |
| Radio~Rec | CS _{LR} RR | 50 | 54 | — | dB | RNE | Vo=-6dBm |
| CD ~Rec | CS _{LR} RL | 50 | 54 | — | dB | CNE | Vo=-6dBm |
| A/B crosstalk | CT _{AB} | — | -67 | -60 | dBm | T * E | With (TAE) Tape A input, and Line Out=0dBm, switch to (TBE) and measure the Line Out level. |
| PB→REC crosstalk | CT _{RP} | — | -92 | -80 | dBm | C * E | With (CNE) CD input, ALC off, and Rec Out=0dBm, switch ALC on, switch to (CAE) and measure the Rec Out level (tape B). |
| Mic mute level | MM | — | -66 | -55 | dBm | TN * | With (TNM) Mic input, and Line Out =0dBm, switch to (TNE) and measure the Line Out level. |
| ALC distortion | THD _{ALC} | — | 0.5 | 1 | % | TNE | Mic input=-40dBm Measured at Rec Out. |
| ALC level | V _{ALC} | -5.7 | -3.7 | -1.7 | dBm | TNE | Mic input=-30dBm Measured at Rec Out. |
| ALC balance | CB _{ALC} | — | 0 | 2.5 | dB | TNE | Mic input=-30dBm Measured at Rec Out. |
| ALC current capacity | I _{ALC} | 4.0 | 7.7 | — | mA | TNE | Mic input=-30dBm Average τ pin output current. |

| Parameter | | Symbol | Min. | Typ. | Max. | Unit | Symbol* | Conditions |
|---|-------------|------------------|---------------------|------|---------------------|------------|---------|--|
| Mic/HS pin output voltage | HS | VHS | 1.0 | 1.4 | — | V | CH— | Current: 300 μ A |
| | Nor | VNor | — | 0.38 | 0.43 | | CNE | |
| Mic/HS pin threshold resistance | ECM | RECM | — | 50 | 100 | k Ω | | |
| | Mic | RMic | 30 | 50 | — | | | |
| Function pin threshold voltage | Dubbing | V _F R | 0.86V _{cc} | — | V _{cc} | V | | |
| | Tape | V _F C | 0.57V _{cc} | — | 0.82V _{cc} | | | |
| | CD | V _F D | 0.27V _{cc} | — | 0.53V _{cc} | | | |
| | Radio | V _F T | 0.07V _{cc} | — | 0.23V _{cc} | | | |
| Tape mode pin threshold voltage | Nor Rec | V _T N | 0.86V _{cc} | — | V _{cc} | V | | |
| | HS Rec | V _T H | 0.57V _{cc} | — | 0.82V _{cc} | | | |
| | B mechanism | V _T B | 0.31V _{cc} | — | 0.53V _{cc} | | | |
| | A mechanism | V _T A | 0.09V _{cc} | — | 0.27V _{cc} | | | |
| Bias oscillator transistor saturation voltage | | V _{SAT} | — | 0.24 | 0.35 | V | CNE | Current: 10mA, 10k Ω resistor connected between V _{cc} and pin 30. |

* Meaning of the abbreviations in the symbol column

| Pin | Symbol | Meaning | Applied voltage or state |
|-------|--------|-------------|--|
| 7pin | E | ECM | Open |
| | M | Mic | Connected to GND via 10k Ω |
| 28pin | N | Nor Rec | Connected to V _{cc} via 10k Ω |
| | H | HS Rec | Connected to V _{cc} via 10k Ω and to GND via 22k Ω |
| | B | B mechanism | Connected to V _{cc} via 6.9k Ω (22k in parallel with 10k) and to GND via 4.7k Ω |
| | A | A mechanism | Connected to V _{cc} via 22k Ω and to GND via 4.7k Ω |
| 27pin | D | Dubbing | Connected to V _{cc} via 10k Ω |
| | T | Tape | Connected to V _{cc} via 10k Ω and to GND via 22k Ω |
| | C | CD | Connected to V _{cc} via 10k Ω and to GND via 6.8k Ω |
| | R | Radio | Connected to V _{cc} via 10k Ω and to GND via 1k Ω |

●Measurement circuit



●Circuit operation

(1) Control pins

The control pin inputs and the corresponding states of the various inputs and outputs are summarized in the input/output pin status table that follows.

Control pin inputs and corresponding input/output pin states

| Control Pin | | | Input/Output Condition | | | | | | | | | | Bias OSC Tr. | HS Out | Transient mute | Set Mode |
|-------------|--------------|--------------------------------|------------------------|------------|-------------|------------|-------------|------------|-------------|------------|-------------|------------|--------------------|-----------|-------------------|----------------|
| Function | Tape Mode | ECM/Mic Open=ECM Low=Mic | A In | | B In | | CD In | | Radio In | | Mic In | | | | | |
| | | | Line Out | Rec Out | Line Out | Rec Out | Line Out | Rec Out | Line Out | Rec Out | Line Out | Rec Out | | | | |
| Dub | Nor Rec | ECM | ● | ● | × | × | × | × | × | × | × | × | on | Low | | Dubbing |
| | | Mic | ● | ● | × | × | × | × | × | × | ● | ● | on | Low | on | Mix—Dubbing |
| | HS—R | ECM | ●HS | ●HS | × | × | × | × | × | × | × | × | on | High | on | HS—Dubbing |
| | B PB | ECM | × | open | ● | open | × | open | × | open | × | open | off | Low | on | B—Play |
| | | Mic | × | open | ● | open | × | open | × | open | ● | open | off | Low | on | B—Mix—Play |
| | A PB | ECM | ● | open | × | open | × | open | × | open | × | open | off | Low | on | A—Play |
| | | Mic | ● | open | × | open | × | open | × | open | ● | open | off | Low | on | A—Mix—Play |
| | Tape | Nor Rec | ECM | × | × | × | × | × | × | × | × | × | ● | on | Low | on |
| Mic | | | × | × | × | × | × | × | × | × | ● | ● | on | Low | on | Mic—Rec |
| HS Rec | | ECM | × | × | × | × | × | × | × | × | × | ● | on | Low | on | ECM—Rec |
| | | Mic | × | × | × | × | × | × | × | × | ● | ● | on | Low | on | Mic—Rec |
| B PB | | ECM | × | open | ● | open | × | open | × | open | × | open | off | Low | on | B—Play |
| | | Mic | × | open | ● | open | × | open | × | open | ● | open | off | Low | on | B—Mix—Play |
| A PB | | ECM | ● | open | × | open | × | open | × | open | × | open | off | Low | on | A—Play |
| | | Mic | ● | open | × | open | × | open | × | open | ● | open | off | Low | on | A—Mix—Play |
| CD | Nor Rec | ECM | × | × | × | × | ● | ● | × | × | × | × | on | Low | * | CD—Dubbing |
| | | Mic | × | × | × | × | ● | ● | × | × | ● | ● | on | Low | * | CD—Mix—Dubbing |
| | HS—R | ECM | × | × | × | × | ● | ●HS | × | × | × | × | on | High | * | CD—HS—Dubbing |
| | B PB | ECM | × | open | × | open | ● | open | × | open | × | open | off | Low | * | CD—Play |
| | | Mic | × | open | × | open | ● | open | × | open | ● | open | off | Low | * | CD—Mix—Play |
| | A PB | ECM | × | open | × | open | ● | open | × | open | × | open | off | Low | * | CD—Play |
| | | Mic | × | open | × | open | ● | open | × | open | ● | open | off | Low | * | CD—Mix—Play |
| | Radio | Nor Rec | ECM | × | × | × | × | × | × | ● | ● | × | × | on | Low | * |
| Mic | | | × | × | × | × | × | × | ● | ● | ● | ● | on | Low | * | Rad—Mix—Rec |
| HS Rec | | ECM | × | × | × | × | × | × | ● | ● | × | × | on | Low | * | Rad—Rec |
| | | Mic | × | × | × | × | × | × | ● | ● | ● | ● | on | Low | * | Rad—Mix—Rec |
| B PB | | ECM | × | open | × | open | × | open | ● | open | × | open | off | Low | * | Rad—Play |
| | | Mic | × | open | × | open | × | open | ● | open | ● | open | off | Low | * | Rad—Mix—Play |
| A PB | | ECM | × | open | × | open | × | open | ● | open | × | open | off | Low | * | Rad—Play |
| | | Mic | × | open | × | open | × | open | ● | open | ● | open | off | Low | * | Rad—Mix—Play |

* Only the A-PLAY Y/B-PLAY switch goes off.


● :Corresponding signal is output.

●HS:The corresponding signal has the high-speed mode equalizer characteristic applied and is output.

× :Corresponding signal is output.

open:In the open (high impedance) state, no signal is output from output pin.

●Application example 1



●Application example 2




Fig. 3

● Operation notes

(1) Amplifier oscillation

As the BA3426AS incorporates dual-cassette dubbing functions on a single IC, it has extremely high input/output gain. In particular, in normal-speed mode, the gain at around the recording equalizer peaking characteristic frequency is about 70dB. The phases of the input and output are reversed to reduce the chance of oscillation due to influence of the PCB pattern, but due consideration must be given to the PCB pattern design to prevent oscillation. In particular, the PCB tracks to the Tape A pins (pins 1 and 4) and Tape B pins (pins 31 and 32) should be sufficiently far apart that there is no coupling capacitance between them, or they should be shielded by having a GND or bias track between them.

(2) Strong RF signals

To prevent signal mixing due to strong electric fields, connect a capacitor (of a few hundred pF) to each input pin. These must be connected close to the pins of the IC to have any effect. Design the PCB track layout so that the capacitors can be connected as close to the base of the pins as possible.

● Electrical characteristics curves




Fig. 4 Quiescent current vs. power supply voltage




Fig. 5 Voltage gain vs. frequency




Fig. 6 Voltage gain vs. frequency




Fig. 7 Voltage gain vs. frequency




Fig. 8 Voltage gain vs. frequency

●External dimensions (Units: mm)

