

Cables



Industrial Cat. 6_A cable, stranded, 8-wire, PUR
to make up flexible connections
(one- or two-sided assembled system cables)

IP 20	☒	IP 65 / IP 67	☒	PUR	Cat. 5	☐	Cat. 6 _A	☒
-------	-------------------------------------	---------------	-------------------------------------	-----	--------	--------------------------	---------------------	-------------------------------------

Cable structure	4 x 2, Twisted Pair, shielded, PIMF
Core structure	4 x 2 x AWG 26/7
Wire insulation	PE, Ø 1.05 mm
Sheath material	PUR
Cable sheath diameter	6.3 mm ... 6.9 mm
Transmission performance	Category 6 _A / Class E _A up to 500 MHz according to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	10/100/1000 Mbit/s, 10 Gbit/s
Shielding	Paired shielded with additional cable shield
Operating temperature range	–40 °C ... +80 °C
Standard lengths	20 m / 50 m / 100 m / 500 m
Colour	Yellow

Advantages

Robust design suitable for industry
Optimal performance reserves
Halogen free
RoHS compliant
Flame retardant sheath material

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Industrial Cat. 6_A cable, stranded,
8-wire
PUR

20 m ring
50 m ring
100 m ring
500 m drum

09 45 600 0630
09 45 600 0640
09 45 600 0600
09 45 600 0620

