

4

3

2

1


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C1	ECR-14-003072	01MAR2014	GK	HMR

REPLACED BY OCEAN STYLE APPLICATOR PART
NUMBER 2151187-1

FOR REPLACEMENT PARTS FOR APPLICATOR 1528251
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
1528251

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN GOPALAKRISHNA HV		TE Connectivity				
			CHK RAGHAVENDRA						
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD RAGHAVENDRA		NAME FINE ADJ SIDE FD HD-I APPL			
				PRODUCT SPEC		SIZE CAGE CODE DRAWING NO A 3 C- 1528251 RESTRICTED TO			
				APPLICATION SPEC					
				WEIGHT					
				CUSTOMER DRAWING					

	—	1	1	1	1	1	1	1528251	PRINT, APPLICATOR LOG SHEET	72
	—	1	1	1	1	1	1	1338705-3	DOCUMENTATION PACKAGE	71
										70
										69
										68
	—	1	1	1	1	1	1	461264-5	PLATE, IDENTIFICATION	67
	—	2	2	2	2	2	2	21017-2	SCR,DRIVE(#2x.19)ID PLATE	66
										65
										64
	—	1	1	1	1	1	1	3-18031-0	SCR,SKT SET(M6X6)RAM	63
										62
	—	2	2	2	2	2	2	2-18032-5	SCR,SET(M5X20)DRAG	61
	—	1	1	1	1	1	1	18024-7	SCR,BHC(M4X10)ANVIL	60
	—	1	1	1	1	1	1	5-18022-2	SCR,HEX(M4X8)FEED FINGER	59
										58
										57
	—	1	1	1	1	1	1	1338685-1	PAWL, FEED	56
										55
	—	4	4	4	4	4	4	18024-8	SCR,BHC(M4x12)SHEAR HOLDER	54
										53
	—	1	1	1	1	1	1	18030-1	NUT,HEX(M3)HOLD DOWN	52
	—	1	1	1	1	1	1	811242-5	BUMPER, HOLDDOWN	51
	—	1	1	1	1	1	1	690753-2	SPACER, TONKER	50
	—	1	1	1	1	1	1	18024-3	SCR,BHC(M3X10)CAM	49
	—	1	1	—	—	1	—	1338675-1	CAM, PRE FEED 30 & 40 mm ST	48
	—	1	—	1	1	—	1	1338676-1	CAM, POST FEED 30 & 40 mm ST	47
	—	1	1	1	1	1	1	1320999-3	APPLICATOR BASIC SUBASSY	46
	—	1	1	1	1	1	1	690191-1	PLUG, NYLON	45
	—	1	1	1	1	1	1	1338660-1	RAM	44
										43
										42
	—	1	1	1	1	1	1	2-18024-6	SCR,BHC(M8X25)RAM	41
										40
	—	1	1	1	1	1	1	690125-1	SHIM SUBASSY	39
	—	1	1	1	1	1	1	469367-9	SPACER, FINE ADJUST	38
	—	1	1	1	1	1	1	879103-2	FINE ADJUST HEAD SUBASSY	37
										36
										35
	—	1	1	1	1	1	1	1320934-1	SUPPORT, TERMINAL	34
	—	2	2	2	2	2	2	1-18024-0	SCR,BHC(M4X20)STRIP GUIDE	33
	—	1	1	1	1	1	1	18027-2	WASHER, FLAT(M4)	32
	—	3	3	3	3	3	3	1-18023-2	SCR,SKT CAP(M4X12)MOUNT BLOCK	31
	—	1	1	1	1	1	1	1320908-1	SPACER, STRIP GUIDE	30
	—	1	1	1	1	1	1	1633073-1	STRIP GUIDE PLATE ASSY	29
	—	1	1	1	1	1	1	1-455888-0	SPACER, FRONT SHEAR DEP	28
	—	2	2	2	2	2	2	1-22284-0	SPRING, DRAG	27
	—	1	1	1	1	1	1	356835-1	LEVER, DRAG RELEASE	26
	—	1	1	1	1	1	1	240792-1	DRAG, TERMINAL	25
	—	1	1	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	24
	—	1	1	1	1	1	1	980371-4	SCR,SHC SHLD	23
	—	1	—	1	1	—	1	690472-2	STRIPPER	22
	—	1	1	1	1	1	1	1-18023-1	SCR,SHC(M4X10)STRIPPER	21
	—	4	4	4	4	4	4	18025-2	WASHER,LOCK(M4)STRIPPER	20
	—	—	1	—	—	1	—	690472-1	STRIPPER	19
1	—	1	—	—	1	—	—	1338684-1	HOLDER, SHEAR, FRONT (NO-CUT)	18
										17
										16
										15
										14
										13
	—	1	1	1	1	1	1	3-22280-3	SPRING, SHEAR	12
	—	1	1	1	1	1	1	356885-4	STOP, SHEAR	11
}	—	—	1	1	—	1	1	1320921-1	HOLDER, SHEAR, FRONT (CUT)	10
	—	1	1	1	1	1	1	454276-1	SHEAR, FLOAT (FRONT)	9
	1	2	2	2	1	1	1	1338696-2	ANVIL	8
										7
										6
	—	1	1	1	1	1	1	1-455889-4	DEPRESSOR, SHEAR (FRONT)	5
	—	1	1	1	1	1	1	238011-4	SPACER, BLOCK CRIMPER	4
1	1	2	2	2	1	1	1	683453-1	CRIMPER, INSULATION	3
1	—	1	1	1	1	1	1	455888-4	SPACER, CRIMPER	2
	1	2	2	2	1	1	1	456408-2	CRIMPER, WIRE	1

[illegible][illegible]

* **WARNING:**
ON INSTALLATION, SET WIRE DISC TO LARGEST WIRE SIZE
SETTING. USE OF SETTINGS BELOW MIN REQ'D CRIMP
HEIGHT SETTING WILL CAUSE DAMAGE TO CRIMP TOOLING.