

Ø22mm

YW Series Control Units



IDEC CORPORATION

Innovative Design, Space-Saving, Safety, and Self-Cleaning Contacts

Emergency Stop Switches



Non-illuminated

Illuminated

Satisfy International Standards

- **Safety Lock Mechanism**

When the emergency stop signal has been generated during actuation of the emergency stop device, the emergency stop function shall be maintained until the emergency stop device is reset (disengaged) (IEC 60947-5-5, 6.2).

- **Direct Opening Action**

Even if the contacts are welded, NC contacts are forced to open and break the circuit (compliant to IEC 60947-5-1, Annex K, IEC 60947-5-5, 5.2).

- **Safe Pushbutton Design**

The pushbutton is designed to ensure that an object cannot become trapped between the mushroom button and the panel, disabling the button operation. In addition, the pushbutton is designed to prevent removal from the front of the panel (IEC 60947-5-5, 6.3.2).

Easy Operation

- **Push-to-lock, Pull/Turn-to-release**

YW emergency stop switches can be unlatched by either pulling or turning the operator.

Unlatching by pulling



Unlatching by turning



Unibody Pilot Lights

Higher Brightness

The new unibody pilot light achieves high brightness.

Short Depth behind the Panel

Unibody type measures only 42mm depth behind the panel.

Four Lens Shapes

Flush, flush with marking, extended, and dome.

Panel Mounting

Unibody pilot lights can be mounted on panels simply by tightening the locking ring.



Flush

Flush w/marking

Extended

Dome

Key Selector Switches



Plastic Bezel



Metal Bezel


A variety of operations, key removal positions, and circuits.

Wide range adds more options to choose from.



Safety


Integrated Finger-safe
Terminal Cover
Degree of Protection: IP20
(From panel front: IP65)




Metal bezels are available
for pushbuttons, illuminated
pushbuttons, selector
switches, and key selector
switches.

Save

New Contact Block Design
YW series




The new contact block design reduces
the depth behind the panel.



Reliable


Retained Locking Lever



An innovative plastic locking lever is
retained and eliminates the need for a
separate lever lock.

Heavy-Duty Rugged Construction

Self-Cleaning Wiping-Action Contacts with Scored Contact Surfaces



YW Series Control Units

Space-saving, 10-mm-thick contact blocks. Removable operator.

- Compact and light-weight
- IP20 finger-safe screw terminals (IEC 60529)
- Emergency stop switches feature safety lock mechanism, direct opening action, and safe pushbutton design.
- Metal bezel, unibody pilot lights, and key selector switches available.
- Separate contact block makes installation and removal easy. Pilot lights feature a large lens for a wide viewing angle.
- Matted surfaces on the buttons, lenses, and bezels reduce reflection of ambient light.
- UL, c-UL listed, EN compliant, and CCC approved.



- UL508, CSA C22.2 No. 14, EN 60947-1, EN 60947-5-1, EN 60947-5-5, GB 14048.5



Contact Ratings (Contact Block)

Rated Insulation Voltage		600V			
Rated Thermal Current		10A			
Operating Voltage		24V	120V	240V	380V
AC 50/60 Hz	Resistive Load (AC-12)	10A	10A	6A	2A
	Inductive Load (AC-15)	10A	6A	3A	1.9A
DC	Resistive Load (DC-12)	8A	2.2A	1.1A	—
	Inductive Load (DC-13)	4A	1.1A	0.55A	—

LED Lamp Ratings

Type No.	Rated Voltage	Rated Current	Color Code
LSED-6②	6V AC/DC	10 mA (A, R, Y) 7 mA (G, PW, S)	A: amber G: green PW: pure white R: red S: blue Y: yellow
LSED-1②	12V AC/DC	14 mA (A, R, Y) 13 mA (G, PW, S)	
LSED-2②	24V AC/DC	14 mA (A, R, Y) 13 mA (G, PW, S)	
LSED-H②	110V AC/DC	5.5 mA	
LSED-M3②	230/240V AC/DC	2.7 mA	

Note: Specify a color code in place of ② in the Type No.
Yellow LED lamps are used for white illumination of pilot lights and illuminated pushbuttons.


Incandescent Lamp Ratings

Type No.	Rated Voltage	Ratings
LS-T6	6V AC/DC	6.3V 1W
LS-T8	12V AC/DC	18V 1W
LS-T3	24V AC/DC	30V 1W

Unibody Pilot Light Ratings

Rated Voltage	Illumination Color	Rated Current
6V AC/DC	A, R, W, Y	16 mA
	G, PW, S	13 mA
12V AC/DC	A, G, PW, R, S, W, Y	20 mA
24V AC/DC		
100/110V AC		
230/240V AC		

Mounting Hole Layout



The 3.2-mm-wide key recess is necessary when the anti-rotation ring is used.

Unit	A (mm)	B (mm)
Emergency stop switch	50 min.	50 min.
Pushbutton	50 min.	30 min.
Selector switch		
Key selector switch		
Mushroom pushbutton	50 min.	40 min.
Pilot light (separate type)	30 min.*	30 min.
Pilot light (unibody type)	50 min.	30 min.

* Keep a minimum spacing of 50 mm when using a lamp of over 1W.


Specifications

Operating Conditions	Operating temperature: -20 to +55°C (no freezing)	
	Operating humidity: 45 to 85% RH (no condensation)	
	Storage temperature: -45 to +80°C	
	Storage humidity: 95% RH maximum	
Degree of Protection	From panel front:	IP65 (IEC 60529)
	Terminal:	IP20 (IEC 60529)
Insulation Resistance	100 MΩ	
Dielectric Strength	Contact block:	2,500V, 1 minute
	Pilot light:	2,000V, 1 minute
Vibration Resistance	<Emergency stop switch> Operating extremes / Damage limits: 10 to 500Hz, amplitude 0.35 mm, acceleration 50 m/s ² (5G)	
	<Pushbutton, pilot light, illuminated pushbutton, selector switch, and key selector switch> Operating extremes: 5 to 55 Hz, amplitude 0.5 mm Damage limits: 30 Hz, amplitude 1.5 mm	
Shock Resistance	<Emergency stop switch> Operating extremes: 150 m/s ² (15G) Damage limits: 1,000 m/s ² (100G)	
	<Pushbutton, pilot light, illuminated pushbutton, selector switch, and key selector switch> Operating extremes: 100 m/s ² (10G) Damage limits: 1,000 m/s ² (100G)	
Mechanical Life (minimum operations)	<Emergency stop switch> 250,000 (single contact block)	
	<Pushbutton and illuminated pushbutton> Momentary: 5,000,000 (single contact block) 1,000,000 (double contact block) Maintained: 250,000 (single contact block) 100,000 (double contact block)	
Electrical Life (minimum operations)	<Selector switch and key selector switch> 250,000 (single contact block) 100,000 (double contact block)	
	<Emergency stop switch> 100,000 (single contact block) <Pushbutton, selector switch, and key selector switch> 100,000 (single contact block) 50,000 (double contact block)	

Emergency Stop Switches

Style	Operation	Contact	Type No.	Button Color Code
Mushroom ø40mm 	Pushlock Pull/Turn Reset	1NC	YW1B-V4E01R	Red only
		2NC	YW1B-V4E02R	
		3NC	YW1B-V4E03R	
		1NO-1NC	YW1B-V4E11R	
		1NO-2NC	YW1B-V4E12R	
		2NO-1NC	YW1B-V4E21R	

Dimensions




Note: The button is locked when pressed, and is reset when either pulled or turned clockwise.

Illuminated Emergency Stop Switches

Style	Illumination Type	Operation	Contacts	Type No.	③ Operating Voltage Code	Lens Color Code
Mushroom ø40mm 	Without Lamp	Pushlock Pull/Turn Reset	1NC	YW1L-V4E01Q0R	0: without lamp 250V AC/DC max.	Red only
			2NC	YW1L-V4E02Q0R		
			1NO-1NC	YW1L-V4E11Q0R		
	LED		1NC	YW1L-V4E01Q③R	2: 6V AC/DC 3: 12V AC/DC 4: 24V AC/DC H: 110V AC/DC M3: 230/240V AC/DC	
			2NC	YW1L-V4E02Q③R		
			1NO-1NC	YW1L-V4E11Q③R		
	Incandescent		1NC	YW1L-V4E01Q③R	5: 6V AC/DC 6: 12V AC/DC 7: 24V AC/DC	
			2NC	YW1L-V4E02Q③R		
			1NO-1NC	YW1L-V4E11Q③R		

Note: Specify an operating voltage code in place of ③ in the Type No.

Dimensions



Note: The button is locked when pressed, and is reset when either pulled or turned clockwise.


All dimensions in mm.

Pushbuttons with Plastic Bezel


Style	Operation	Contact	Type No.	① Button Color Code
Flush 	Momentary	1NO	YW1B-M1E10①	B: black G: green R: red S: blue W: white Y: yellow
		1NC	YW1B-M1E01①	
		2NO	YW1B-M1E20①	
		2NC	YW1B-M1E02①	
		1NO-1NC	YW1B-M1E11①	
		3NO	YW1B-M1E30①	
		3NC	YW1B-M1E03①	
		2NO-1NC	YW1B-M1E21①	
		1NO-2NC	YW1B-M1E12①	
	Maintained	1NO	YW1B-A1E10①	
		1NC	YW1B-A1E01①	
		2NO	YW1B-A1E20①	
		2NC	YW1B-A1E02①	
		1NO-1NC	YW1B-A1E11①	
Extended 	Momentary	1NO	YW1B-M2E10①	B: black G: green R: red S: blue W: white Y: yellow
		1NC	YW1B-M2E01①	
		2NO	YW1B-M2E20①	
		2NC	YW1B-M2E02①	
		1NO-1NC	YW1B-M2E11①	
	Maintained	1NO	YW1B-A2E10①	
		1NC	YW1B-A2E01①	
		2NO	YW1B-A2E20①	
		2NC	YW1B-A2E02①	
		1NO-1NC	YW1B-A2E11①	
Mushroom ø40mm 	Momentary	1NO	YW1B-M4E10①	B: black G: green R: red S: blue W: white Y: yellow
		1NC	YW1B-M4E01①	
		2NO	YW1B-M4E20①	
		2NC	YW1B-M4E02①	
		1NO-1NC	YW1B-M4E11①	
	Maintained	1NO	YW1B-A4E10①	
		1NC	YW1B-A4E01①	
		2NO	YW1B-A4E20①	
		2NC	YW1B-A4E02①	
		1NO-1NC	YW1B-A4E11①	

Note: Specify a button color code in place of ① in the Type No.


Dimensions




• Flush



• Mushroom



• Extended




All dimensions in mm.

Pushbuttons with Metal Bezel

Style	Operation	Contact	Type No.	① Button Color Code
Flush Metal Bezel 	Momentary	1NO	YW4B-M1E10①	B: black G: green R: red S: blue W: white Y: yellow
		1NC	YW4B-M1E01①	
		2NO	YW4B-M1E20①	
		2NC	YW4B-M1E02①	
		1NO-1NC	YW4B-M1E11①	
		3NO	YW4B-M1E30①	
		3NC	YW4B-M1E03①	
		2NO-1NC	YW4B-M1E21①	
		1NO-2NC	YW4B-M1E12①	
	Maintained	1NO	YW4B-A1E10①	
		1NC	YW4B-A1E01①	
		2NO	YW4B-A1E20①	
		2NC	YW4B-A1E02①	
		1NO-1NC	YW4B-A1E11①	
Extended Metal Bezel 	Momentary	1NO	YW4B-M2E10①	B: black G: green R: red S: blue W: white Y: yellow
		1NC	YW4B-M2E01①	
		2NO	YW4B-M2E20①	
		2NC	YW4B-M2E02①	
		1NO-1NC	YW4B-M2E11①	
	Maintained	1NO	YW4B-A2E10①	
		1NC	YW4B-A2E01①	
		2NO	YW4B-A2E20①	
		2NC	YW4B-A2E02①	
		1NO-1NC	YW4B-A2E11①	
Mushroom ø40mm Metal Bezel 	Momentary	1NO	YW4B-M4E10①	B: black G: green R: red S: blue W: white Y: yellow
		1NC	YW4B-M4E01①	
		2NO	YW4B-M4E20①	
		2NC	YW4B-M4E02①	
		1NO-1NC	YW4B-M4E11①	
	Maintained	1NO	YW4B-A4E10①	
		1NC	YW4B-A4E01①	
		2NO	YW4B-A4E20①	
		2NC	YW4B-A4E02①	
		1NO-1NC	YW4B-A4E11①	

Note: Specify a button color code in place of ① in the Type No.

Dimensions




Pilot Lights (Unibody Type)


Style	Illumination Type	Operating Voltage	Type No.	② Lens Color Code
Flush Full Voltage 	LED	6V AC/DC	YW1P-1UQ2②	A: amber G: green PW: pure white R: red S: blue W: white Y: yellow
		12V AC/DC	YW1P-1UQ3②	
		24V AC/DC	YW1P-1UQ4②	
		100/110V AC	YW1P-1UQH②	
		230/240V AC	YW1P-1UQM3②	
Flush Marking Type Full Voltage 	LED	6V AC/DC	YW1P-1BUQ2②	
		12V AC/DC	YW1P-1BUQ3②	
		24V AC/DC	YW1P-1BUQ4②	
		100/110V AC	YW1P-1BUQH②	
		230/240V AC	YW1P-1BUQM3②	
Extended Full Voltage 	LED	6V AC/DC	YW1P-2TUQ2②	
		12V AC/DC	YW1P-2TUQ3②	
		24V AC/DC	YW1P-2TUQ4②	
		100/110V AC	YW1P-2TUQH②	
		230/240V AC	YW1P-2TUQM3②	
Dome Full Voltage 	LED	6V AC/DC	YW1P-2UQ2②	
		12V AC/DC	YW1P-2UQ3②	
		24V AC/DC	YW1P-2UQ4②	
		100/110V AC	YW1P-2UQH②	
		230/240V AC	YW1P-2UQM3②	

Dimensions


Flush




Flush Marking Type



Extended



Dome



All dimensions in mm.

Pilot Lights (Separate Type)

Style	Illumination Type	Operating Voltage	Type No.	② Lens Color Code
Flush Full Voltage 	Without Lamp	250V AC/DC max.	YW1P-1EQ0②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow)
	LED	6V AC/DC	YW1P-1EQ2②	A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) Built-in LED lamp: LSED-③②
		12V AC/DC	YW1P-1EQ3②	
		24V AC/DC	YW1P-1EQ4②	
		110V AC/DC	YW1P-1EQH②	
		230/240V AC/DC	YW1P-1EQM3②	
	Incandescent	6V AC/DC	YW1P-1EQ5②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow) Built-in incandescent lamp: LS-T③
		12V AC/DC	YW1P-1EQ6②	
		24V AC/DC	YW1P-1EQ7②	
Flush Transformer Type 	LED	100/110V AC	YW1P-1EH2②	A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) Built-in LED lamp: LSED-6②
		200/220V AC	YW1P-1EM2②	
		115/120V AC	YW1P-1EH22②	
		230/240V AC	YW1P-1EM42②	
	Incandescent	100/110V AC	YW1P-1EH5②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow) Built-in incandescent lamp: LS-T6
		200/220V AC	YW1P-1EM5②	
		115/120V AC	YW1P-1EH25②	
		230/240V AC	YW1P-1EM45②	
Flush Marking Type Full Voltage 	Without Lamp	250V AC/DC max.	YW1P-1BEQ0②	A (amber), G (green), R (red), S (blue), W (white), Y (yellow)
	LED	6V AC/DC	YW1P-1BEQ2②	A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) Built-in LED lamp: LSED-③②
		12V AC/DC	YW1P-1BEQ3②	
		24V AC/DC	YW1P-1BEQ4②	
		110V AC/DC	YW1P-1BEQH②	
		230/240V AC/DC	YW1P-1BEQM3②	
	Incandescent	6V AC/DC	YW1P-1BEQ5②	A (amber), G (green), R (red), S (blue), W (white), Y (yellow) Built-in incandescent lamp: LS-T③
		12V AC/DC	YW1P-1BEQ6②	
		24V AC/DC	YW1P-1BEQ7②	
Flush Marking Type Transformer Type 	LED	100/110V AC	YW1P-1BEH2②	A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) Built-in LED lamp: LSED-6②
		200/220V AC	YW1P-1BEM2②	
		115/120V AC	YW1P-1BEH22②	
		230/240V AC	YW1P-1BEM42②	
	Incandescent	100/110V AC	YW1P-1BEH5②	A (amber), G (green), R (red), S (blue), W (white), Y (yellow) Built-in incandescent lamp: LS-T6
		200/220V AC	YW1P-1BEM5②	
		115/120V AC	YW1P-1BEH25②	
		230/240V AC	YW1P-1BEM45②	

Note: Specify a lens color code in place of ② in the Type No.
Clear lenses are used for PW (pure white) illumination of pilot lights.

ø22 YW Series Control Units


Style	Illumination Type	Operating Voltage	Type No.	② Lens Color Code
Extended Full Voltage 	Without Lamp	250V AC/DC max.	YW1P-2TEQ0②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow)
	LED	6V AC/DC	YW1P-2TEQ2②	A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) Built-in LED lamp: LSED-③②
		12V AC/DC	YW1P-2TEQ3②	
		24V AC/DC	YW1P-2TEQ4②	
		110V AC/DC	YW1P-2TEQH②	
		230/240V AC/DC	YW1P-2TEQM3②	
	Incandescent	6V AC/DC	YW1P-2TEQ5②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow) Built-in incandescent lamp: LS-T③
		12V AC/DC	YW1P-2TEQ6②	
		24V AC/DC	YW1P-2TEQ7②	
Extended Transformer Type 	LED	100/110V AC	YW1P-2TEH2②	A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) Built-in LED lamp: LSED-6②
		200/220V AC	YW1P-2TEM2②	
		115/120V AC	YW1P-2TEH22②	
		230/240V AC	YW1P-2TEM42②	
	Incandescent	100/110V AC	YW1P-2TEH5②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow) Built-in incandescent lamp: LS-T6
		200/220V AC	YW1P-2TEM5②	
		115/120V AC	YW1P-2TEH25②	
		230/240V AC	YW1P-2TEM45②	
Dome Full Voltage 	Without Lamp	250V AC/DC max.	YW1P-2EQ0②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow)
	LED	6V AC/DC	YW1P-2EQ2②	A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) Built-in LED lamp: LSED-③②
		12V AC/DC	YW1P-2EQ3②	
		24V AC/DC	YW1P-2EQ4②	
		110V AC/DC	YW1P-2EQH②	
		230/240V AC/DC	YW1P-2EQM3②	
	Incandescent	6V AC/DC	YW1P-2EQ5②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow) Built-in incandescent lamp: LS-T③
		12V AC/DC	YW1P-2EQ6②	
		24V AC/DC	YW1P-2EQ7②	
Dome Transformer Type 	LED	100/110V AC	YW1P-2EH2②	A (amber), G (green), PW (pure white), R (red), S (blue), W (white), Y (yellow) Built-in LED lamp: LSED-6②
		200/220V AC	YW1P-2EM2②	
		115/120V AC	YW1P-2EH22②	
		230/240V AC	YW1P-2EM42②	
	Incandescent	100/110V AC	YW1P-2EH5②	A (amber), C (clear), G (green), R (red), S (blue), W (white), Y (yellow) Built-in incandescent lamp: LS-T6
		200/220V AC	YW1P-2EM5②	
		115/120V AC	YW1P-2EH25②	
		230/240V AC	YW1P-2EM45②	

Note: Specify a lens color code in place of ② in the Type No.
Clear lenses are used for PW (pure white) illumination of pilot lights.


Dimensions (Separate Type Pilot Lights)

• Flush

Full Voltage




Transformer Type




• Flush Marking Type

Full Voltage




Transformer Type




• Extended

Full Voltage




Transformer Type




• Dome

Full Voltage



Transformer Type



All dimensions in mm.

Illuminated Pushbuttons with Plastic Bezel


Style	Illumination Type	Operation	Contacts	Type No.	③ Operating Voltage Code	② Lens Color Code
Extended 	Without Lamp	Momentary	1NO	YW1L-M2E10Q0②	0: without lamp 250V AC/DC max.	A: amber G: green R: red S: blue W: white Y: yellow
			1NC	YW1L-M2E01Q0②		
			2NO	YW1L-M2E20Q0②		
			2NC	YW1L-M2E02Q0②		
			1NO-1NC	YW1L-M2E11Q0②		
		Maintained	1NO	YW1L-A2E10Q0②		
			1NC	YW1L-A2E01Q0②		
			2NO	YW1L-A2E20Q0②		
			2NC	YW1L-A2E02Q0②		
			1NO-1NC	YW1L-A2E11Q0②		
	LED	Momentary	1NO	YW1L-M2E10Q③②	2: 6V AC/DC 3: 12V AC/DC 4: 24V AC/DC H: 110V AC/DC M3: 230/240V AC/DC	A: amber G: green PW: pure white R: red S: blue W: white Y: yellow Built-in LED lamp: LSED-③②
			1NC	YW1L-M2E01Q③②		
			2NO	YW1L-M2E20Q③②		
			2NC	YW1L-M2E02Q③②		
			1NO-1NC	YW1L-M2E11Q③②		
		Maintained	1NO	YW1L-A2E10Q③②		
			1NC	YW1L-A2E01Q③②		
			2NO	YW1L-A2E20Q③②		
			2NC	YW1L-A2E02Q③②		
			1NO-1NC	YW1L-A2E11Q③②		
	Incandescent	Momentary	1NO	YW1L-M2E10Q③②	5: 6V AC/DC 6: 12V AC/DC 7: 24V AC/DC	A: amber G: green R: red S: blue W: white Y: yellow Built-in incandescent lamp: LS-T③
			1NC	YW1L-M2E01Q③②		
			2NO	YW1L-M2E20Q③②		
			2NC	YW1L-M2E02Q③②		
			1NO-1NC	YW1L-M2E11Q③②		
		Maintained	1NO	YW1L-A2E10Q③②		
			1NC	YW1L-A2E01Q③②		
			2NO	YW1L-A2E20Q③②		
			2NC	YW1L-A2E02Q③②		
			1NO-1NC	YW1L-A2E11Q③②		
Extended with Full Shroud 	Without Lamp	Momentary	1NO	YW1L-MF2E10Q0②	0: without lamp 250V AC/DC max.	A: amber G: green R: red S: blue W: white Y: yellow
			1NC	YW1L-MF2E01Q0②		
			2NO	YW1L-MF2E20Q0②		
			2NC	YW1L-MF2E02Q0②		
			1NO-1NC	YW1L-MF2E11Q0②		
		Maintained	1NO	YW1L-AF2E10Q0②		
			1NC	YW1L-AF2E01Q0②		
			2NO	YW1L-AF2E20Q0②		
			2NC	YW1L-AF2E02Q0②		
			1NO-1NC	YW1L-AF2E11Q0②		
	LED	Momentary	1NO	YW1L-MF2E10Q③②	2: 6V AC/DC 3: 12V AC/DC 4: 24V AC/DC H: 110V AC/DC M3: 230/240V AC/DC	A: amber G: green PW: pure white R: red S: blue W: white Y: yellow Built-in LED lamp: LSED-③②
			1NC	YW1L-MF2E01Q③②		
			2NO	YW1L-MF2E20Q③②		
			2NC	YW1L-MF2E02Q③②		
			1NO-1NC	YW1L-MF2E11Q③②		
		Maintained	1NO	YW1L-AF2E10Q③②		
			1NC	YW1L-AF2E01Q③②		
			2NO	YW1L-AF2E20Q③②		
			2NC	YW1L-AF2E02Q③②		
			1NO-1NC	YW1L-AF2E11Q③②		
	Incandescent	Momentary	1NO	YW1L-MF2E10Q③②	5: 6V AC/DC 6: 12V AC/DC 7: 24V AC/DC	A: amber G: green R: red S: blue W: white Y: yellow Built-in incandescent lamp: LS-T③
			1NC	YW1L-MF2E01Q③②		
			2NO	YW1L-MF2E20Q③②		
			2NC	YW1L-MF2E02Q③②		
			1NO-1NC	YW1L-MF2E11Q③②		
		Maintained	1NO	YW1L-AF2E10Q③②		
			1NC	YW1L-AF2E01Q③②		
			2NO	YW1L-AF2E20Q③②		
			2NC	YW1L-AF2E02Q③②		
			1NO-1NC	YW1L-AF2E11Q③②		

Note: Specify a lens color code in place of ② in the Type No.
Specify an operating voltage code in place of ③ in the Type No.


Style	Illumination Type	Operation	Contacts	Type No.	③ Operating Voltage Code	② Lens Color Code
	Without Lamp	Momentary	1NO	YW1L-M4E10Q0②	0: without lamp 250V AC/DC max.	A: amber G: green R: red S: blue W: white Y: yellow
			1NC	YW1L-M4E01Q0②		
			2NO	YW1L-M4E20Q0②		
			2NC	YW1L-M4E02Q0②		
		Maintained	1NO-1NC	YW1L-M4E11Q0②		
			1NO	YW1L-A4E10Q0②		
			1NC	YW1L-A4E01Q0②		
			2NO	YW1L-A4E20Q0②		
			2NC	YW1L-A4E02Q0②		
			1NO-1NC	YW1L-A4E11Q0②		
	LED	Momentary	1NO	YW1L-M4E10Q③②	2: 6V AC/DC 3: 12V AC/DC 4: 24V AC/DC H: 110V AC/DC M3: 230/240V AC/DC	A: amber G: green PW: pure white R: red S: blue W: white Y: yellow Built-in LED lamp: LSED-③②
			1NC	YW1L-M4E01Q③②		
			2NO	YW1L-M4E20Q③②		
			2NC	YW1L-M4E02Q③②		
		Maintained	1NO-1NC	YW1L-M4E11Q③②		
			1NO	YW1L-A4E10Q③②		
			1NC	YW1L-A4E01Q③②		
			2NO	YW1L-A4E20Q③②		
			2NC	YW1L-A4E02Q③②		
			1NO-1NC	YW1L-A4E11Q③②		
	Incandescent	Momentary	1NO	YW1L-M4E10Q③②	5: 6V AC/DC 6: 12V AC/DC 7: 24V AC/DC	A: amber G: green R: red S: blue W: white Y: yellow Built-in incandescent lamp: LS-T③
			1NC	YW1L-M4E01Q③②		
			2NO	YW1L-M4E20Q③②		
			2NC	YW1L-M4E02Q③②		
		Maintained	1NO-1NC	YW1L-M4E11Q③②		
			1NO	YW1L-A4E10Q③②		
			1NC	YW1L-A4E01Q③②		
			2NO	YW1L-A4E20Q③②		
			2NC	YW1L-A4E02Q③②		
			1NO-1NC	YW1L-A4E11Q③②		

Note: Specify a lens color code in place of ② in the Type No.
Specify an operating voltage code in place of ③ in the Type No.


Dimensions (Illuminated Pushbuttons with Plastic Bezel)




• Extended



• Extended with Full Shroud



• Mushroom



All dimensions in mm.

Illuminated Pushbuttons with Metal Bezel

Style	Illumination Type	Operation	Contacts	Type No.	③ Operating Voltage Code	② Lens Color Code
Extended 	Without Lamp	Momentary	1NO	YW4L-M2E10Q0②	0: without lamp 250V AC/DC max.	A: amber G: green R: red S: blue W: white Y: yellow
			1NC	YW4L-M2E01Q0②		
			2NO	YW4L-M2E20Q0②		
			2NC	YW4L-M2E02Q0②		
			1NO-1NC	YW4L-M2E11Q0②		
		Maintained	1NO	YW4L-A2E10Q0②		
			1NC	YW4L-A2E01Q0②		
			2NO	YW4L-A2E20Q0②		
			2NC	YW4L-A2E02Q0②		
			1NO-1NC	YW4L-A2E11Q0②		
	LED	Momentary	1NO	YW4L-M2E10Q③②	2: 6V AC/DC 3: 12V AC/DC 4: 24V AC/DC H: 110V AC/DC M3: 230/240V AC/DC	A: amber G: green PW: pure white R: red S: blue W: white Y: yellow Built-in LED lamp: LSED-③②
			1NC	YW4L-M2E01Q③②		
			2NO	YW4L-M2E20Q③②		
			2NC	YW4L-M2E02Q③②		
			1NO-1NC	YW4L-M2E11Q③②		
		Maintained	1NO	YW4L-A2E10Q③②		
			1NC	YW4L-A2E01Q③②		
			2NO	YW4L-A2E20Q③②		
			2NC	YW4L-A2E02Q③②		
			1NO-1NC	YW4L-A2E11Q③②		
	Incandescent	Momentary	1NO	YW4L-M2E10Q③②	5: 6V AC/DC 6: 12V AC/DC 7: 24V AC/DC	A: amber G: green R: red S: blue W: white Y: yellow Built-in incandescent lamp: LS-T③
			1NC	YW4L-M2E01Q③②		
			2NO	YW4L-M2E20Q③②		
			2NC	YW4L-M2E02Q③②		
			1NO-1NC	YW4L-M2E11Q③②		
		Maintained	1NO	YW4L-A2E10Q③②		
			1NC	YW4L-A2E01Q③②		
			2NO	YW4L-A2E20Q③②		
			2NC	YW4L-A2E02Q③②		
			1NO-1NC	YW4L-A2E11Q③②		
Extended with Full Shroud 	Without Lamp	Momentary	1NO	YW4L-MF2E10Q0②	0: without lamp 250V AC/DC max.	A: amber G: green R: red S: blue W: white Y: yellow
			1NC	YW4L-MF2E01Q0②		
			2NO	YW4L-MF2E20Q0②		
			2NC	YW4L-MF2E02Q0②		
			1NO-1NC	YW4L-MF2E11Q0②		
		Maintained	1NO	YW4L-AF2E10Q0②		
			1NC	YW4L-AF2E01Q0②		
			2NO	YW4L-AF2E20Q0②		
			2NC	YW4L-AF2E02Q0②		
			1NO-1NC	YW4L-AF2E11Q0②		
	LED	Momentary	1NO	YW4L-MF2E10Q③②	2: 6V AC/DC 3: 12V AC/DC 4: 24V AC/DC H: 110V AC/DC M3: 230/240V AC/DC	A: amber G: green PW: pure white R: red S: blue W: white Y: yellow Built-in LED lamp: LSED-③②
			1NC	YW4L-MF2E01Q③②		
			2NO	YW4L-MF2E20Q③②		
			2NC	YW4L-MF2E02Q③②		
			1NO-1NC	YW4L-MF2E11Q③②		
		Maintained	1NO	YW4L-AF2E10Q③②		
			1NC	YW4L-AF2E01Q③②		
			2NO	YW4L-AF2E20Q③②		
			2NC	YW4L-AF2E02Q③②		
			1NO-1NC	YW4L-AF2E11Q③②		
	Incandescent	Momentary	1NO	YW4L-MF2E10Q③②	5: 6V AC/DC 6: 12V AC/DC 7: 24V AC/DC	A: amber G: green R: red S: blue W: white Y: yellow Built-in incandescent lamp: LS-T③
			1NC	YW4L-MF2E01Q③②		
			2NO	YW4L-MF2E20Q③②		
			2NC	YW4L-MF2E02Q③②		
			1NO-1NC	YW4L-MF2E11Q③②		
		Maintained	1NO	YW4L-AF2E10Q③②		
			1NC	YW4L-AF2E01Q③②		
			2NO	YW4L-AF2E20Q③②		
			2NC	YW4L-AF2E02Q③②		
			1NO-1NC	YW4L-AF2E11Q③②		


Note: Specify a lens color code in place of ② in the Type No.
Specify an operating voltage code in place of ③ in the Type No.

Style	Illumination Type	Operation	Contacts	Type No.	③ Operating Voltage Code	② Lens Color Code
	Without Lamp	Momentary	1NO	YW4L-M4E10Q0②	0: without lamp 250V AC/DC max.	A: amber G: green R: red S: blue W: white Y: yellow
			1NC	YW4L-M4E01Q0②		
			2NO	YW4L-M4E20Q0②		
			2NC	YW4L-M4E02Q0②		
		Maintained	1NO-1NC	YW4L-M4E11Q0②		
			1NO	YW4L-A4E10Q0②		
			1NC	YW4L-A4E01Q0②		
			2NO	YW4L-A4E20Q0②		
			2NC	YW4L-A4E02Q0②		
	LED	Momentary	1NO-1NC	YW4L-A4E11Q0②	2: 6V AC/DC 3: 12V AC/DC 4: 24V AC/DC H: 110V AC/DC M3: 230/240V AC/DC	A: amber G: green PW: pure white R: red S: blue W: white Y: yellow Built-in LED lamp: LSED-③②
			1NO	YW4L-M4E10Q③②		
			1NC	YW4L-M4E01Q③②		
			2NO	YW4L-M4E20Q③②		
		Maintained	2NC	YW4L-M4E02Q③②		
			1NO-1NC	YW4L-M4E11Q③②		
			1NO	YW4L-A4E10Q③②		
			1NC	YW4L-A4E01Q③②		
			2NO	YW4L-A4E20Q③②		
	Incandescent	Momentary	2NC	YW4L-A4E02Q③②	5: 6V AC/DC 6: 12V AC/DC 7: 24V AC/DC	A: amber G: green R: red S: blue W: white Y: yellow Built-in incandescent lamp: LS-T③
			1NO-1NC	YW4L-A4E11Q③②		
		Maintained	1NO	YW4L-M4E10Q③②		
			1NC	YW4L-M4E01Q③②		
			2NO	YW4L-M4E20Q③②		
			2NC	YW4L-M4E02Q③②		
			1NO-1NC	YW4L-A4E11Q③②		
			1NO	YW4L-A4E10Q③②		
			1NC	YW4L-A4E01Q③②		
			2NO	YW4L-A4E20Q③②		
			2NC	YW4L-A4E02Q③②		
			1NO-1NC	YW4L-A4E11Q③②		


Note: Specify a lens color code in place of ② in the Type No.

Specify an operating voltage code in place of ③ in the Type No.


Dimensions (Illuminated Pushbutton with Metal Bezel)




• Extended



• Extended with Full Shroud



• Mushroom



All dimensions in mm.

Selector Switches with Plastic Bezel

Style						Knob Type					
											
No. of Positions	Contact Configuration	Contact Block Mounting Position	Operator Position			Maintained	Spring Return from Right	—	—		
			L	R	—						
90° 2-Position L R	1NO (10)	1	NO		●		YW1S-2E10	YW1S-21E10	—	—	
		2									
		3									
	1NC (01)	1						YW1S-2E01	YW1S-21E01	—	—
		2									
		3	NC	●							
	2NO (20)	1	NO		●		YW1S-2E20	YW1S-21E20	—	—	
		2									
		3	NO		●						
	2NC (02)	1	NC	●			YW1S-2E02	YW1S-21E02	—	—	
		2									
		3	NC	●							
	1NO-1NC (11)	1	NO		●		YW1S-2E11	YW1S-21E11	—	—	
		2									
		3	NC	●							
	3NO (30)	1	NO		●		YW1S-2E30	YW1S-21E30	—	—	
		2	NO		●						
		3	NO		●						
	3NC (03)	1	NC	●			YW1S-2E03	YW1S-21E03	—	—	
		2	NC	●							
		3	NC	●							
	2NO-1NC (21)	1	NO		●		YW1S-2E21	YW1S-21E21	—	—	
		2	NO		●						
		3	NC	●							
	1NO-2NC (12)	1	NO		●		YW1S-2E12	YW1S-21E12	—	—	
		2	NC	●							
		3	NC	●							
No. of Positions	Contact Configuration	Contact Block Mounting Position	Operator Position			Maintained	Spring Return from Right	Spring Return from Left	Spring Return Two-Way		
L	C	R									
45° 3-Position L C R	2NO (20)	1	NO	●			YW1S-3E20	YW1S-31E20	YW1S-32E20	YW1S-33E20	
		2									
		3	NO				●				
	2NO (20N1)	1		●			●	YW1S-3E20N1	YW1S-31E20N1	YW1S-32E20N1	YW1S-33E20N1
		2	NO				●				
		3	NO				●				
	2NC (02)	1	NC		●	●	YW1S-3E02	YW1S-31E02	YW1S-32E02	YW1S-33E02	
		2									
		3	NC	●	●						
	2NC (02N1)	1		●		●	YW1S-3E02N1	YW1S-31E02N1	YW1S-32E02N1	YW1S-33E02N1	
		2	NC		●						
		3	NC	●	●						
	1NO-1NC (11)	1	NO	●			YW1S-3E11	YW1S-31E11	YW1S-32E11	YW1S-33E11	
		2									
		3	NC	●	●						
	1NO-1NC (11N1)	1	NC		●	●	YW1S-3E11N1	YW1S-31E11N1	YW1S-32E11N1	YW1S-33E11N1	
		2									
		3	NO				●				
	1NO-1NC (11N2)	1	NO	●			YW1S-3E11N2	YW1S-31E11N2	YW1S-32E11N2	YW1S-33E11N2	
		2	NC		●						
		3									
	1NO-1NC (11N3)	1					YW1S-3E11N3	YW1S-31E11N3	YW1S-32E11N3	YW1S-33E11N3	
		2	NC		●						
		3	NO				●				
	1NO-1NC (11N4)	1		●		●	YW1S-3E11N4	YW1S-31E11N4	YW1S-32E11N4	YW1S-33E11N4	
		2	NO	●							
		3	NC	●	●						
	3NO (30)	1	NO	●		●	YW1S-3E30	YW1S-31E30	YW1S-32E30	YW1S-33E30	
		2	NO	●		●					
		3	NO				●				
	3NC (03)	1	NC		●	●	YW1S-3E03	YW1S-31E03	YW1S-32E03	YW1S-33E03	
		2	NC		●						
		3	NC	●	●						
	2NO-1NC (21)	1	NO	●		●	YW1S-3E21	YW1S-31E21	YW1S-32E21	YW1S-33E21	
		2	NC		●						
		3	NO				●				
	1NO-2NC (12)	1	NC	●	●	●	YW1S-3E12	YW1S-31E12	YW1S-32E12	YW1S-33E12	
		2	NO	●		●					
		3	NC	●							

Selector Switches with Metal Bezel

Style						Knob Type						
												
No. of Positions	Contact Configuration	Contact Block Mounting Position		Operator Position			Maintained	Spring Return from Right	—	—		
				L	R	—						
90° 2-Position L R	1NO (10)	1	NO			●		YW4S-2E10	YW4S-21E10	—	—	
		2										
		3										
	1NC (01)	1							YW4S-2E01	YW4S-21E01	—	—
		2										
		3	NC	●								
	2NO (20)	1	NO			●		YW4S-2E20	YW4S-21E20	—	—	
		2										
		3	NO			●						
	2NC (02)	1	NC	●				YW4S-2E02	YW4S-21E02	—	—	
		2										
		3	NC	●								
	1NO-1NC (11)	1	NO			●		YW4S-2E11	YW4S-21E11	—	—	
		2										
		3	NC	●								
	3NO (30)	1	NO			●		YW4S-2E30	YW4S-21E30	—	—	
		2	NO			●						
		3	NO			●						
	3NC (03)	1	NC	●				YW4S-2E03	YW4S-21E03	—	—	
		2	NC	●								
		3	NC	●								
	2NO-1NC (21)	1	NO			●		YW4S-2E21	YW4S-21E21	—	—	
		2	NO			●						
		3	NC	●								
	1NO-2NC (12)	1	NO			●		YW4S-2E12	YW4S-21E12	—	—	
		2	NC	●								
		3	NC	●								
	No. of Positions	Contact Configuration	Contact Block Mounting Position		Operator Position			Maintained	Spring Return from Right	Spring Return from Left	Spring Return Two-Way	
L	C	R										
45° 3-Position L C R	2NO (20)	1	NO	●				YW4S-3E20	YW4S-31E20	YW4S-32E20	YW4S-33E20	
		2										
		3	NO									
	2NO (20N1)	1							YW4S-3E20N1	YW4S-31E20N1	YW4S-32E20N1	YW4S-33E20N1
		2	NO	●			●					
		3	NO				●					
	2NC (02)	1	NC						YW4S-3E02	YW4S-31E02	YW4S-32E02	YW4S-33E02
		2										
		3	NC									
	2NC (02N1)	1							YW4S-3E02N1	YW4S-31E02N1	YW4S-32E02N1	YW4S-33E02N1
		2	NC			●						
		3	NC									
	1NO-1NC (11)	1	NO	●					YW4S-3E11	YW4S-31E11	YW4S-32E11	YW4S-33E11
		2										
		3	NC									
	1NO-1NC (11N1)	1	NC						YW4S-3E11N1	YW4S-31E11N1	YW4S-32E11N1	YW4S-33E11N1
		2										
		3	NO				●					
	1NO-1NC (11N2)	1	NO	●					YW4S-3E11N2	YW4S-31E11N2	YW4S-32E11N2	YW4S-33E11N2
		2	NC			●						
		3										
	1NO-1NC (11N3)	1							YW4S-3E11N3	YW4S-31E11N3	YW4S-32E11N3	YW4S-33E11N3
		2	NC			●						
		3	NO				●					
	1NO-1NC (11N4)	1	NO	●			●		YW4S-3E11N4	YW4S-31E11N4	YW4S-32E11N4	YW4S-33E11N4
		2	NO	●			●					
		3	NC									
	3NO (30)	1	NO	●			●		YW4S-3E30	YW4S-31E30	YW4S-32E30	YW4S-33E30
		2	NO	●			●					
		3	NO				●					
	3NC (03)	1	NC						YW4S-3E03	YW4S-31E03	YW4S-32E03	YW4S-33E03
		2	NC			●						
		3	NC									
	2NO-1NC (21)	1	NO	●					YW4S-3E21	YW4S-31E21	YW4S-32E21	YW4S-33E21
		2	NC			●						
		3	NO				●					
	1NO-2NC (12)	1	NC						YW4S-3E12	YW4S-31E12	YW4S-32E12	YW4S-33E12
		2	NO	●			●					
		3	NC									

Contact Block Mounting Position

• Selector Switch with Plastic Bezel


Contact Block
Mounting Position



L C R
Operator Position

Dimensions

• Selector Switch with Plastic Bezel




• Selector Switch with Metal Bezel

Contact Block
Mounting Position



L C R
Operator Position

• Selector Switch with Metal Bezel



All dimensions in mm.

Key Selector Switches

No. of Positions	Contact Configuration	Contact Block Mounting Position		Operator Position		Type No.	
				L	R	Plastic Bezel	Metal Bezel
							
90° 2-position Maintained 	1NO (10)	1	NO		●	YW1K-2AE10	YW4K-2AE10
		2					
		3					
	1NC (01)	1				YW1K-2AE01	YW4K-2AE01
		2					
		3	NC	●			
	2NO (20)	1	NO		●	YW1K-2AE20	YW4K-2AE20
		2					
		3	NO		●		
	2NC (02)	1	NC	●		YW1K-2AE02	YW4K-2AE02
		2					
		3	NC	●			
	1NO-1NC (11)	1	NO		●	YW1K-2AE11	YW4K-2AE11
		2					
		3	NC	●			
	3NO (30)	1	NO		●	YW1K-2AE30	YW4K-2AE30
		2	NO		●		
		3	NO		●		
	3NC (03)	1	NC	●		YW1K-2AE03	YW4K-2AE03
		2	NC	●			
		3	NC	●			
	2NO-1NC (21)	1	NO		●	YW1K-2AE21	YW4K-2AE21
		2	NO		●		
		3	NC	●			
	1NO-2NC (12)	1	NO		●	YW1K-2AE12	YW4K-2AE12
		2	NC	●			
		3	NC	●			
90° 2-position Spring Return from Right 	1NO (10)	1	NO		●	YW1K-21BE10	YW4K-21BE10
		2					
		3					
	1NC (01)	1				YW1K-21BE01	YW4K-21BE01
		2					
		3	NC	●			
	2NO (20)	1	NO		●	YW1K-21BE20	YW4K-21BE20
		2					
		3	NO		●		
	2NC (02)	1	NC	●		YW1K-21BE02	YW4K-21BE02
		2					
		3	NC	●			
	1NO-1NC (11)	1	NO		●	YW1K-21BE11	YW4K-21BE11
		2					
		3	NC	●			
	3NO (30)	1	NO		●	YW1K-21BE30	YW4K-21BE30
		2	NO		●		
		3	NO		●		
	3NC (03)	1	NC	●		YW1K-21BE03	YW4K-21BE03
		2	NC	●			
		3	NC	●			
	2NO-1NC (21)	1	NO		●	YW1K-21BE21	YW4K-21BE21
		2	NO		●		
		3	NC	●			
	1NO-2NC (12)	1	NO		●	YW1K-21BE12	YW4K-21BE12
		2	NC	●			
		3	NC	●			

- On the spring-returned types, the key can be removed only from the maintained position. On the maintained types, the key can be removed from every position. Key retained positions are also available. See the ordering information shown on page 20.
- Each key selector switch is supplied with two identical keys.

No. of Positions	Contact Configuration	Contact Block Mounting Position		Operator Position			Type No.	
				L	C	R	Plastic Bezel	Metal Bezel
45° 3-position Maintained	2NO (20)	1	NO	●			YW1K-3AE20	YW4K-3AE20
		2						
		3	NO			●		
	2NO (20N1)	1					YW1K-3AE20N1	YW4K-3AE20N1
		2	NO	●		●		
		3	NO			●		
	2NC (02)	1	NC		■	■	YW1K-3AE02	YW4K-3AE02
		2						
		3	NC	■	■			
	2NC (02N1)	1					YW1K-3AE02N1	YW4K-3AE02N1
		2	NC		●			
		3	NC	■	■			
	1NO-1NC (11)	1	NO	●			YW1K-3AE11	YW4K-3AE11
		2						
		3	NC	■	■			
	1NO-1NC (11N1)	1	NC		■	■	YW1K-3AE11N1	YW4K-3AE11N1
		2						
		3	NO			●		
	1NO-1NC (11N2)	1	NO	●			YW1K-3AE11N2	YW4K-3AE11N2
		2	NC		●			
		3						
	1NO-1NC (11N3)	1					YW1K-3AE11N3	YW4K-3AE11N3
		2	NC		●			
		3	NO			●		
	1NO-1NC (11N4)	1					YW1K-3AE11N4	YW4K-3AE11N4
		2	NO	●		●		
		3	NC	■	■			
	3NO (30)	1	NO	●			YW1K-3AE30	YW4K-3AE30
		2	NO	●		●		
		3	NO			●		
	3NC (03)	1	NC		■	■	YW1K-3AE03	YW4K-3AE03
		2	NC		●			
		3	NC	■	■			
	2NO-1NC (21)	1	NO	●			YW1K-3AE21	YW4K-3AE21
		2	NC		●			
		3	NO			●		
	1NO-2NC (12)	1	NC		■	■	YW1K-3AE12	YW4K-3AE12
		2	NO	●		●		
		3	NC	■	■			


- On the maintained types, the key can be removed from every position. Key retained positions are also available. See the ordering information shown below.
- Each key selector switch is supplied with two identical keys.

Ordering Information

YW1K-2 A E21

- Key removal position code
- 2-position
- A: Removable in all positions
 - B: Removable in left only
 - C: Removable in right only
- 3-position
- A: Removable in all positions
 - B: Removable in left and center
 - C: Removable in right and center
 - D: Removable in center only
 - E: Removable in right and left
 - G: Removable in left only
 - H: Removable in right only

Contact Block Mounting Position



No. of Positions	Contact Configuration	Contact Block Mounting Position		Operator Position			Type No.	
				L	C	R	Plastic Bezel	Metal Bezel
								
45° 3-position Spring Return from Right L C R	2NO (20)	1	NO	●			YW1K-31BE20	YW4K-31BE20
		2						
		3	NO			●		
	2NO (20N1)	1					YW1K-31BE20N1	YW4K-31BE20N1
		2	NO	●		●		
		3	NO			●		
	2NC (02)	1	NC		■		YW1K-31BE02	YW4K-31BE02
		2						
		3	NC	■				
	2NC (02N1)	1					YW1K-31BE02N1	YW4K-31BE02N1
		2	NC		●			
		3	NC	■				
	1NO-1NC (11)	1	NO	●			YW1K-31BE11	YW4K-31BE11
		2						
		3	NC	■				
	1NO-1NC (11N1)	1	NC		■		YW1K-31BE11N1	YW4K-31BE11N1
		2						
		3	NO			●		
	1NO-1NC (11N2)	1	NO	●			YW1K-31BE11N2	YW4K-31BE11N2
		2	NC		●			
		3						
	1NO-1NC (11N3)	1					YW1K-31BE11N3	YW4K-31BE11N3
		2	NC		●			
		3	NO			●		
	1NO-1NC (11N4)	1					YW1K-31BE11N4	YW4K-31BE11N4
		2	NO	●		●		
		3	NC	■				
	3NO (30)	1	NO	●			YW1K-31BE30	YW4K-31BE30
		2	NO	●		●		
		3	NO			●		
	3NC (03)	1	NC		■		YW1K-31BE03	YW4K-31BE03
		2	NC		●			
		3	NC	■				
	2NO-1NC (21)	1	NO	●			YW1K-31BE21	YW4K-31BE21
		2	NC		●			
		3	NO			●		
	1NO-2NC (12)	1	NC		■		YW1K-31BE12	YW4K-31BE12
		2	NO	●		●		
		3	NC	■				

- On the spring-returned types, the key can be removed only from the maintained position. Key retained positions are also available. See the ordering information shown on page 20.
- Each key selector switch is supplied with two identical keys.

ø22 YW Series Control Units

No. of Positions	Contact Configuration	Contact Block Mounting Position		Operator Position			Type No.	
				L	C	R	Plastic Bezel	Metal Bezel
45° 3-position Spring Return from Left	2NO (20)	1	NO	●			YW1K-32CE20	YW4K-32CE20
		2						
		3	NO			●		
	2NO (20N1)	1					YW1K-32CE20N1	YW4K-32CE20N1
		2	NO	●		●		
		3	NO			●		
	2NC (02)	1	NC		■	■	YW1K-32CE02	YW4K-32CE02
		2						
		3	NC	■	■			
	2NC (02N1)	1					YW1K-32CE02N1	YW4K-32CE02N1
		2	NC		●			
		3	NC	■	■			
	1NO-1NC (11)	1	NO	●			YW1K-32CE11	YW4K-32CE11
		2						
		3	NC	■	■			
	1NO-1NC (11N1)	1	NC		■	■	YW1K-32CE11N1	YW4K-32CE11N1
		2						
		3	NO			●		
	1NO-1NC (11N2)	1	NO	●			YW1K-32CE11N2	YW4K-32CE11N2
		2	NC		●			
		3						
	1NO-1NC (11N3)	1					YW1K-32CE11N3	YW4K-32CE11N3
		2	NC		●			
		3	NO			●		
	1NO-1NC (11N4)	1					YW1K-32CE11N4	YW4K-32CE11N4
		2	NO	●		●		
		3	NC	■	■			
	3NO (30)	1	NO	●			YW1K-32CE30	YW4K-32CE30
		2	NO	●		●		
		3	NO			●		
	3NC (03)	1	NC		■	■	YW1K-32CE03	YW4K-32CE03
		2	NC		●			
		3	NC	■	■			
	2NO-1NC (21)	1	NO	●			YW1K-32CE21	YW4K-32CE21
		2	NC		●			
		3	NO			●		
	1NO-2NC (12)	1	NC		■	■	YW1K-32CE12	YW4K-32CE12
		2	NO	●		●		
		3	NC	■	■			


- On the spring-returned types, the key can be removed only from the maintained position. Key retained positions are also available. See the ordering information shown on page 20.
- Each key selector switch is supplied with two identical keys.

No. of Positions	Contact Configuration	Contact Block Mounting Position		Operator Position			Type No.	
				L	C	R	Plastic Bezel	Metal Bezel
								
45° 3-position Spring Return Two-way 	2NO (20)	1	NO	●			YW1K-33DE20	YW4K-33DE20
		2						
		3	NO			●		
	2NO (20N1)	1					YW1K-33DE20N1	YW4K-33DE20N1
		2	NO	●		●		
		3	NO			●		
	2NC (02)	1	NC		■		YW1K-33DE02	YW4K-33DE02
		2						
		3	NC	■				
	2NC (02N1)	1					YW1K-33DE02N1	YW4K-33DE02N1
		2	NC		●			
		3	NC	■				
	1NO-1NC (11)	1	NO	●			YW1K-33DE11	YW4K-33DE11
		2						
		3	NC	■				
	1NO-1NC (11N1)	1	NC		■		YW1K-33DE11N1	YW4K-33DE11N1
		2						
		3	NO			●		
	1NO-1NC (11N2)	1	NO	●			YW1K-33DE11N2	YW4K-33DE11N2
		2	NC		●			
		3						
	1NO-1NC (11N3)	1					YW1K-33DE11N3	YW4K-33DE11N3
		2	NC		●			
		3	NO			●		
	1NO-1NC (11N4)	1					YW1K-33DE11N4	YW4K-33DE11N4
		2	NO	●		●		
		3	NC	■				
	3NO (30)	1	NO	●			YW1K-33DE30	YW4K-33DE30
		2	NO	●		●		
		3	NO			●		
	3NC (03)	1	NC		■		YW1K-33DE03	YW4K-33DE03
		2	NC		●			
		3	NC	■				
	2NO-1NC (21)	1	NO	●			YW1K-33DE21	YW4K-33DE21
		2	NC		●			
		3	NO			●		
	1NO-2NC (12)	1	NC		■		YW1K-33DE12	YW4K-33DE12
		2	NO	●		●		
		3	NC	■				


- On the spring-returned types, the key can be removed only from the maintained position. Key retained positions are also available. See the ordering information shown on page 20.
- Each key selector switch is supplied with two identical keys.

Dimensions (Key Selector Switch)

• Plastic Bezel














• Metal Bezel













All dimensions in mm.

Accessories

Name & Shape	Ordering Type No.	Description & Dimensions (mm)	Package Quantity
	MW9Z-T1	Metallic tool used to tighten the plastic locking ring when installing the YW series control unit in a panel. 	1
	OR-55	Made of rubber. Used for replacing lamps. 	1
	OB-31PN05	Used for plugging unused mounting holes in the panel. Color: Black 	5
	LW9Z-BM	Used for plugging unused mounting holes in the panel. Weight: Approx. 18g 	1
	HW9Z-RLPN10	Prevents rotation of switches in panel. Mainly used with selector switches when no nameplate is used. With waterproof gasket (IP65). Made of plastic (black). Applicable panel thickness: 1.2 to 4.5 mm 	10

Name & Shape	Ordering Type No.	Description & Dimensions (mm)		Package Quantity
Padlock Cover 	HW9Z-KL1	Plastic hinged cover to protect pushbuttons, illuminated pushbuttons, or selector switches. Degree of protection: IP65. Applicable panel thickness: 0.8 to 3.2 mm 		1
LED Lamp 	LSED-6②	6V AC/DC	Specify a color code in place of ② in the Type No.: A (amber), G (green), PW (pure white), R (red), S (blue), Y (yellow) Applicable units: • LED illuminated pilot lights • LED illuminated pushbuttons 	1
	LSED-1②	12V AC/DC		
	LSED-2②	24V AC/DC		
LED Lamp 	LSED-H②	110V AC/DC	For the rated current, see page 4. Note: Yellow LED lamps are used for white illumination of pilot lights and illuminated push-buttons. 	1
	LSED-M3②	230/240V AC/DC		
Incandescent Lamp 	LS-T6P	6.3V, 1W	One pack contains 100 incandescent lamps. 	100
	LS-T8P	18V, 1W		
	LS-T3P	30V, 1W		
Single Contact Block 	YW-E10P	Contact: 1NO		10
	YW-E01P	Contact: 1NC		
Double Contact Block 	YW-EW20P	Contact: 2NO	 Note: Double contact blocks cannot be used on emergency stop switches.	10
	YW-EW11P	Contact: 1NO-1NC		
	YW-EW02P	Contact: 2NC		
Spare Key 	YW9Z-SK00PN02			2

Buttons, Lenses, and Marking Plates

Name	Style	Ordering Type No.	① ② Color Code	Dimensions (mm)	Package Quantity
Button (for pushbuttons)	Extended	YW9Z-B12①PN10	B: black G: green R: red S: blue W: white Y: yellow		10
	Mushroom ø40mm	YW9Z-B14①PN10			
Lens (for pilot lights)	Flush	YW9Z-PL11②PN10	A: amber C: clear G: green R: red S: blue W: white Y: yellow		10
	Flush Marking	YW9Z-PL11B②PN10	A: :amber C: clear G: green R: red S: blue Y: yellow		10
	Extended	YW9Z-PL12T②PN10	A: amber C: clear G: green R: red S: blue W: white Y: yellow		10
	Dome	YW9Z-PL12②PN10	A: :amber C: clear G: green R: red S: blue W: white Y: yellow		10
Lens (for illuminated pushbuttons)	Extended	YW9Z-L12②PN10	A: amber C: clear G: green R: red S: blue Y: yellow		10
	Mushroom ø40mm	YW9Z-L14②PN10			
Marking Plate (for pilot lights)	—	YW9Z-PP12PN10	—		10
Marking Plate (for illuminated pushbuttons)	—	YW9Z-P12PN10	—		10

Nameplates

• HWAM, HWAQ, HWAS, and HWAV

Type	Legend	Material	Type No.	Ordering Type No.	Package Quantity	Dimensions (mm)
HWAM	Order marking plate separately.	Plastic (black) 1.5 mm thick	HWAM	HWAM	1	
				HWAMPN10	10	
HWAQ	Order marking plate separately.	Plastic (black) 1.5 mm thick	HWAQ	HWAQ	1	
				HWAQPN10	10	
HWAS	Blank	Plastic (black) 1.5 mm thick	HWAS-0	HWAS-0	1	
				HWAS-0PN10	10	
HWAV	Blank	Plastic (yellow) 1.5 mm thick	HWAV-0	HWAV-0	1	
	EMERGENCY STOP		HWAV-27	HWAV-27	1	

• Legend "Emergency Stop" is indicated outside a ø44mm circle.

• Making Plate


Description	Material	Type No.	Ordering Type No.	Package Quantity	Dimensions (mm)
HWNP	Aluminum (black) 1.0 mm thick	HWNP-*	HWNP-*	1	
			HWNP-*PN10	10	

• Specify a legend code in place of * in the Ordering Type No.


Legends

Code	Legend
0	(blank)
1	ON
2	OFF
3	START
4	STOP
31	OFF-ON
35	HAND-AUTO
53	HAND-OFF-AUTO

• Installing the marking plate on a nameplate







• To remove the marking plate, insert the flat screwdriver between the marking plate and nameplate.



When requiring no anti-rotation, remove the projection using pliers.

Note: When using an nameplate, the mounting panel thickness is decreased by 1.5 mm.

EMO Switch Guards

Type No. & Appearance	Dimensions (mm)	Type No. & Appearance	Dimensions (mm)
HW9Z-KG1  EMO Switch Guard SEMI S2 compliant (Note 1)		HW9Z-KG3  EMO Switch Guard SEMI S2 compliant (Note 2)	
HW9Z-KG2  EMO Switch Guard SEMI S2 compliant (Note 1) SEMATECH compliant (Note 3)		HW9Z-KG4  EMO Switch Guard SEMI S2 compliant (Note 2) SEMATECH compliant (Note 3)	

Material: Polyamide (PA6)
 Color: Yellow, Munsell 2.5Y 8/10 equivalent
 Degree of protection: IP65


• Degree of protection IP65 applies to the combination of an emergency stop switch and an EMO switch guard.

Note 1: SEMI S2-0703 12.5.1 compliant.

Note 2: The combination of IDEC's emergency stop switches and EMO switch guards are approved by TÜV Rheinland for compliance with SEMI S2 standard.


Note 3: SEMATECH Application Guide for SEMI S2-93, 12.4.c. compliant.

Separate DIN Rail Mounting Type Transformer



Primary Voltage (50/60 Hz)	Type No.	Applicable Lamp Rating
110V AC	TWR516	One full voltage type illuminated unit containing LED lamp LSED-6 (6V AC/DC) or incandescent lamp LS-T6 (6.3V)
115V AC	TWR5116	
120V AC	TWR5126	
220V AC	TWR526	
230V AC	TWR5236	
240V AC	TWR5246	
380V AC	TWR5386	
440V AC	TWR546	
480V AC	TWR5486	

• Dimensions (mm)



Note: Finger-safe terminal cover is supplied with the transformer.

Safety Precautions

- Turn off the power to the YV series control units before starting installation, removal, wiring, maintenance, and inspection of the products. Failure to turn power off may cause electrical shocks or fire hazard.
- To avoid burning your hand, use the lamp holder tool when replacing lamps.

ing lamps.

- For wiring, use wires of a proper size to meet the voltage and current requirements. Tighten the M3.5 terminal screws to a tightening torque of 1.0 N·m. Failure to tighten the terminal screws may cause overheating and fire.

Instructions

Panel Mounting

- Remove the contact block from the operator (for pilot lights, remove the transformer or full voltage unit from the pilot light). Remove the locking ring from the operator. Insert the operator into the panel cut-out from the front, tighten the locking ring from the back, then install the contact block to the operator.

• Removing and Installing the Contact Block



- ① Pull up the locking lever.
- ② Turn the lever to the left.


- ③ Pull out the contact block.

- To remove the operator from the contact block, pull up the locking lever and turn it to the left. Then the operator can be pulled out.
- To reinstall, place the TOP marking on the operator and the idec marking on the contact block mounting adapter in the same direction, and insert the operator into the contact block mounting adapter. Then turn the locking lever to the right.




• Removing and Installing the Transformer Unit

- Insert a flat screwdriver (5 mm wide at maximum) into the latch hole on the transformer unit as shown in the photo below, and disengage the latch. Then pull out the operator.
- To reinstall, place the TOP marking on the operator and the latch in the same direction, and push the operator into the transformer unit.



• Removing the Full Voltage Unit




- To remove the full voltage unit, squeeze the full voltage unit from both sides to disengage the latch as shown, and pull it out. Like the transformer unit, the full voltage unit can also be pulled out by inserting a flat screwdriver into the latch hole as shown.
- To reinstall, place the TOP markings on the operator and the latch on the full voltage unit in the same direction, and insert the operator into the full voltage unit.

• Notes for Panel Mounting


- Use the optional locking ring wrench (MW9Z-T1) to mount the operator onto a panel. Tightening torque must not exceed 2.0 N·m. Do not use pliers. Excessive tightening will damage the locking ring.
- For contact blocks and transformers housing LED and incandescent lamps, make sure not to press the lamps too hard, otherwise the lamp socket may be damaged.

Insertion Order of Lens and Marking Plate

• Illuminated Pushbutton



• Pilot Light



Marking

For YW series pilot lights and illuminated pushbuttons, legends and symbols can be engraved on built-in marking plates, or printed mylar film can be inserted under the lens for labeling purposes. Mylar film is not supplied with the control units and must be supplied by the end user.

- **Built-in Marking Plate and Marking Film Size**

Unit	Pilot Light	Illuminated Pushbutton
Built-in Marking Plate		
	Engraving depth: 0.5 mm maximum Marking plate material: White acrylic	
Applicable Marking Film		
	0.1-mm-thick × 2 sheets or 0.2-mm-thick × 1 sheet Film material: Mylar (not recommended) Note: Marking film is not supplied with the pilot light or illuminated pushbutton.	

- **Replacement (LED and incandescent lamps)**

Lamps can be replaced using the lamp holder tool (OR-55) from the front of the panel, or by removing the contact block from the operator unit.


- **Removing the Lamp from the Front of the Panel**




To remove, gently insert the lamp holder tool onto the lamp head. Then push slightly, and turn the lamp holder tool to the left.

- **Installing the Lamp from the Front of the Panel**

1. To install, insert the lamp head into the lamp holder tool, and hold the lamp as shown in the figure below.



2. Place the pins on the lamp base to the grooves in the lamp socket. Insert the lamp and turn it to the right.




Note: LED lamps in unibody type pilot lights cannot be replaced.

Removing Contact Blocks and Full Voltage Adapter

Insert a flat screwdriver between the latch and contact block mounting adapter, and disengage the latch.



Make sure to remove the lamp and contact blocks before removing the full voltage adapter.




Tightening Torque for Terminal Screws

Tighten terminal screws to a torque of 1.0 N·m.


Anti-rotation Ring and Mounting Panel

Turn the TOP marking on the operator and the ▲ mark on the anti-rotation ring to the recess on the mounting panel.



Mounting Panel Thickness

The mounting panel must be 0.8 to 6.0 mm in thickness. When optional accessories are added, the applicable panel thickness changes as shown below.




Contact Bounce

When pressing or turning the operator, the NC and NO contacts will bounce. When designing a control circuit, take the contact bounce time into consideration (reference value: 20 ms).

Precautions for Noise

When using the unibody pilot light in an environment where it is subjected to noise, connect a noise suppressor across terminals X1 and X2 as shown below.




Key Selector Switch

Before operation, ensure that the key is inserted into the key hole completely. Operating the key selector switch with a loose key will cause damage to the key selector switch.

Nameplate

When anti-rotation is not required, remove the projection from the nameplate using pliers.



Handling

Do not expose the switch to excessive shock and vibration, otherwise the switch may be deformed or damaged, causing malfunction or operation failure.



Instructions

LED Illumination

LED lamps consist of semiconductors. If the applied voltage exceeds the rated voltage, LED elements deteriorate due to over-heat, resulting in significant decrease in brightness, hue change, or failure of lighting. Also, if extraneous noise, transient voltage, or transient current is applied to the circuit, similar effects will be caused. When using LED lamps, observe the following instructions.

• Rated Voltage

The LED illuminated units are rated at 6V, 12V, 24V, 110V, or 230/240V AC/DC, and can be used within $\pm 10\%$ the rated voltage of either AC or DC, except the 230/240V AC/DC types can be used on 250V AC/DC maximum.


• DC Power

1. Switching power supply
Regulated voltage from a switching power supply is best suited. Make sure to use within the rated voltage of the LED lamp.
2. Rechargeable battery
Note that the battery voltage may exceed the rated voltage of the LED lamp while the battery is being charged and immediately after the charging is complete. Be sure to use the LED lamp on a voltage of $\pm 10\%$ the rated voltage, except the 230/240V AC/DC types on 250V AC/DC maximum.
3. Full-wave rectification
Since the LED lamp is AC/DC compatible, a diode bridge for rectification is not necessary. If the LED lamp is used on a full-wave rectification current through a diode bridge, the rectifier diodes will reduce the voltage, resulting in lower brightness.
4. Single-phase half-wave rectification
This is not suitable for the power source of LED lamps. Use constant-voltage DC power.


• Noise

LED elements deteriorate due to extraneous noise, resulting in significant decrease in brightness, hue change, or failure of lighting. When such effects are anticipated, take a protection measure shown below, such as RC elements or a surge absorber.

[Protection Example 1] For AC circuit



[Protection Example 2] For DC circuit




• Countermeasures against Dim Lighting

1. Leakage current through transistors or a contact protection circuit may cause the LED lamp to illuminate dimly even when the output is off.
2. When the LED lamp is illuminated by a transistor output, take the following measure.

[Circuit Example]

Connect shunt resistor R in parallel with the LED lamp.



I_o : Leakage current when the output is off
R: Shunt resistor

Ordering Information

- When ordering, specify the Type No. and quantity.
- Replacement contact blocks are supplied in a package containing 10 pieces.

Specifications and other descriptions in this catalog are subject to change without notice.



IDEC CORPORATION

7-31, Nishi-Miyahara 1-Chome, Yodogawa-ku, Osaka 532-8550, Japan
Tel: +81-6-6398-2571, Fax: +81-6-6392-9731
E-mail: marketing@idec.co.jp

IDEC CORPORATION (USA)
1175 Elko Drive, Sunnyvale, CA 94089-2209, USA
Tel: +1-408-747-0550 / (800) 262-IDEC (4332)
Fax: +1-408-744-9055 / (800) 635-6246
E-mail: opencontact@idec.com

IDEC CANADA LIMITED
3155 Pepper Mill Court, Unit 4, Mississauga,
Ontario, L5L 4X7, Canada
Tel: +1-905-890-8561, Toll Free: (888) 317-4332
Fax: +1-905-890-8562
E-mail: sales@ca.idec.com

IDEC AUSTRALIA PTY. LTD.
2/3 Macro Court, Rowville, Victoria 3178, Australia
Tel: +61-3-9763-3244, Toll Free: 1800-68-4332
Fax: +61-3-9763-3255
E-mail: sales@au.idec.com

IDEC ELECTRONICS LIMITED
Unit 2, Beechwood, Chineham Business Park,
Basingstoke, Hampshire RG24 8WA, UK
Tel: +44-1256-321000, Fax: +44-1256-327755
E-mail: sales@uk.idec.com

IDEC ELEKTROTECHNIK GmbH
Wendenstrasse 331, 20537 Hamburg, Germany
Tel: +49-40-25 30 54 - 0, Fax: +49-40-25 30 54 - 24
E-mail: service@idec.de

IDEC (SHANGHAI) CORPORATION
Room 608-609, 6F, Gangtai Plaza, No. 700,
Yan'an East Road, Shanghai 200001, PRC
Tel: +86-21-5353-1000, Fax: +86-21-5353-1263
E-mail: idec@cn.idec.com

IDEC (BEIJING) CORPORATION
Room 211B, Tower B, The Grand Pacific Building,
8A Guanghua Road, Chaoyang District,
Beijing 100026, PRC
Tel: +86-10-6581-6131, Fax: +86-10-6581-5119

IDEC (SHENZHEN) CORPORATION
Unit AB-3B2, Tian Xiang Building, Tian'an Cyber Park,
Fu Tian District, Shenzhen, Guang Dong 518040, PRC
Tel: +86-755-8356-2977, Fax: +86-755-8356-2944

IDEC IZUMI (H.K.) CO., LTD.
Units 11-15, Level 27, Tower 1,
Millennium City 1, 388 Kwun Tong Road,
Kwun Tong, Kowloon, Hong Kong
Tel: +852-2803-8989, Fax: +852-2565-0171
E-mail: info@hk.idec.com

IDEC TAIWAN CORPORATION
8F-1, No. 79, Hsin Tai Wu Road, Sec. 1,
Hsi-Chih, Taipei County, Taiwan
Tel: +886-2-2698-3929, Fax: +886-2-2698-3931
E-mail: service@tw.idec.com

IDEC IZUMI ASIA PTE. LTD.
No. 31, Tannery Lane #05-01,
HB Centre 2, Singapore 347788
Tel: +65-6746-1155, Fax: +65-6844-5995
E-mail: info@sg.idec.com