

## SmartRack 9U Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRW9U**



### Description

The SRW9U 9U Wall-Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications where floor space is limited and security is a consideration. Its locking doors and side panels offer a perfect solution for keeping limited-access devices secure and out of the way in classrooms, back offices and storage closets. Its ventilated, reversible front door and removable side panels allow generous airflow to keep equipment operating safely. Adjustable vertical mounting rails with square holes accommodate up to 9U of all standard 19-inch rack equipment. It supports up to 200 lbs of equipment. A sturdy wall-mount bracket allows the cabinet to easily be hung on the wall. The SRW9U wall-mount rack cabinet ships fully assembled and comes backed by a 5-year warranty.

### Features

#### Space-Saving, Wall-Mounting

The SRW9U Wall-Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in a full 9U rack for installations where space is limited.

#### Easy Installation

The SRW9U ships fully assembled for quick and easy deployment. Rail adjustment is quick and convenient—simply unscrew the rails, slide them to the desired depth and restore the screws. Both the front and rear pairs of rails adjust in 1/4-inch increments with numbered rack spaces for easy reference. Square mounting holes and included mounting hardware support up to 200 lbs. of standard 19-inch rack equipment. The optional SRCASTER rolling caster kit adapts the enclosure to floor-standing and rollaway applications under desks, tables or counters.

#### Secure Equipment Access

Designed to provide a safe, secure installation solution for mission-critical rackmount equipment, the SRW9U features a locking, reversible front door and locking, removable side panels. This prevents unauthorized access to installed equipment while making it easy for authorized personnel to perform inspections, maintenance and equipment replacement. The swing direction of the front door can be reversed by rotating the enclosure 180 degrees before installation. The side panels and door are perforated to allow generous airflow.

### Highlights

- Ideal for IT and education environments where equipment needs to be secure and out of the way
- 9U with adjustable front vertical rackmount rails and a mounting depth of up to 17 inches
- Heavy-duty steel construction supports up to 200 lbs. of equipment
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

### Applications

IT network environments with limited floor space and classrooms where equipment needs to be secure and out of the way of students.

### Package Includes

- SRW9U Wallmount Rack Enclosure
- (18) M6 screws
- (18) M6 cage nuts
- (18) M6 washers
- (2) Keys
- Owner's Manual

#### PCI DSS Compliance

The SRW9U meets all requirements toward PCI DSS (Payment Card Industry Data Security Standard) compliance. A locking, reversible front door and locking, removable side panels restrict unwanted access to installed equipment while still allowing authorized personnel to perform inspections, maintenance and equipment replacement.

#### Vented Top and Bottom Panels with Cable Cutouts

The top and bottom panels of the SRW9U are furnished with vents designed to help remove warm air from the enclosure and draw in cool air by convection. They also support installation of standard user-supplied case fans. The top and bottom panels are also provided with ports for cable routing through the enclosure. Removable covers block unused cable ports.

#### 5-Year Warranty

The SRW9U is manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility. For peace of mind, it comes backed by a 5-year warranty.

## Specifications

General Info	
Product Group	RACKS
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	16.5
Installed Whole System Maximum Rack Depth (cm)	41.9
Installed Whole System Minimum Rack Depth (in.)	3
Rack Height	9U
Shipping Dimensions (hwd / in.)	22.6 x 26.4 x 20.5
Shipping Dimensions (hwd / cm)	57.40 x 67.06 x 52.07
Shipping Weight (lbs.)	38.4
Shipping Weight (kg)	17.41
Unit Dimensions (in.)	19.88 x 23.63 x 17.78
Unit Weight (lbs.)	35
Unit Weight (kg)	15.875
Unit Dimensions (cm)	50.49 x 60.02 x 45.16
Color	Black
Style	Wall Mounted
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.7



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
<b>SPECIAL FEATURES</b>	
Grounding Lug	Front and Back door frames
<b>CERTIFICATIONS</b>	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.