

**Part Number: 87657-0011**

1.27mm Pitch DDR DIMM Socket, Vertical, Extended Height, Single Key, with Plastic Pegs, 184 Circuits

Image not available

Status:	OBsolete
Replacement:	87636
Series:	87657
Category:	Memory Module Sockets

Series image - Reference only

Mates With Part(s):

JEDEC standard 1.27mm modules

Product Environmental ComplianceEU RoHS: Compliance Status Not ReviewedChina RoHS:REACH SVHC: Not ReviewedLow-Halogen Status: Not Reviewed**Part Detail****General**

Status	Obsolete
Category	Memory Module Sockets
Series	87657
Component Type	Socket
JEDEC Outline	MO-206
Obsolete Date	2004/04/01
Product Name	DDR DIMM

Physical

Circuits (Loaded)	184
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Keying to Mating Part	Yes
Material - Plating Mating	Gold
PC Tail Length	2.67mm, 3.23mm
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Plating min - Mating	0.381µm
Temperature Range - Operating	-10°C to +85°C
Termination Interface: Style	Through Hole

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Voltage - Maximum	30V
Voltage Key	1.8V, Center

Material Info**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**[Check our list of old tooling that used to be available for this part](#)